



Diagonal Cutters

ISO 5749



70 01 160




70 02 160




70 08 160 SBA




- the essential cutting tool for versatile use
- high quality material and precise workmanship for long service life
- precision cutting edges (cutting edge hardness approx. 62 HRC) for soft and hard wire
- clean cutting of thin copper wires, also at the cutting edge tips
- narrow head style for use in confined areas
- Vanadium electric steel; forged, oil-hardened



Cuts fine wires cleanly over the complete length of the blades



The slim head style and precise cutting capability are perfect for working in confined areas



Product Number	↔ inch	↔ mm		Pliers	Head	Handles	Cutting capacities						
							Ø inch	Ø inch	Ø inch	Ø mm	Ø mm	Ø mm	Ounces
70 01 110	4 1/4	110					1/8	5/64	3/64	3.0	2.0	1.2	2.8
70 01 125	5	125					1/8	3/32	1/16	3.0	2.3	1.5	2.8
70 01 140	5 1/2	140	✓	black atramentized	polished	plastic coated	5/32	3/32	5/64	4.0	2.5	1.8	4.4
70 01 160	6 1/4	160					5/32	7/64	5/64	4.0	2.8	2.0	6.0
70 01 180	7 1/4	180					5/32	1/8	3/32	4.0	3.0	2.5	7.1
70 02 125	5	125					1/8	3/32	1/16	3.0	2.3	1.5	4.2
70 02 140	5 1/2	140	✓	black atramentized	polished	with multi-component grips	5/32	3/32	5/64	4.0	2.5	1.8	5.3
70 02 160	6 1/4	160					5/32	7/64	5/64	4.0	2.8	2.0	7.3
70 02 180	7 1/4	180					5/32	1/8	3/32	4.0	3.0	2.5	8.9
70 08 160 SBA	6 1/4	160	⚠ 1000V	black atramentized	polished	insulated with multi-component grips, VDE-tested	5/32	7/64	5/64	4.0	2.8	2.0	6.0
70 08 180 SBA	7 1/4	180	⚠ 1000V	black atramentized	polished	insulated with multi-component grips, VDE-tested	5/32	1/8	3/32	4.0	3.0	2.5	7.1