



## Kvaser D-sub 9 pin 120 Ohm termination adapter

## EAN: 73-30130-00801-4


Kvaser D-sub 9 pin 120 Ohm termination adapter is a CAN adaptor with a 9pin male D-Sub connector at one end and a 9-pin female D-Sub socket at the other. Between CAN High (pin 7) and CAN Low (pin 2) there is a built-in 120 Ohm CAN terminating resistor.

This adapter provides quick and easy termination to any Kvaser high-speed CAN product. The Kvaser CAN termination adapter is used when there is a need to terminate a CAN node without internal termination or when no CAN node is connected to the bus. The Kvaser D-sub 9 pin 120 Ohm termination adapter has a 9-pin male D-Sub plug connector and a 9-pin female D-Sub socket. A 120 ohm terminating resistor sits between pins 2 and 7.



## TECHNICAL DATA - KVASER D-SUB 9 PIN 120 OHM TERMINATION ADAPTER

CASING MATERIAL	
CAN FD	No
RUGGED	N/A
CASING MATERIAL	N/A
WEIGHT (G)	N/A
ON-BOARD RX BUFFER	N/A
HEIGHT (MM)	N/A
OPERATING SYSTEM	Linux,Win Vista,Win 10,Win 8,Win 7,Win XP
TIMESTAMP RESOLUTION (US)	N/A
STATUS	Active
GALVANIC ISOLATION	N/A
NETWORK CHANNEL(S)	
CERTIFICATIONS	CE,RoHS
MINIMUM BITRATE (KBPS)	N/A
IP CLASS	N/A
WIDTH (MM)	N/A
ERROR COUNTERS READING	N/A
ERROR FRAME GENERATION	N/A
MAXIMUM BITRATE (KBPS)	N/A
CURRENT CONSUMPTION	N/A
EMBEDDED SCRIPT	No
API, FREE	N/A
CLOCK SYNC	N/A
OPERATING TEMPERATURE RANGE (C)	-30.00 to 85.00
CONNECTOR	DSUB 9
PIN COUNT	N/A





API, LICENCED	None
# OF CAN CHANNELS	0
ERROR FRAME DETECTION	N/A
ON-BOARD BUFFER	N/A
ON-BOARD TX BUFFER	N/A
PC INTERFACE	Cable
SOUND	N/A
LENGTH (MM)	N/A
PRODUCT GROUPS	Accessory
MSGRATE TX MAX	N/A
SILENT MODE	N/A
PLAY BACK LOG FILE	No
CB BOARD	No
DATABASE DBC SUPPORT	No
MSGRATE RX MAX	N/A
The information bergin is subject to shange without potice	

The information herein is subject to change without notice