

661 SERIES PANEL INDICATOR LED



FEATURES

- Ø10.2mm mounting
- Plastic housing
- · Sealed to IP67 weatherproof
- Bi-polar operation
- Range of LED colour options
- · Choice of solder pins or wires

BENEFITS

- · Standard industrial mounting size
- Low cost, lightweight solution
- · Suitable for external applications
- · Prevents wrong polarity installation
- · Suitable for status panel indication
- · Flexibility for different applications
- · Outstanding reliability

Marl Part Number	LED Colour	Lens Appearance	Typical Voltage DC Vopr	Max. Power Dissipation	Typical LED Luminous Intensity @20mA	Typical LED Wavelength λp	Viewing Angle 2 O 1/2	Operating Temp Topr *	Storage Temp Tstg
661-505-64	Red	White Diffused	8-48	400	14	645	120	-30 to +85	-40 to +85
661-508-64	Amber	White Diffused	8-48	400	9	605	120	-30 to +85	-40 to +85
661-511-64	Yellow	White Diffused	8-48	400	105	590	120	-30 to +85	-40 to +85
661-514-64	Green	White Diffused	8-48	400	11	568	120	-30 to +85	-40 to +85
661-520-64	Blue	White Diffused	8-48	400	70	430	120	-30 to +85	-40 to +85
661-997-64	White (5000K)	White Diffused	8-48	400	210	N/A	120	-30 to +85	-40 to +85
			Vdc	mW	mcd	nm	Deg	°C	°C

OPTIONAL FLYING LEAD TERMINATORS

Marl Part No Suffix	Wire Length	No/Diameter of Conductors	Diameter of Insulation	Wire Specification
661-505-04 -40	305mm	11/0.16mm	1.15mm	24AWG

NOTES

All LED components are supplied in anti-static packaging.

* LED Characteristics stated at Ta = 25°C. For operating temperature derating graphs, please refer to sheet 2.









F +44 (0) 1229 585 155 | E sales@marl.co.uk | www.leds.co.uk



661 SERIES PANEL INDICATOR LED

TECHNICAL CHARACTERISTICS

Series	Panel Cutout	Min. Mounting Centres	Min Max. Panel Thickness	Nut mounting torque
661	10.2	25.0	1.5 - 6.0	0.35
	mm	mm	mm	Nm


TECHNICAL DRAWING

Dimensions in mm (typical). Not to scale. Mounting hole to be clean and burr free.


Standard Version

Weight (g): 3.2












Flying Leads Version








DE-RATING GRAPHS





MATERIALS

Body Polycarbonate Polycarbonate Lens Termination (Standard version) LED Leads

Termination (Flying Leads version) Wires, Stripped and Tinned

Nut Lock Washer Sealing Ring

Stainless Steel Stainless Steel Silicone Rubber

DESIGN CONSIDERATIONS

Electro-Static Discharge (ESD)

Build up of electro-static discharge occurs in many situations involving people moving and handling products. The range of possible situations is very diverse but voltage levels as high as several thousand volts can and do arise in many individual situations. When an operator charged up to these levels handles a static sensitive device, there is a very probable likelihood that the device will be irreversibly damaged. It is essential that precautions are taken at all stages during manufacture and assembly of these products. Although LEDs were never considered to be static sensitive

devices, changes in manufacturing technology and materials used to produce higher intensity products over a large range of the wavelength spectrum have changed this. Marl has an approved system of ESD control from goods in, through production and into final packing and despatch. Marl recommend all users of LED based products follow the guidelines of BS 100015.

Voltage, Current and Temperature

The forward voltage / current value of an LED is dependent upon the ambient temperature of the environment in which it is operated. Therefore, care must be taken to operate the LED at the correct voltage / current values, depending upon the ambient temperature.

Marl should be contacted if the device is to be operated outside the temperature range specified. Marl accept no liability for any product that is operated outside the stated voltage or temperature range.

To order please contact us on +44 (0) 1229 582 430

F +44 (0) 1229 585 155 | E sales@marl.co.uk | www.leds.co.uk



f marlinternationallimited in company/marl-international-limited





