Data Sheet



RF Attenuator 6620_SMA-50-2/199_N

Description

Standard Attenuator, Low Power



Product Configuration

Connector (side 1 / side 2) SMA plug (male) / SMA jack (female)

Interface Standards IEC 60169-15_MIL-STD-348A/310_CECC 22110

Technical Data

Electrical Data

 $\begin{array}{lll} \mbox{Nominal impedance} & 50 \ \Omega \\ \mbox{Nominal attenuation} & 20 \ \mbox{dB} \\ \mbox{Frequency range} & DC \ \mbox{to 6 GHz} \\ \mbox{Attenuation deviation (<math>\pm \mbox{dB}$)} & 0.75 \\ \mbox{VSWR max.} & 1.2 \\ \end{array}

Power rating 2 Watt average power up to 25 °C ambient temperature, linearly derated to 1.1 Watt at 85 °C ambient

emperature.

Mechanical Data

Weight 0.004 kg

Environmental Data

Operating temperature -20 °C to 85 °C 2011/65/EU (RoHS - including 2015/863 and 2017/2102) compliant

Material Data

Piece Part (side 1)	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating
Outer contact	Stainless Steel	Passivated (Plating)
Body	Stainless Steel	Passivated (Plating)
Insulator	PTFE (Polytetrafluoroethylene)	
Coupling nut	Stainless Steel	Passivated (Plating)
Piece Part (side2)	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating
Outer contact	Stainless Steel	Passivated (Plating)
Body	Stainless Steel	Passivated (Plating)
Insulator	DTEE (Delutetraficare ethylone)	
Ilisulator	PTFE (Polytetrafluoroethylene)	

Related Documents

Outline drawing DOU-00095953

Ordering Information

Single packaging 6620_SMA-50-2/199_NE

HUBER+SUHNER is certified according to ISO 9001, ISO 14001, ISO/TS 16949 and IRIS

www.hubersuhner.com

Waiver: It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical specifications and/or the fitness for any particular purpose. The facts and figures contained herein are carefully compiled to the best of our knowledge, but they are intended for general information purposes only.