

FEATURES

- Our model gives you ABS with polycarbonate lids
- IP66 rating
- Sustaining process temperature of 0°C up to 90°C
- The application provides an adjustable control temperature range
- The thermostat has the following dimensions 75 mm (height) x 125 mm (length) x 125mm (width)
- Low-cost Thermostat

RS PRO Trace Heating Thermostat 75mm x 125mm x 125 mm, 0 → +90 °C

RS Stock No.: 665-7551



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Trace Heating Thermostat accompaniment each other with surface heating systems as temperature control can significantly reduce the network operating cost up to 90%. Controlling your trace heating using our Thermostat is giving you many advantages to use in domestic, commercial and industrial (non-explosive, e.g. pipe systems) to trace heating applications

General Specifications

Type	Thermostat
Enclosure Material	ABS with PC Lid

Mechanical Specifications

Dimensions	125mm x 75mm x 125mm
Height	75mm
Length	125mm
Width	125mm
Applications	Heating Systems (pipe heating in industrial applications, Temperature Control Units to provide sophisticated trace heating control)

Operation Environment Specifications

Operating Temperature Range	0°C to 90°C
Minimum Operating Temperature	0°C
Maximum Operating Temperature	90°C

Protection Category

IP Rating

IP66

