



With integrated forged joint axle for very tough, continuous use

| Article No. | EAN<br>4003773- | ↔<br>mm |          | Style | Pliers                | Head     | Handles  | Cutting capacities |      |      |     |
|-------------|-----------------|---------|----------|-------|-----------------------|----------|--|--------------------|------|------|-----|
|             |                 |         |          |       |                       |          |  | Ø mm               | Ø mm | Ø mm | g   |
| 74 01 140   | 039747          | 140     |          |       |                       |          |  | 3.1                | 2.0  | 1.5  | 131 |
| 74 01 160   | 033141          | 160     |          |       |                       |          |  | 3.4                | 2.5  | 2.0  | 178 |
| 74 01 180   | 022008          | 180     | ✂        | 0     | black<br>atramentized | polished | plastic coated   | 3.8                | 2.7  | 2.2  | 241 |
| 74 01 200   | 034056          | 200     |          |       |                       |          |  | 4.2                | 3.0  | 2.5  | 263 |
| 74 01 250   | 034063          | 250     |          |       |                       |          |  | 4.6                | 3.5  | 3.0  | 391 |
| 74 02 140   | 042419          | 140     |          |       |                       |          |  | 3.1                | 2.0  | 1.5  | 157 |
| 74 02 160   | 023081          | 160     | ✂        | 0     | black<br>atramentized | polished | with multi-component grips   | 3.4                | 2.5  | 2.0  | 209 |
| 74 02 180   | 023074          | 180     |          |       |                       |          |  | 3.8                | 2.7  | 2.2  | 273 |
| 74 02 200   | 040309          | 200     |          |       |                       |          |  | 4.2                | 3.0  | 2.5  | 304 |
| 74 02 200 T | 080084          | 200     | ✂        | 0     | black<br>atramentized | polished | with multi-component grips and<br>integrated tether attachment point | 4.2                | 3.0  | 2.5  | 308 |
| 74 02 250   | 042402          | 250     | ✂        | 0     | black atramentized    | polished | with multi-component grips   | 4.6                | 3.5  | 3.0  | 437 |
| 74 02 250 T | 080091          | 250     | ✂        | 0     | black atramentized    | polished | with multi-component grips and<br>integrated tether attachment point | 4.6                | 3.5  | 3.0  | 441 |
| 74 05 140   | 039617          | 140     |          |       |                       |          |  | 3.1                | 2.0  | 1.5  | 157 |
| 74 05 160   | 022961          | 160     |          |       |                       |          |  | 3.4                | 2.5  | 2.0  | 209 |
| 74 05 180   | 022978          | 180     | ✂        | 0     | chrome plated         |          | with multi-component grips   | 3.8                | 2.7  | 2.2  | 270 |
| 74 05 200   | 035367          | 200     |          |       |                       |          |  | 4.2                | 3.0  | 2.5  | 303 |
| 74 05 250   | 039754          | 250     |          |       |                       |          |  | 4.6                | 3.5  | 3.0  | 440 |
| 74 06 160   | 040705          | 160     |          |       |                       |          |  | 3.4                | 2.5  | 2.0  | 215 |
| 74 06 180   | 022985          | 180     | ⚠ 1000 V | 0     | chrome plated         |          | insulated with multi-component<br>grips, VDE-tested                  | 3.8                | 2.7  | 2.2  | 280 |
| 74 06 200   | 033820          | 200     |          |       |                       |          |  | 4.2                | 3.0  | 2.5  | 308 |
| 74 06 250   | 041955          | 250     |          |       |                       |          |  | 4.6                | 3.5  | 3.0  | 453 |
| 74 07 200   | 018414          | 200     | ⚠ 1000 V | 0     | chrome plated         |          | with dipped insulation,<br>VDE-tested                                | 4.2                | 3.0  | 2.5  | 328 |
| 74 07 250   | 018421          | 250     |          |       |                       |          |  | 4.6                | 3.5  | 3.0  | 510 |
| 74 12 160   | 065111          | 160     | ✂        | 1     | black<br>atramentized | polished | with multi-component grips   | 3.4                | 2.5  | 2.0  | 209 |
| 74 12 180   | 060192          | 180     |          |       |                       |          |  | 3.8                | 2.7  | 2.2  | 273 |
| 74 21 180   | 069973          | 180     |          |       |                       |          |  | 3.8                | 2.7  | 2.2  | 235 |
| 74 21 200   | 050483          | 200     | ∠12°     | 2     | black<br>atramentized | polished | plastic coated   | 4.2                | 3.0  | 2.5  | 258 |
| 74 21 250   | 045021          | 250     |          |       |                       |          |  | 4.6                | 3.5  | 3.0  | 390 |
| 74 22 200   | 051831          | 200     |          |       |                       |          | with multi-component grips   | 4.2                | 3.0  | 2.5  | 300 |
| 74 22 200 T | 080107          | 200     | ∠12°     | 2     | black<br>atramentized | polished | with multi-component grips and<br>integrated tether attachment point | 4.2                | 3.0  | 2.5  | 304 |
| 74 22 250   | 071372          | 250     |          |       |                       |          | with multi-component grips   | 4.6                | 3.5  | 3.0  | 437 |
| 74 22 250 T | 080114          | 250     |          |       |                       |          | with multi-component grips and<br>integrated tether attachment point | 4.6                | 3.5  | 3.0  | 441 |

\* Other tools with tethering can be found from page 254 ff