

699 SERIES PANEL INDICATOR LED



FEATURES

- Ø12.7mm (1/2") mounting
- · Black anodised alumimium housing
- Sealed to IP67 weatherproof
- · Coloured diffused lens
- · Internal potting
- Bi-polar circuitry
- · Range of LED colour options
- · Custom voltage options available

BENEFITS

- · Standard industrial mounting size
- Suitable for portable applications
- · Suitable for external applications
- Diffused lens gives wide viewing angle
- Suitable for high vibration applications
- · Suitable for AC or low voltage DC in any orientation
- · Suitable for status panel indication
- Bespoke versions can be developed for your application
- · Outstanding reliability
- · Vandal resistant

| Marl Part Number | LED Colour | Typical Voltage Vopr | Typical Current DC lopr | Typical LED Luminous Intensity | Typical LED Wavelength λρ | Operating Temp Topr * | Storage Temp Tstg |
|---------------------|------------|-------------------------|----------------------------|--------------------------------------|---------------------------------|-----------------------------|-------------------------|
| 699-501-63 | Red | 12-28 Vac/dc | 6-16 | 236 @ 10mA | 625 | -40 to +75 | -40 to +100 |
| 699-521-63 | Yellow | 12-28 Vac/dc | 6-16 | 217 @ 10mA | 590 | -40 to +75 | -40 to +100 |
| 699-532-63 | Green | 12-28 Vac/dc | 6-16 | 1360 @ 10mA | 520 | -40 to +75 | -40 to +100 |
| 699-930-63 | Blue | 12-28 Vac/dc | 6-16 | 270 @ 10mA | 470 | -40 to +75 | -40 to +100 |
| 699-997-63 | Cool White | 12-28 Vac/dc | 6-16 | 743 @ 10mA | See Below | -40 to +75 | -40 to +100 |
| 699-501-75 | Red | 110 Vac | 7 | 112 | 625 | -40 to +75 | -40 to +100 |
| 699-521-75 | Yellow | 110 Vac | 7 | 103 | 590 | -40 to +75 | -40 to +100 |
| 699-532-75 | Green | 110 Vac | 7 | 814 | 520 | -40 to +75 | -40 to +100 |
| 699-930-75 | Blue | 110 Vac | 7 | 154 | 470 | -40 to +75 | -40 to +100 |
| 699-997-75 | Cool White | 110 Vac | 7 | 393 | See Below | -40 to +75 | -40 to +100 |
| | | Bi-polar | mA | mcd | nm | °C | °C |

| Typical Emission Colours Cool White LED | | | | | | |
|---|-------|------|------|--|--|--|
| Χ | 0.275 | 0.28 | 0.29 | | | |
| Υ | 0.27 | 0.28 | 0.30 | | | |

NOTES

Intensities (Iv) and colour shades of white (X-Y co-ordinates) may vary between LEDs within a batch. Additional LED Colours, Voltage Options and Flying Lead lengths available for semicustom projects. Please contact our Sales Team. All LED components are supplied in anti-static packaging.

* For operating temperature derating graphs, please refer to sheet 2.











699 SERIES PANEL INDICATOR LED


TECHNICAL CHARACTERISTICS


| Series | Max. Power Dissipation | Panel Cutout | Nut Mounting Torque | Min. Mounting Centres | Min Max. Panel Thickness |
|--------|---------------------------|--------------|------------------------|--------------------------|-----------------------------|
| 699 | 825 | 12.7 | 1.0 | 26.0 | 2.0 - 10.0 |
| | mW | mm | Nm | mm | mm |

TECHNICAL DRAWING


Weight (g): 12.6

Dimensions in mm (typical). Not to scale. Mounting hole to be clean and burr free.







PUSH ON CONNECTOR



925-000-00 is brass tin plated - for use with 699 series lamps. Dimensions in mm (typical). Not to scale.

DE-RATING GRAPHS





MATERIALS

Body Black Anodised Aluminium Grade 6063

Nut Stainless Steel Grade 303

Panel Seal Viton Lens Polycarbonate Encapsulation Black Polyurethane Lock Washer Zinc Plated Steel Silver Flash Coated Brass Termination Header Nylon 66 A82

DESIGN CONSIDERATIONS

Electro-Static Discharge (ESD)

Build up of electro-static discharge occurs in many situations involving people moving and handling products. The range of possible situations is very diverse but voltage levels as high as several thousand volts can and do arise in many individual situations. When an operator charged up to these levels handles a static sensitive device, there is a very probable likelihood that the device will be irreversibly damaged. It is essential that precautions are taken at all stages during manufacture and assembly of these products. Although LEDs were never considered to be static sensitive

devices, changes in manufacturing technology and materials used to produce higher intensity products over a large range of the wavelength spectrum have changed this. Marl has an approved system of ESD control from goods in, through production and into final packing and despatch. Marl recommend all users of LED based products follow the guidelines of BS 100015.

Voltage, Current and Temperature

The forward voltage / current value of an LED is dependent upon the ambient temperature of the environment in which it is operated. Therefore, care must be taken to operate the LED at the correct voltage / current values, depending upon the ambient temperature.

Marl should be contacted if the device is to be operated outside the temperature range specified. Marl accept no liability for any product that is operated outside the stated voltage or temperature range.





