

SITOP PSU100S 12 V/14 A
 SITOP PSU100S 12 V/14 A Stabilized power supply input: 120/230 V
 AC, output: 12 V DC/14 A



Input	
Input	1-phase AC
Supply voltage	
<ul style="list-style-type: none"> • 1 at AC Rated value • 2 at AC Rated value • Note 	120 V 230 V Automatic range selection
Input voltage	
<ul style="list-style-type: none"> • 1 at AC • 2 at AC 	85 ... 132 V 170 ... 264 V
Wide-range input	No
Oversoltage resistance	2.3 × Vin rated, 1.3 ms
Mains buffering at Iout rated, min.	20 ms; at Vin = 93/187 V
Rated line frequency 1	50 Hz
Rated line frequency 2	60 Hz
Rated line range	47 ... 63 Hz
Input current	
<ul style="list-style-type: none"> • at rated input voltage 120 V • at rated input voltage 230 V 	3.24 A 1.41 A
Switch-on current limiting (+25 °C), max.	60 A

Built-in incoming fuse	T 6.3 A/250 V (not accessible)
Protection in the mains power input (IEC 898)	Recommended miniature circuit breaker: from 10 A characteristic C

Output

Output	Controlled, isolated DC voltage
Rated voltage Vout DC	12 V
Total tolerance, static ±	3 %
Static mains compensation, approx.	0.1 %
Static load balancing, approx.	1 %
Residual ripple peak-peak, max.	150 mV
Residual ripple peak-peak, typ.	20 mV
Spikes peak-peak, max. (bandwidth: 20 MHz)	240 mV
Spikes peak-peak, typ. (bandwidth: 20 MHz)	100 mV
Adjustment range	11.5 ... 15.5 V
Product function Output voltage adjustable	Yes
Output voltage setting	via potentiometer
Status display	Green LED for 12 V OK
Signaling	Relay contact (NO contact, rating 60 V DC/ 0.3 A) for 12 V OK
On/off behavior	Overshoot of Vout < 3 %
Startup delay, max.	0.3 s
Voltage rise, typ.	10 ms
Rated current value Iout rated	14 A
Current range	0 ... 14 A
• Note	+50 ... +70 °C: Derating 3.5%/K
Supplied active power typical	168 W
Short-term overload current	
• on short-circuiting during the start-up typical	40 A
• at short-circuit during operation typical	40 A
Duration of overloading capability for excess current	
• on short-circuiting during the start-up	800 ms
• at short-circuit during operation	800 ms
Parallel switching for enhanced performance	Yes
Numbers of parallel switchable units for enhanced performance	2

Efficiency

Efficiency at Vout rated, Iout rated, approx.	87 %
Power loss at Vout rated, Iout rated, approx.	24 W

Closed-loop control

Dynamic load smoothing (Iout: 10/90/10 %), Uout ± typ.	5 %
Load step setting time 10 to 90%, typ.	1 ms
Load step setting time 90 to 10%, typ.	1 ms

Protection and monitoring	
Output overvoltage protection	< 20 V
Current limitation	14 ... 16.4 A
Property of the output Short-circuit proof	Yes
Short-circuit protection	Constant current characteristic
Enduring short circuit current RMS value <ul style="list-style-type: none"> • typical 	16.4 A
Overcurrent overload capability in normal operation	overload capability 150 % I _{out} rated up to 5 s/min
Overload/short-circuit indicator	-

Safety	
Primary/secondary isolation	Yes
Galvanic isolation	Safety extra-low output voltage U _{out} acc. to EN 60950-1 and EN 50178
Protection class	Class I
Leakage current <ul style="list-style-type: none"> • maximum • typical 	3.5 mA 0.8 mA
CE mark	Yes
UL/cUL (CSA) approval	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259; cCSAus (CSA C22.2 No. 60950-1, UL 60950-1)
Explosion protection	IECEx Ex nA nC IIC T4 Gc; ATEX (EX) II 3G Ex nA nC IIC T4 Gc; cULus Class I Div. 2 (ANSI/ISA-12.12.01-2007, CSA C22.2 No. 213) Group ABCD, T4; cCSAus (CSA C22.2 No. 213, ANSI/ISA-12.12.01) Class I, Div. 2, Group ABCD, T4
FM approval	-
CB approval	Yes
Marine approval	DNV GL
Degree of protection (EN 60529)	IP20

EMC	
Emitted interference	EN 55022 Class B
Supply harmonics limitation	EN 61000-3-2
Noise immunity	EN 61000-6-2

Operating data	
Ambient temperature <ul style="list-style-type: none"> • during operation — Note • during transport • during storage 	-25 ... +70 °C with natural convection -40 ... +85 °C -40 ... +85 °C
Humidity class according to EN 60721	Climate class 3K3, no condensation

Mechanics	
Connection technology	screw-type terminals
Connections	

<ul style="list-style-type: none"> • Supply input 	L, N, PE: 1 screw terminal each for 0.5 ... 2.5 mm ² single-core/finely stranded
<ul style="list-style-type: none"> • Output 	+ , - : 2 screw terminals each for 0.5 ... 2.5 mm ²
<ul style="list-style-type: none"> • Auxiliary 	Alarm signals: 2 screw terminals for 0.5 ... 2.5 mm ²
Connections signaling contact	2 screw terminals for 0.5 ... 2.5 mm ²
Width of the enclosure	70 mm
Height of the enclosure	125 mm
Depth of the enclosure	120 mm
Required spacing	
<ul style="list-style-type: none"> • top 	50 mm
<ul style="list-style-type: none"> • bottom 	50 mm
<ul style="list-style-type: none"> • left 	0 mm
<ul style="list-style-type: none"> • right 	0 mm
Weight, approx.	0.7 kg
Product feature of the enclosure housing for side-by-side mounting	Yes
Installation	Snaps onto DIN rail EN 60715 35x7.5/15
MTBF at 40 °C	1 614 510 h
Other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)