

SITOP PSU300B 24 V/30 A  
 SITOP PSU300B 30 A Stabilized power supply input: 3 AC 400-500 V output: 24 V DC/30 A



Input	
Input	3-phase AC
Rated voltage value $V_{in}$ rated	400 ... 500 V
Voltage range AC	320 ... 575 V
Wide-range input	Yes
Mains buffering at $I_{out}$ rated, min.	20 ms; at $V_{in} = 400$ V
Rated line frequency 1	50 Hz
Rated line frequency 2	60 Hz
Rated line range	47 ... 63 Hz
Input current	
• at rated input voltage 400 V	1.6 A
• at rated input voltage 500 V	1.3 A
Switch-on current limiting (+25 °C), max.	56 A
$I^2t$ , max.	2.24 A <sup>2</sup> ·s
Built-in incoming fuse	none
Protection in the mains power input (IEC 898)	Required: 3-pole connected miniature circuit breaker 10 ... 16 A characteristic C or circuit breaker 3RV2011-1DA10 (setting 3 A) or 3RV2711-1DD10 (UL 489)

### Output

Output	Controlled, isolated DC voltage
Rated voltage $V_{out}$ DC	24 V
Total tolerance, static $\pm$	3 %
Static mains compensation, approx.	0.1 %
Static load balancing, approx.	0.1 %
Residual ripple peak-peak, max.	100 mV
Spikes peak-peak, max. (bandwidth: 20 MHz)	200 mV
Adjustment range	24 ... 28.8 V
Product function Output voltage adjustable	Yes
Output voltage setting	via potentiometer
Status display	Green LED for 24 V OK
Signaling	Relay contact (NO contact, rating 60 V DC/ 0.3 A) for "24 V OK"
On/off behavior	No overshoot of $V_{out}$ (soft start)
Startup delay, max.	2.5 s
Voltage increase time of the output voltage maximum	500 ms
Rated current value $I_{out}$ rated	30 A
Current range	0 ... 30 A
• Note	+60 ... +70 °C: Derating 1.7%/K
Supplied active power typical	960 W
Constant overload current	
• on short-circuiting during the start-up typical	32 A
• at short-circuit during operation typical	32 A
Parallel switching for enhanced performance	Yes; switchable characteristic
Numbers of parallel switchable units for enhanced performance	2

### Efficiency

Efficiency at $V_{out}$ rated, $I_{out}$ rated, approx.	93 %
Power loss at $V_{out}$ rated, $I_{out}$ rated, approx.	50 W

### Closed-loop control

Dynamic mains compensation ( $V_{in}$ rated $\pm 15$ %), max.	1 %
Dynamic load smoothing ( $I_{out}$ : 50/100/50 %), $U_{out}$ $\pm$ typ.	3 %
Setting time maximum	10 ms

### Protection and monitoring

Output overvoltage protection	< 35 V
Current limitation, typ.	32 A
Property of the output Short-circuit proof	Yes
Short-circuit protection	Alternatively, constant current characteristic approx. 32 A or latching shutdown
Enduring short circuit current RMS value	
• typical	32 A
Overload/short-circuit indicator	LED yellow for "overload", LED red for "latching shutdown"

Safety	
Primary/secondary isolation	Yes
Galvanic isolation	Safety extra-low output voltage U <sub>out</sub> acc. to EN 60950-1 and EN 50178
Protection class	Class I
Leakage current <ul style="list-style-type: none"> <li>• maximum</li> </ul>	3.5 mA
CE mark	Yes
UL/cUL (CSA) approval	cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259
Explosion protection	-
FM approval	-
CB approval	No
Marine approval	-
Degree of protection (EN 60529)	IP20

EMC	
Emitted interference	EN 55022 Class B
Supply harmonics limitation	EN 61000-3-2
Noise immunity	EN 61000-6-2

Operating data	
Ambient temperature <ul style="list-style-type: none"> <li>• during operation</li> <li>— Note</li> <li>• during transport</li> <li>• during storage</li> </ul>	-25 ... +70 °C with natural convection -40 ... +85 °C -40 ... +85 °C
Humidity class according to EN 60721	Climate class 3K3, no condensation

Mechanics	
Connection technology	screw-type terminals
Connections <ul style="list-style-type: none"> <li>• Supply input</li> <li>• Output</li> <li>• Auxiliary</li> </ul>	L1, L2, L3, PE: 1 screw terminal each for 0.2 ... 4 mm <sup>2</sup> single-core/finely stranded +, -: 2 screw terminals each for 0.33 ... 10 mm <sup>2</sup> 13, 14 (alarm signal): 1 screw terminal each for 0.14 ... 1.5 mm <sup>2</sup>
Width of the enclosure	150 mm
Height of the enclosure	125 mm
Depth of the enclosure	150 mm
Required spacing <ul style="list-style-type: none"> <li>• top</li> <li>• bottom</li> <li>• left</li> <li>• right</li> </ul>	50 mm 50 mm 0 mm 0 mm
Weight, approx.	3.4 kg

Product feature of the enclosure housing for side-by-side mounting	Yes
Installation	Snaps onto DIN rail EN 60715 35x15
Electrical accessories	Buffer module
Mechanical accessories	Device identification label 20 mm × 7 mm, TI-grey 3RT2900-1SB20
MTBF at 40 °C	885 739 h
Other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)