


Electronics Diagonal Cutters

ISO 9654



77 01 115



- for fine cutting work, e.g. in electronics and fine mechanics
- sturdy, zero-backlash box joint
- low-friction double spring for gentle and even opening
- the polish or mirror polish (only finish 2) together with a fine film of oil, offers effective rust protection – no circuit faults caused by peeling chrome from plated tools
- cutting edge hardness approx. 62 HRC
- High-grade special tool steel; forged, oil-hardened

77 01 115

round head, with bevel

77 02 115

round head, with small bevel

77 11 115

round head, with bevel and lead catcher – no uncontrolled loss of cut wire ends

77 21 115

pointed head, without bevel

77 22 115

round head, without bevel; cutting edge hardness approx. 57 HRC

77 32 115

pointed head, with small bevel

77 42 115


pointed head, without bevel; cutting edge hardness approx. 57 HRC

77 52 115

pointed, flat head, with small bevel; cutting edge hardness approx. 57 HRC

77 72 115

miniature head with small bevel




77 02 115



77 12 115




77 22 115



77 42 115



77 52 115



77 72 115

