




## **Electronics Diagonal Cutters**













- for fine cutting work, e.g. in electronics and fine mechanics
- sturdy, zero-backlash box joint
- low-friction double spring for gentle and even opening
- the polish or mirror polish (only finish 2) together with a fine film of oil, offers effective rust protection – no circuit faults caused by peeling chrome from plated tools
- cutting edge hardness approx. 62 HRC
- High-grade special tool steel; forged, oil-hardened

77 01 115 round head, with bevel

77 02 115 round head, with small bevel

77 11 115 round head, with bevel and lead catcher – no uncontrolled loss of cut wire ends

77 21 115 pointed head, without bevel

**77 22 115** round head, without bevel; cutting edge hardness approx. 57 HRC

77 32 115 pointed head, with small bevel

**77 42 115** pointed head, without bevel; cutting edge hardness approx. 57 HRC

**77 52 115** pointed, flat head, with small bevel; cutting edge hardness approx. 57 HRC

77 72 115 miniature head with small bevel



