

SIMATIC ET 200SP, Digital input module, DI 16x 24V DC Standard, type 3 (IEC 61131), sink input, (PNP, P-reading), Packing unit: 1 Piece, fits to BU-type A0, Colour Code CC00, input delay time 0,05..20ms, diagnostics wire break, diagnostics supply voltage



General information	
Product type designation	DI 16x24 VDC ST
Firmware version	V0.0
<ul style="list-style-type: none"> FW update possible 	No
usable BaseUnits	BU type A0
Color code for module-specific color identification plate	CC00
Product function	
<ul style="list-style-type: none"> I&M data 	Yes; I&M0 to I&M3
Engineering with	
<ul style="list-style-type: none"> STEP 7 TIA Portal configurable/integrated as of version 	V14
<ul style="list-style-type: none"> STEP 7 configurable/integrated as of version 	V5.5 SP3
<ul style="list-style-type: none"> PCS 7 configurable/integrated as of version 	V8.1 SP1
<ul style="list-style-type: none"> PROFIBUS as of GSD version/GSD revision 	One GSD file each, Revision 3 and 5 and higher
<ul style="list-style-type: none"> PROFINET as of GSD version/GSD revision 	GSDML V2.3
Operating mode	
<ul style="list-style-type: none"> DI 	Yes
<ul style="list-style-type: none"> Counter 	No

<ul style="list-style-type: none"> • Oversampling 	No
<ul style="list-style-type: none"> • MSI 	No
Supply voltage	
Rated value (DC)	24 V
permissible range, lower limit (DC)	19.2 V
permissible range, upper limit (DC)	28.8 V
Reverse polarity protection	Yes
Input current	
Current consumption, max.	90 mA
Encoder supply	
24 V encoder supply	
<ul style="list-style-type: none"> • 24 V 	No
Power loss	
Power loss, typ.	1.7 W
Address area	
Address space per module	
<ul style="list-style-type: none"> • Inputs 	2 byte; + 2 bytes for QI information
Hardware configuration	
Automatic encoding	Yes
<ul style="list-style-type: none"> • Mechanical coding element 	Yes
Submodules	
<ul style="list-style-type: none"> • Number of configurable submodules, max. 	4
Selection of BaseUnit for connection variants	
<ul style="list-style-type: none"> • 1-wire connection 	BU type A0
<ul style="list-style-type: none"> • 2-wire connection 	BU type A0 + Potential isolation module
<ul style="list-style-type: none"> • 3-wire connection 	BU type A0 + Potential isolation module
<ul style="list-style-type: none"> • 4-wire connection 	BU type A0 + Potential isolation module
Digital inputs	
Number of digital inputs	16
Digital inputs, parameterizable	Yes
Source/sink input	P-reading
Input characteristic curve in accordance with IEC 61131, type 3	Yes
Input voltage	
<ul style="list-style-type: none"> • Type of input voltage 	DC
<ul style="list-style-type: none"> • Rated value (DC) 	24 V
<ul style="list-style-type: none"> • for signal "0" 	-30 to +5V
<ul style="list-style-type: none"> • for signal "1" 	+11 to +30V
Input current	
<ul style="list-style-type: none"> • for signal "1", typ. 	2.5 mA

Input delay (for rated value of input voltage)	
for standard inputs	
— parameterizable	Yes; 0.05 / 0.1 / 0.4 / 0.8 / 1.6 / 3.2 / 12.8 / 20 ms (in each case + delay of 30 to 500 µs, depending on line length)
— at "0" to "1", min.	0.05 ms
— at "0" to "1", max.	20 ms
— at "1" to "0", min.	0.05 ms
— at "1" to "0", max.	20 ms
Cable length	
• shielded, max.	1 000 m
• unshielded, max.	600 m
Encoder	
Connectable encoders	
• 2-wire sensor	Yes
— permissible quiescent current (2-wire sensor), max.	1.5 mA
Isochronous mode	
Isochronous operation (application synchronized up to terminal)	No
Interrupts/diagnostics/status information	
Diagnostics function	Yes
Alarms	
• Diagnostic alarm	Yes
Diagnostic messages	
• Diagnostic information readable	Yes
• Monitoring the supply voltage	Yes
— parameterizable	Yes
• Monitoring of encoder power supply	No
• Wire-break	Yes; Module-by-module, optional protective circuit for preventing wire-break diagnostics in the case of simple encoder contacts: 25 kOhm to 45 kOhm
• Short-circuit	No
• Group error	Yes
Diagnostics indication LED	
• Monitoring of the supply voltage (PWR-LED)	Yes; green PWR LED
• Channel status display	Yes; Green LED
• for channel diagnostics	No
• for module diagnostics	Yes; green/red DIAG LED
Potential separation	
Potential separation channels	
• between the channels	No

- between the channels and backplane bus
- between the channels and the power supply of the electronics

Yes

No

Isolation

Isolation tested with 707 V DC (type test)

Ambient conditions

Ambient temperature during operation

- horizontal installation, min. 0 °C
- horizontal installation, max. 60 °C
- vertical installation, min. 0 °C
- vertical installation, max. 50 °C

Altitude during operation relating to sea level

- Ambient air temperature-barometric pressure-altitude On request: Ambient temperatures lower than 0 °C (without condensation) and/or installation altitudes greater than 2 000 m

Dimensions

Width 15 mm

Height 73 mm

Depth 58 mm

Weights

Weight, approx. 28 g

last modified: 07/25/2018