SIEMENS

Data sheet

6ES7141-5AF00-0BA0

SIMATIC ET 200AL, DI 8x 24 V DC, 4x M12, Degree of protection IP67



General information	
Product type designation	DI 8x24VDC
HW functional status	FS03
Firmware version	V1.0.x
Product function	
● I&M data	Yes; I&M0 to I&M3
Engineering with	
 STEP 7 TIA Portal configurable/integrated as of version 	STEP 7 V13 SP1 or higher
 STEP 7 configurable/integrated as of version 	V5.5 SP4 Hotfix 7 or higher
 PROFIBUS as of GSD version/GSD revision 	GSD as of Revision 5
 PROFINET as of GSD version/GSD revision 	GSDML V2.3.1

Supply voltage

Load voltage 1L+

• Rated value (DC)	24 V
• permissible range, lower limit (DC)	20.4 V
 permissible range, upper limit (DC) 	28.8 \

Reverse polarity protection	Yes; Against destruction; encoder power supply outputs applied with reversed polarity
Input current	
Current consumption (rated value)	25 mA; without load
from load voltage 1L+ (unswitched voltage)	4 A; Maximum value
from load voltage 2L+, max.	4 A; Maximum value
Encoder supply	
Number of outputs	4
24 V encoder supply	
Short-circuit protection	Yes; per module, electronic
Output current, max.	0.7 A; Total current of all encoders
Device less	
Power loss Power loss, typ.	1.9 W
1 6wc1 1655, typ.	1.0 VV
Digital inputs	
Number of digital inputs	8
Input characteristic curve in accordance with IEC 61131, type 3	Yes
Number of simultaneously controllable inputs	
all mounting positions	
— up to 55 °C, max.	8
Input voltage	
Rated value (DC)	24 V
• for signal "0"	-30 to +5 V
• for signal "1"	+11 to +30V
Input current	
• for signal "1", typ.	3.2 mA
Input delay (for rated value of input voltage)	
for standard inputs	
— at "0" to "1", min.	1.2 ms
— at "0" to "1", max.	4.8 ms
— at "1" to "0", min.	1.2 ms
— at "1" to "0", max.	4.8 ms
Cable length	
• unshielded, max.	30 m
Encoder	
Connectable encoders	
• 2-wire sensor	Yes
 permissible quiescent current (2-wire sensor), max. 	1.5 mA
Interrupts/diagnostics/status information	

Alarms		
Diagnostic alarm	Yes; Parameterizable	
Diagnostic messages		
Short-circuit	Yes; Sensor supply to M; module by module	
Diagnostics indication LED		
Channel status display	Yes; green LED	
• for module diagnostics	Yes; green/red LED	
Potential separation		
between the load voltages	Yes	
Potential separation channels		
between the channels	No	
	Yes	
between the channels and backplane bus		
 between the channels and the power supply of the electronics 	No	
the electronics		
Isolation		
Isolation tested with	707 V DC (type test)	
Degree and class of protection		
IP degree of protection	IP65/67	
Standards, approvals, certificates	Vaca France FC04	
Suitable for safety-related tripping of standard modules	Yes; From FS01	
Highest safety class achievable for safety-related tripping	ng of standard modules	
Performance level according to ISO 13849-1	PL d	
Category according to ISO 13849-1	Cat. 3	
• SILCL according to IEC 62061	SILCL 2	
GILGE according to ILC 02001	CILOL 2	
Ambient conditions		
Ambient temperature during operation		
• min.	-30 °C	
• max.	55 °C	
Connection method		
Design of electrical connection for the inputs and	M12, 5-pole	
outputs		
Design of electrical connection for supply voltage	M8, 4-pole	
ET-Connection		
ET-Connection	M8, 4-pin, shielded	
Dimensions		
Width	30 mm	
Height	159 mm	
Depth	40 mm	
Weights		

Weight, approx.	145 g

02/04/2020 last modified: