
Thomas & Betts





The Ty-Rap® detectable cable ties and accessories from Thomas & Betts incorporate a unique patented compound that can be detected by X-Ray equipment, metal detectors and visual inspection equipment.

Those products are particularly recommended for applications in food, pharmaceutical and other contamination-sensitive industries using detection systems, where cable tie installation residuals (cut tails) and/or accessories are not allowed in the finished product.

By specifying the Ty-Rap® detectable cable ties and accessories of Thomas & Betts for your plant you help reducing the risk of product contamination.

Another great aspect of the detectable products of Thomas & Betts: they help your business achieve a great step towards meeting the HACCP* EU-directive. The HACCP directive is a systematic preventative approach to food safety that addresses physical, chemical and biological hazards as a means of prevention rather than finished product inspection.

The Ty-Rap® detectable cable ties and accessories made of detectable Nylon (NDT) and Polypropylene (PDT) are compliant to the FDA regulation, which means the products are intended for use in the proximity of food processing, handling and packaging operations.

- HACCP= Hazard Analysis Critical Control Points
- HACCP is a system, which identifies specific hazards and preventative measures for their control to minimize the risk of producing defective products and services.

Main applications for detectable products:

- Food and beverage processing
- Pharmaceutical production
- Chemical and compounds manufacturing
- Tire and airbag manufacturing
- Any other contamination-sensitive industry using detection equipment

Detection methods

Metal Detection

Ty-Rap® Detectable Cable Ties have been tested and are rated at 1.5 mm diameter ferrous sphere setting. Therefore sensitive enough to be picked up by nearly every metal detector in service.

X-Ray Detection

X-Rays are the future of the detection industry. Depending on the density of the product being verified, Ty-Rap® Detectable Cable Ties reach an impressive differential of between 200 and 2000 on the X-Ray grey scale.

Visual Detection

Visual detection systems detect surface irregularities and volume changes. This method is often used in beverage and chemical processing plants. The bright blue colour ensures an easy visual detection.

Features

- Detectable by metal detectors set at minimum 1.5 mm diameter ferrous sphere*
- Detectable by X-Ray equipment**
- Bright blue colour for an easy visual detection
- Help achieve the HACCP EU-Directive, compliant to the FDA regulation
- Halogen free
- Available in standard Polyamide 6.6 (all references ending with NDT) or in buoyant Polypropylene (all references ending with PDT) version for liquid-processing applications
- All the advantages of the standard Ty-Rap® cable ties as "The Grip of Steel" locking device which offers superior performance
- Available in 5 different sizes in convenient small bags with Euroslot
- * Tested by Thermo Electron Corporation, Minneapolis, MN, USA
- ** Tested by Smiths Detection, Alcoa, TN, USA

Ty-Rap® Detectable Cable Ties

Product ref.	Length [mm]	Width [mm]	Bundle Dia. FromTo [mm]	Minimum Tensile Strength [N]	Quantity [pieces]	Tooling
TY523M-NDT	92	2.4	2 - 16	80	100	ERG50
TY524M-NDT	140	3.6	2 - 29	180	100	ERG50
TY525M-NDT	186	4.8	3.5 - 45	220	100	ERG50 / ERG120
TY528M-NDT	360	4.8	3.5 - 102	220	100	ERG50 / ERG120
TY527M-NDT	340	7.0	6 - 90	540	50	ERG120
TY523M-PDT	92	2.4	2-16	50	100	ERG50
TY525M-PDT	186	4.8	3.5-45	130	100	ERG50
TY528M-PDT	360	4.8	3.5-102	130	100	ERG50
TY527M-PDT	340	7.0	6-90	270	50	ERG120

2-way and 4-way entry mounting bases



Product ref.	Mounting method	Width	Length	For tie width up to	Mounting hole (2x)	Quantity
		[mm]	[mm]	[mm]	[mm]	[pieces]
TC5344A-NDT	self-adhesive*/screw	19,1	19,1	3,6	3	100
TC5344A-PDT	self-adhesive*/screw	19,1	19,1	3,6	3	100
TC344A-NDT	self-adhesive*/screw	19,1	19,1	3,6	3	1000
TC5347A-NDT	self-adhesive*/screw	29	29	7,6	4,4	100
TC5347A-PDT	self-adhesive*/screw	29	29	7,6	4,4	100
TC347A-NDT	self-adhesive*/screw	29	29	7,6	4,4	1000

Saddle support




Product ref.	Mounting method	Width	Length	For tie width up to	Mounting hole diameter	Quantity
		[mm]	[mm]	[mm]	[mm]	[pieces]
TC5141-NDT	screw	11,1	17	4,8	3,8	100
TC5141-PDT	screw	11,1	17	4,8	3,8	100
TC141-NDT	screw	11,1	17	4,8	3,8	500
TC5142-NDT	screw	14,2	23,4	7,6	5,2	100
TC5142-PDT	screw	14,2	23,4	7,6	5,2	100
TC142-NDT	screw	14,2	23,4	7,6	5,2	500

Srew-mounted miniature bases



Product ref.	Mounting method	Width [mm]	Length [mm]	For tie width up to [mm]	Mounti diameter D1 [mm]	ng hole diameter D2 [mm]	Quantity [pieces]
TC5102-NDT	screw	12,7	19,1	4,8	4,4	8,7	100
TC102-NDT	screw	12,7	19,1	4,8	4,4	8,7	1000
TC102-PDT	screw	12,7	19,1	4,8	4,4	8,7	1000

Low profile plates



Product ref.	Mounting method	Width	Length	For tie width up to	Quantity
		[mm]	[mm]	[mm]	[pieces]
TC5342A-NDT	self-adhesive*	29	29	4,8	100
TC5342A-PDT	self-adhesive*	29	29	4,8	100
TC342A-NDT	self-adhesive*	29	29	4,8	1000

^{*} Surface preparation: surface should be cleaned with alcohol-based cleaner before application. Installation: Surface must be clean and dry prior to application of accessory.

Allow 15-minute setting time for maximum adhesion performance of synthetic rubber adhesive (SRA).



Thomas & Betts

www.tnb-europe.com

EUROPEAN HEADQUARTERS

Thomas & Betts 200 Chaussée de Waterloo B-1640 Rhode-St-Genèse Belgium

Tel: +32 (0) 2 359 82 00 Fax: +32 (0) 2 359 82 01

EUROPEAN Customer Service

Boulevard du Millenium 8 B-7110 Houdeng-Goegnies Belgium Tel: +32 (0) 64 88 63 88

Tel: +32 (0) 64 88 63 88 Fax: +32 (0) 64 88 65 50

UNITED KINGDOM

Wilford Road Nottingham NG2 1EB United Kingdom Tel: +44 (0)115 964 3700 Fax: +44 (0)115 986 0538

GERMANY / EAST EUROPE / NORDIC

Lindberghstrasse 5 D-64625 Bensheim Deutschland Tel: +49 (0) 6251 669 0 Fax: +49 (0) 6251 669 155 Customer Service Tel: +49 (0) 6251 669 199/165/132 Fax: +49 (0) 6251 669 176

AUSTRIA / SWITZERLAND

Aathalstrasse 90 CH-8610 Uster Switzerland Phone: +41 44 905 61 04 Fax: +41 44 905 61 22

BENELUX

Oosteinde 3 Postbus 32 2990 AA Barendrecht Netherlands

Phone: +31 (0180) 641 888 Fax: +31 (0180) 641 889

FRANCE

ZI Parc d'Activités de la Gare 19/21 Av. Henri Beaudelet BP 27 - 77831 OZOIR Cedex France

Tel: +33 (0) 1 64 40 49 93 Fax: +33 (0) 1 64 40 20 11

ITALY

Via Paracelso 26 Centro Colleoni I-20864 Agrate Brianza - Monza Brianza Italia Tel: +39 039 657 90 28/22/34 Fax: +39 039 657 90 77

Servizio Clientela Tel: +39 039 657 90 32 Fax: +39 039 657 90 80

MIDDLE EAST

Office 107 5EA East Wing Dubai Airport Free Zone PO Box 54567 Dubai United Arab Emirates Tel: +9714 609 1635 Fax: +9714 609 1636

SPAIN

Pol.Ind. Cardedeu Sud · Avda. Vallés, 22 08440 Cardedeu (Barcelona) Tel: +34 / 938 45 45 70 Fax: +34 / 938 45 47 80

The content of the Thomas & Betts price list has been carefully checked for accuracy at the time of print. However, Thomas & Betts doesn't give any warranty of any kind, express or implied, in this respect and shall not be liable for any loss or damage that may result from any use or as a consequence of any inaccuracies in or any omissions from the information which it may contain.

Copyright Thomas & Betts 2013. Ćopyright in these pages is owned by Thomas & Betts except where otherwise indicated. No part of this publication may be reproduced, copied or transmitted in any form or by any means, without our prior written permission. Images, trade marks, brands, designs and technology are also protected by other intellectual property rights and may not be reproduced or appropriated in any manner without written permission of their respective owners. Thomas & Betts reserves the right to change and improve any product specifications or other mentions in the catalogue at its own discretion and at any time. These conditions of use are governed by the laws of the Netherlands and the courts of Amsterdam shall have exclusive jurisdiction in any dispute.