

SIMATIC DP, ET 200ECO PN, 8 DI 24 V DC; 8xM12, Degree of protection IP67



Figure similar

General information	
Vendor identification (VendorID)	002AH
Device identifier (DeviceID)	0306H
Supply voltage	
Rated value (DC)	24 V
Reverse polarity protection	Yes
Input current	
Current consumption, typ.	100 mA
Encoder supply	
Number of outputs	8
24 V encoder supply	
<ul style="list-style-type: none"> Short-circuit protection 	Yes; Electronic
<ul style="list-style-type: none"> Output current, max. 	100 mA; per output
Power loss	
Power loss, typ.	4.5 W

Digital inputs	
Number of digital inputs	8
<ul style="list-style-type: none"> • in groups of 	1
Input characteristic curve in accordance with IEC 61131, type 3	Yes
Number of simultaneously controllable inputs	
all mounting positions	
— up to 60 °C, max.	8
Input voltage	
<ul style="list-style-type: none"> • Rated value (DC) 	24 V
<ul style="list-style-type: none"> • for signal "0" 	-3 to +5V
<ul style="list-style-type: none"> • for signal "1" 	+11 to +30V
Input current	
<ul style="list-style-type: none"> • for signal "1", typ. 	7 mA
Input delay (for rated value of input voltage)	
for standard inputs	
— at "0" to "1", max.	typically 3 ms
— at "1" to "0", max.	typically 3 ms
Cable length	
<ul style="list-style-type: none"> • unshielded, max. 	30 m
Encoder	
Connectable encoders	
<ul style="list-style-type: none"> • 2-wire sensor 	Yes
— permissible quiescent current (2-wire sensor), max.	1.5 mA
Interfaces	
Transmission procedure	100BASE-TX
Number of PROFINET interfaces	1
1. Interface	
Interface types	
<ul style="list-style-type: none"> • integrated switch 	Yes
<ul style="list-style-type: none"> • M12 port 	Yes
Interface types	
M12 port	
<ul style="list-style-type: none"> • Autonegotiation 	Yes
<ul style="list-style-type: none"> • Autocrossing 	Yes
<ul style="list-style-type: none"> • Transmission rate, max. 	100 Mbit/s
Protocols	
Supports protocol for PROFINET IO	Yes
PROFINET CBA	No

PROFIsafe	No
PROFINET IO Device	
Services	
— IRT with the option "high flexibility"	Yes
— Prioritized startup	Yes
Redundancy mode	
Media redundancy	
— MRP	Yes
Open IE communication	
• TCP/IP	No
• SNMP	Yes
• DCP	Yes
• LLDP	Yes
• ping	Yes
• ARP	Yes
Interrupts/diagnostics/status information	
Diagnostics function	Yes
Alarms	
• Diagnostic alarm	Yes
Diagnostic messages	
• Diagnostic information readable	Yes
• Monitoring the supply voltage	Yes; green "ON" LED
• Wire-break in signal transmitter cable	Yes
• Short-circuit encoder supply	Yes; Per channel group
• Group error	Yes; Red/yellow "SF/MT" LED
Potential separation	
between the load voltages	Yes
between load voltage and all other switching components	No
between Ethernet and electronics	Yes
Potential separation channels	
• between the channels	No
Isolation	
tested with	
• 24 V DC circuits	707 V DC (type test)
• Test voltage for interface, rms value [Vrms]	1 500 V; According to IEEE 802.3
Degree and class of protection	
IP degree of protection	IP67
Connection method	
Design of electrical connection	4/5-pin M12 circular connectors

Dimensions

Width	60 mm
Height	175 mm
Depth	49 mm

Weights

Weight, approx.	910 g
-----------------	-------

last modified: 04/10/2020