## **SIEMENS**

## Data sheet

6ES7143-5AH00-0BA0

SIMATIC ET 200AL, DIQ 16x24 V DC/0.5 A, 8xM12, Degree of protection IP67  $\,$ 



General information	
Product type designation	DIQ 16x24VDC/0.5A
HW functional status	FS03
Firmware version	V1.2.x
Product function	
• I&M data	Yes; I&M0 to I&M3
Engineering with	
<ul> <li>STEP 7 TIA Portal configurable/integrated as of version</li> </ul>	STEP 7 V14 or higher
<ul> <li>STEP 7 configurable/integrated as of version</li> </ul>	V5.5 SP4 Hotfix 7 or higher
<ul> <li>PROFIBUS as of GSD version/GSD revision</li> </ul>	GSD as of Revision 5
<ul> <li>PROFINET as of GSD version/GSD revision</li> </ul>	GSDML V2.3.1
Operating mode	
• DI	Yes
Counter	Yes
• DQ	Yes
Supply voltage	
Load voltage 1L+	

• Rated value (DC)	24 V
• permissible range, lower limit (DC)	20.4 V
• permissible range, upper limit (DC)	28.8 V
<ul> <li>Reverse polarity protection</li> </ul>	Yes; Against destruction; encoder power supply outputs applied with reversed polarity, loads pick up
Load voltage 2L+	
Rated value (DC)	24 V
<ul> <li>permissible range, lower limit (DC)</li> </ul>	20.4 V
• permissible range, upper limit (DC)	28.8 V
Reverse polarity protection	Yes; Against destruction; encoder power supply outputs applied with reversed polarity, loads pick up
Input current	
Current consumption (rated value)	75 mA; without load
from load voltage 1L+ (unswitched voltage)	4 A; Maximum value
from load voltage 2L+, max.	4 A; Maximum value
Encoder supply	
Number of outputs	8
24 V encoder supply	
Short-circuit protection	Yes; Per load voltage, electronic
Output current, max.	1.4 A; Total current of all encoders, max. 0.7 A per load voltage
Power loss	
Power loss, typ.	4 W
Power loss, typ.  Digital inputs	4 W
	4 W  16; Parameterizable as DIQ
Digital inputs	
Digital inputs  Number of digital inputs  Input characteristic curve in accordance with IEC	16; Parameterizable as DIQ
Digital inputs  Number of digital inputs  Input characteristic curve in accordance with IEC 61131, type 3	16; Parameterizable as DIQ
Digital inputs  Number of digital inputs  Input characteristic curve in accordance with IEC 61131, type 3  Number of simultaneously controllable inputs	16; Parameterizable as DIQ
Digital inputs  Number of digital inputs  Input characteristic curve in accordance with IEC 61131, type 3  Number of simultaneously controllable inputs  all mounting positions	16; Parameterizable as DIQ Yes
Digital inputs  Number of digital inputs  Input characteristic curve in accordance with IEC 61131, type 3  Number of simultaneously controllable inputs  all mounting positions  — up to 55 °C, max.	16; Parameterizable as DIQ Yes
Digital inputs  Number of digital inputs  Input characteristic curve in accordance with IEC 61131, type 3  Number of simultaneously controllable inputs  all mounting positions  — up to 55 °C, max.  Digital input functions, parameterizable	16; Parameterizable as DIQ Yes  16
Digital inputs  Number of digital inputs  Input characteristic curve in accordance with IEC 61131, type 3  Number of simultaneously controllable inputs  all mounting positions  — up to 55 °C, max.  Digital input functions, parameterizable  • Freely usable digital input	16; Parameterizable as DIQ Yes  16 Yes
Digital inputs  Number of digital inputs  Input characteristic curve in accordance with IEC 61131, type 3  Number of simultaneously controllable inputs  all mounting positions  — up to 55 °C, max.  Digital input functions, parameterizable  • Freely usable digital input  • Counter	16; Parameterizable as DIQ Yes  16  Yes  Yes  Yes
Digital inputs  Number of digital inputs  Input characteristic curve in accordance with IEC 61131, type 3  Number of simultaneously controllable inputs  all mounting positions  — up to 55 °C, max.  Digital input functions, parameterizable  • Freely usable digital input  • Counter  — Number, max.	16; Parameterizable as DIQ Yes  16  Yes  Yes  Yes  4
Digital inputs  Number of digital inputs  Input characteristic curve in accordance with IEC 61131, type 3  Number of simultaneously controllable inputs  all mounting positions  — up to 55 °C, max.  Digital input functions, parameterizable  • Freely usable digital input  • Counter  — Number, max.  — Counting frequency, max.	16; Parameterizable as DIQ Yes  16  Yes Yes Yes 4 2 kHz
Digital inputs  Number of digital inputs  Input characteristic curve in accordance with IEC 61131, type 3  Number of simultaneously controllable inputs  all mounting positions  — up to 55 °C, max.  Digital input functions, parameterizable  • Freely usable digital input  • Counter  — Number, max.  — Counting frequency, max.  — Counting width	16; Parameterizable as DIQ Yes  16  Yes Yes Yes 4 2 kHz 32 bit; Incl. sign
Digital inputs  Number of digital inputs  Input characteristic curve in accordance with IEC 61131, type 3  Number of simultaneously controllable inputs  all mounting positions  — up to 55 °C, max.  Digital input functions, parameterizable  • Freely usable digital input  • Counter  — Number, max.  — Counting frequency, max.  — Counting width  — Counting direction up/down	16; Parameterizable as DIQ Yes  16  Yes Yes Yes 4 2 kHz 32 bit; Incl. sign
Digital inputs  Number of digital inputs  Input characteristic curve in accordance with IEC 61131, type 3  Number of simultaneously controllable inputs  all mounting positions  — up to 55 °C, max.  Digital input functions, parameterizable  • Freely usable digital input  • Counter  — Number, max.  — Counting frequency, max.  — Counting width  — Counting direction up/down  Input voltage	16; Parameterizable as DIQ Yes  16  Yes Yes Yes 4 2 kHz 32 bit; Incl. sign Yes
Digital inputs  Number of digital inputs  Input characteristic curve in accordance with IEC 61131, type 3  Number of simultaneously controllable inputs  all mounting positions  — up to 55 °C, max.  Digital input functions, parameterizable  • Freely usable digital input  • Counter  — Number, max.  — Counting frequency, max.  — Counting width  — Counting direction up/down  Input voltage  • Rated value (DC)	16; Parameterizable as DIQ Yes  16  Yes Yes 4 2 kHz 32 bit; Incl. sign Yes
Digital inputs  Number of digital inputs  Input characteristic curve in accordance with IEC 61131, type 3  Number of simultaneously controllable inputs  all mounting positions  — up to 55 °C, max.  Digital input functions, parameterizable  • Freely usable digital input  • Counter  — Number, max.  — Counting frequency, max.  — Counting width  — Counting direction up/down  Input voltage  • Rated value (DC)  • for signal "0"	16; Parameterizable as DIQ Yes  16  Yes Yes 4 2 kHz 32 bit; Incl. sign Yes  24 V -3 to +5V

● for signal "1", typ.	3 mA
Input delay (for rated value of input voltage)	
for standard inputs	
— parameterizable	Yes
— at "0" to "1", min.	0.05 ms; 1.6 ms for channels 8 through 15
— at "0" to "1", max.	20 ms
— at "1" to "0", min.	0.05 ms; 1.6 ms for channels 8 through 15
— at "1" to "0", max.	20 ms
for technological functions	
— parameterizable	Yes
Cable length	
• unshielded, max.	30 m
Digital outputs	
Number of digital outputs	16; Parameterizable as DIQ
• in groups of	8; 2 load groups for 8 outputs each
Short-circuit protection	Yes; per channel, electronic
• Response threshold, typ.	0.7 A
Limitation of inductive shutdown voltage to	L+ (-53 V)
Digital output functions, parameterizable	
Switching tripped by comparison values	Yes
<ul> <li>Freely usable digital output</li> </ul>	Yes
Switching capacity of the outputs	
• on lamp load, max.	5 W
Load resistance range	
• lower limit	48 Ω
• upper limit	4 kΩ
Output voltage	
● for signal "1", min.	L+ (-0.8 V)
Output current	
● for signal "1" rated value	0.5 A
• for signal "0" residual current, max.	0.5 mA
Switching frequency	
• with resistive load, max.	100 Hz
<ul><li>with inductive load, max.</li></ul>	0.5 Hz
• on lamp load, max.	1 Hz
Total current of the outputs	
Current per group, max.	4 A
Cable length	
• unshielded, max.	30 m
Encoder	
Connectable encoders	

◆ 2-wire sensor
 — permissible quiescent current (2-wire sensor), max.

sensor), max.	
Interrupts/diagnostics/status information	
Substitute values connectable	Yes; channel by channel, parameterizable
Alarms	
Diagnostic alarm	Yes; Parameterizable
Diagnostic messages	
Short-circuit	Yes; Outputs to M; encoder supply to M; module by module
Diagnostics indication LED	
Channel status display	Yes; green LED
• for module diagnostics	Yes; green/red LED
<ul> <li>For load voltage monitoring</li> </ul>	Yes; green LED
Potential separation	
between the load voltages	Yes
Potential separation channels	
• between the channels, in groups of	8
<ul> <li>between the channels and backplane bus</li> </ul>	Yes
<ul> <li>between the channels and the power supply of</li> </ul>	No; 8 channels are non-isolated and 8 channels are isolated from
the electronics	supply voltage 1L+
Isolation	
Isolation tested with	707 V DC (type test)
Degree and class of protection	
IP degree of protection	IP65/67
Ambient conditions	
Ambient temperature during operation	
• min.	-30 °C
• max.	55 °C
Connection method	
Design of electrical connection for the inputs and outputs	M12, 5-pole
Design of electrical connection for supply voltage	M8, 4-pole
ET-Connection	
ET-Connection	M8, 4-pin, shielded
Dimensions	
Width	45 mm
Height	159 mm
Depth	40 mm
	10 111111

Weight, approx.

195 g

last modified: 02/04/2020