












# **Dimensions**



## **Model Number**


## VL18-54-M/40a/118/128

Retroreflective sensor with 4-pin, M12 x 1 connector

### **Features**

- Array control panel with highly visible LED display
- Flashing power on LED in case of short-circuit
- Multiple device installation possible, no mutual interference (no cross-talk)
- Not sensitive to ambient light, even with switched energy saving lamps
- Protection class II

## **Electrical connection**



- O = Light on
- = Dark on


### **Pinout**

Wire colors in accordance with EN 60947-5-2



1	BN	(brown)
2	WH	(white)
3	BU	(blue)
4	BK	(black)

## Indicators/operating means



l l	Light/dark switch		
2	Operating display green		
3	Switch state	yellow	
4	Sensitivity adjustment		

Technical data		
General specifications		
Effective detection range		0 3.5 m
Threshold detection range		4 m
Reference target		H50 reflector
Light source		LED
Light type		modulated visible red light , 632 nm
Polarization filter		yes
Diameter of the light spot		200 mm at a distance of 3500 mm
Angle of divergence		3 °
Optical face		frontal
Ambient light limit		30000 Lux; according to EN 60947-5-2:2007
Hysteresis	Н	< 15 %
Functional safety related parame	eters	
MTTF <sub>d</sub>		700 a
Mission Time (T <sub>M</sub> )		20 a
Diagnostic Coverage (DC)		0%
Indicators/operating means		0 /0
		LED groon, flooboo in coop of abort circuit
Operation indicator Function indicator		LED green, flashes in case of short-circuit  LED yellow, light with free light beam, flashes when falling short
		of the stability control , OFF when light beam is interrupted
Control elements		Sensitivity adjuster, light/dark switch
Electrical specifications		
Operating voltage	U <sub>B</sub>	10 30 V DC , class 2
No-load supply current	I <sub>O</sub>	< 25 mA
Protection class		II , rated voltage $\leq$ 50 V AC with pollution degree 1-2 according to IEC 60664-1
Output		
Switching type		light/dark on, switchable
Signal output		Push-pull (4 in 1) output short-circuit protected overvoltage protected
Switching voltage		30 V DC
Switching current		max. 200 mA
Voltage drop	U <sub>d</sub>	≤ 2.5 V DC
Switching frequency	f	500 Hz
Response time		1 ms
Ambient conditions		
Ambient temperature		-25 70 °C (-13 158 °F)
Storage temperature		-30 70 °C (-22 158 °F)
Relative humidity		90 % , noncondensing
Mechanical specifications		
Degree of protection		IP67
Connection		4-pin, M12 x 1 connector
Material		i pin, mile x i dominodoi
Housing		brass, nickel-plated
Optical face		PMMA
Mass		60 g
Compliance with standards and		50 g
directives conformity		EMC Directive 2004/109/EC
Directive conformity		EMC Directive 2004/108/EC
Standard conformity  Product standard		EN 60947-5-2:2007 IEC 60947-5-2:2007
Approvals and certificates		
UL approval		cULus Listed, Type 1 enclosure
CCC approval		CCC approval / marking not required for products rated ≤36 V
Tr		1 / · · · · · · · · · · · · · · · · · ·

### **Accessories**

### CPZ18B03

Mounting Bracket with swivel nut

#### **BF 18**

Mounting flange, 18 mm

#### BF 18-F

Plastic mounting adapter, 18 mm

### BF 5-30

Universal mounting bracket for cylindrical sensors with a diameter of 5 ... 30 mm

Other suitable accessories can be found at www.pepperl-fuchs.com

# **Curves/Diagrams**

