



Figure similar

SIMATIC ET 200SP, bundle PROFINET interface module IM 155-6 PN ST, max. 32 I/O modules, and 16 ET 200AL modules, multi hot swap, optional PN strain relief, PN security class 1, bundle consists of: interface module (6ES7155-6AA02-0BN0), server module (6ES7193-6PA00-0AA0), SIMATIC bus adapter BA 2x RJ45 (6ES7193-6AR00-0AA0)

General information	
Firmware version	V6.1
<ul style="list-style-type: none"> FW update possible 	Yes
Vendor identification (VendorID)	002AH
Device identifier (DeviceID)	0313H
Manufacturer ID according to ODVA (VendorID)	04E3H
Device ID according to ODVA (Product code)	0FA2H
Product function	
<ul style="list-style-type: none"> I&M data 	Yes; I&M0 to I&M4
<ul style="list-style-type: none"> Module swapping during operation (hot swapping) 	Yes; Multi-hot swapping
<ul style="list-style-type: none"> Isochronous mode 	No
Engineering with	
<ul style="list-style-type: none"> STEP 7 TIA Portal configurable/integrated from version 	V18
<ul style="list-style-type: none"> PROFINET from GSD version/GSD revision 	GSDML V2.43
Configuration control	
via dataset	Yes
Supply voltage	
Rated value (DC)	24 V
permissible range, lower limit (DC)	19.2 V
permissible range, upper limit (DC)	28.8 V
Reverse polarity protection	Yes
Short-circuit protection	Yes
Mains buffering	
<ul style="list-style-type: none"> Mains/voltage failure stored energy time 	10 ms
Input current	
Current consumption (rated value)	350 mA
Current consumption, max.	450 mA
Inrush current, max.	1 A
I^2t	0.05 A ² ·s
Power loss	
Power loss, typ.	1.8 W
Address area	
Address space per module	
<ul style="list-style-type: none"> Address space per module, max. 	288 byte; For input and output data respectively
Address space per station	
<ul style="list-style-type: none"> Address space per station, max. 	1 440 byte
Hardware configuration	
Rack	
<ul style="list-style-type: none"> Quantity of operable ET 200SP modules, max. 	32

• Quantity of operable ET 200AL modules, max.	16
Submodules	
• Number of submodules per station, max.	256
Interfaces	
Number of PROFINET interfaces	1; 2 ports (switch)
1. Interface	
Interface types	
• RJ 45 (Ethernet)	Yes; with BusAdapter
• Number of ports	2; with BusAdapter
• integrated switch	Yes
• BusAdapter (PROFINET)	Yes; BA 2x RJ45, BA 2x FC, BA 2x M12
Protocols	
• PROFINET IO Device	Yes
• Open IE communication	Yes
• Media redundancy	Yes; PROFINET MRP client
PROFINET IO Device	
Services	
— IRT	Yes; 250 µs to 4 ms in 125 µs frame
— PROFlenergy	Yes
— Prioritized startup	Yes
— Shared device	Yes
— Number of IO Controllers with shared device, max.	4
Interface types	
RJ 45 (Ethernet)	
• Transmission procedure	PROFINET with 100 Mbit/s full duplex (100BASE-TX)
• 100 Mbps	Yes
• Autonegotiation	Yes
• Autocrossing	Yes
Protocols	
Modbus TCP	No
Redundancy mode	
• PROFINET system redundancy (S2)	No
Media redundancy	
— MRP	Yes
— MRPD	No
Open IE communication	
• TCP/IP	Yes
• SNMP	Yes
• LLDP	Yes
Interrupts/diagnostics/status information	
Status indicator	Yes
Alarms	Yes
Diagnostics function	Yes
Diagnostics indication LED	
• RUN LED	Yes; green LED
• ERROR LED	Yes; red LED
• MAINT LED	Yes; Yellow LED
• Monitoring of the supply voltage (PWR-LED)	Yes; green PWR LED
• Connection display LINK TX/RX	Yes; 2x green link LEDs on BusAdapter
Potential separation	
between backplane bus and electronics	No
between PROFINET and all other circuits	Yes; 1500 V AC (type test)
between supply and all other circuits	No
Permissible potential difference	
between different circuits	Safety extra low voltage SELV
Isolation	
Isolation tested with	707 V DC (type test)
Standards, approvals, certificates	
Network loading class	3
product functions / security / header	

PROFINET Security Class	1
signed firmware update	Yes
safely removing data	Yes
data integrity	Yes
Ambient conditions	
Ambient temperature during operation	
<ul style="list-style-type: none"> horizontal installation, min. horizontal installation, max. vertical installation, min. vertical installation, max. 	<ul style="list-style-type: none"> -30 °C; No condensation 60 °C -30 °C; No condensation 50 °C
Altitude during operation relating to sea level	
<ul style="list-style-type: none"> Installation altitude above sea level, max. 	5 000 m; restrictions for installation altitudes > 2 000 m, see ET 200SP system manual
connection method	
ET-Connection	
<ul style="list-style-type: none"> via BU/BA Send 	Yes; + 16 ET 200AL modules
Mechanics/material	
Strain relief	Yes; Optional
Dimensions	
Width	50 mm
Height	117 mm
Depth	74 mm
Weights	
Weight, approx.	120 g; without BusAdapter

last modified: 4/10/2024 