



SIMATIC S7-400, Power supply PS407: 10 A, wide range, UC 120/230V, 5 V DC/10 A

Figure similar

Supply voltage	
Rated value (DC)	
• 120 V DC	Yes
• 230 V DC	Yes
Rated value (AC)	
• 120 V AC	Yes
• 230 V AC	Yes
Line frequency	
• Rated value 50 Hz	Yes
• Rated value 60 Hz	Yes
• permissible range, lower limit	47 Hz
• permissible range, upper limit	63 Hz
Mains buffering	
• Mains/voltage failure stored energy time	20 ms
• Mains buffering according to NAMUR recommendation	Yes
Input current	
Rated value at 120 V DC	1 A
Rated value at 230 V DC	0.5 A
Rated value at 120 V AC	0.9 A
Rated value at 230 V AC	0.5 A
Inrush current, max.	63 A; Full width at half maximum 1 ms
Leakage current, max.	3.5 mA
Output voltage	
Type of output voltage	DC
Rated value (DC)	
• 5 V DC	Yes
• 24 V DC	Yes
Output current	
for backplane bus (5 V DC), max.	10 A; no base load required
for backplane bus (24 V DC), max.	1 A; idling-proof
Short-circuit protection	Yes
Power	
Active power input, typ.	95 W
Power loss	
Power loss, typ.	20 W

Battery	
Backup battery	
• Backup battery (optional)	Yes; 1x lithium AA; 3.6 V / 2.2 Ah
Hardware configuration	
Slots	
• required slots	2
Potential separation	
primary/secondary	Yes
Isolation	
Overvoltage category	II
EMC	
Compliance with line harmonic distortion limits	
• Compliance with line harmonic distortion acc. to IEC 61000-3-2, IEC 61000-3-3	Yes
Degree and class of protection	
Equipment protection class	I, with protective conductor
Standards, approvals, certificates	
FM approval	Yes; Ta: 0 °C to 70 °C T4
Ambient conditions	
Ambient temperature during operation	
• min.	0 °C
• max.	60 °C
Connection method	
Design of electrical connection	3x 1.5 mm <sup>2</sup> , solid or stranded wire with end sleeve, external diameter 3 mm to 9 mm
Dimensions	
Width	50 mm
Height	290 mm
Depth	217 mm
Weights	
Weight, approx.	1 200 g
<b>last modified:</b>	2/7/2021 