



SIMATIC S7-1500 Analog input/output module AI 4x U/I/RTD/TC ST; 4 channels in groups of 4; Hardware interrupts; Diagnostics AQ 2x U/I ST; 2 channels in groups of 2; Substitute value; Diagnostics Common mode voltage approx. 10 V 16 bit; Accuracy 0.3%; Delivery including push-in front connector, infeed element, shield bracket and shield terminal

General information	
Product type designation	AI 4xU/I/RTD/TC /AQ 2xU/I ST
HW functional status	FS01
Firmware version	V1.0.0
<ul style="list-style-type: none"> FW update possible 	Yes
Product function	
<ul style="list-style-type: none"> I&M data 	Yes; I&M0 to I&M3
<ul style="list-style-type: none"> Isochronous mode 	No
<ul style="list-style-type: none"> Prioritized startup 	No
<ul style="list-style-type: none"> Measuring range scalable 	No
<ul style="list-style-type: none"> Scalable measured values 	No
<ul style="list-style-type: none"> Adjustment of measuring range 	No
<ul style="list-style-type: none"> Output range scalable 	No
Engineering with	
<ul style="list-style-type: none"> STEP 7 TIA Portal configurable/integrated from version 	V13 / V13.0.2
<ul style="list-style-type: none"> STEP 7 configurable/integrated from version 	V5.5 SP3 / -
<ul style="list-style-type: none"> PROFIBUS from GSD version/GSD revision 	V1.0 / V5.1
<ul style="list-style-type: none"> PROFINET from GSD version/GSD revision 	V2.3 / -
Operating mode	
<ul style="list-style-type: none"> Oversampling 	No
<ul style="list-style-type: none"> MSI 	Yes
<ul style="list-style-type: none"> MSO 	Yes
CiR - Configuration in RUN	
Reparameterization possible in RUN	Yes
Calibration possible in RUN	Yes
Supply voltage	
Rated value (DC)	24 V
permissible range, lower limit (DC)	19.2 V
permissible range, upper limit (DC)	28.8 V
Reverse polarity protection	Yes
Input current	
Current consumption, max.	200 mA; with 24 V DC supply
Encoder supply	
24 V encoder supply	
<ul style="list-style-type: none"> Short-circuit protection 	Yes
<ul style="list-style-type: none"> Output current, max. 	20 mA; Max. 47 mA per channel for a duration < 10 s
Power	
Power available from the backplane bus	0.7 W

Power loss	
Power loss, typ.	3.3 W
Analog inputs	
Number of analog inputs	4
<ul style="list-style-type: none"> • For current measurement • For voltage measurement • For resistance/resistance thermometer measurement • For thermocouple measurement 	4 4 2 4
permissible input voltage for voltage input (destruction limit), max.	28.8 V
permissible input current for current input (destruction limit), max.	40 mA
Constant measurement current for resistance-type transmitter, typ.	150 Ohm, 300 Ohm, 600 Ohm, Pt100, Pt200, Ni100: 1.25 mA; 6 000 Ohm, Pt500, Pt1000, Ni1000, LG-Ni1000: 0.625 mA; PTC: 0.472 mA
Technical unit for temperature measurement adjustable	Yes; °C/°F/K
Analog input with oversampling	No
Standardization of measured values	No
Input ranges (rated values), voltages	
<ul style="list-style-type: none"> • 0 to +5 V • 0 to +10 V • 1 V to 5 V <ul style="list-style-type: none"> — Input resistance (1 V to 5 V) • -1 V to +1 V <ul style="list-style-type: none"> — Input resistance (-1 V to +1 V) • -10 V to +10 V <ul style="list-style-type: none"> — Input resistance (-10 V to +10 V) • -2.5 V to +2.5 V <ul style="list-style-type: none"> — Input resistance (-2.5 V to +2.5 V) • -25 mV to +25 mV • -250 mV to +250 mV <ul style="list-style-type: none"> — Input resistance (-250 mV to +250 mV) • -5 V to +5 V <ul style="list-style-type: none"> — Input resistance (-5 V to +5 V) • -50 mV to +50 mV <ul style="list-style-type: none"> — Input resistance (-50 mV to +50 mV) • -500 mV to +500 mV <ul style="list-style-type: none"> — Input resistance (-500 mV to +500 mV) • -80 mV to +80 mV <ul style="list-style-type: none"> — Input resistance (-80 mV to +80 mV) 	No No Yes 100 kΩ Yes 10 MΩ Yes 100 kΩ Yes 10 MΩ Yes 10 MΩ No Yes 10 MΩ Yes 100 kΩ Yes 10 MΩ Yes 10 MΩ Yes 10 MΩ
Input ranges (rated values), currents	
<ul style="list-style-type: none"> • 0 to 20 mA <ul style="list-style-type: none"> — Input resistance (0 to 20 mA) • -20 mA to +20 mA <ul style="list-style-type: none"> — Input resistance (-20 mA to +20 mA) • 4 mA to 20 mA <ul style="list-style-type: none"> — Input resistance (4 mA to 20 mA) 	Yes 25 Ω; Plus approx. 42 ohms for overvoltage protection by PTC Yes 25 Ω; Plus approx. 42 ohms for overvoltage protection by PTC Yes 25 Ω; Plus approx. 42 ohms for overvoltage protection by PTC
Input ranges (rated values), thermocouples	
<ul style="list-style-type: none"> • Type B <ul style="list-style-type: none"> — Input resistance (Type B) • Type C • Type E <ul style="list-style-type: none"> — Input resistance (Type E) • Type J <ul style="list-style-type: none"> — Input resistance (type J) • Type K <ul style="list-style-type: none"> — Input resistance (Type K) • Type L • Type N <ul style="list-style-type: none"> — Input resistance (Type N) • Type R 	Yes 10 MΩ No Yes 10 MΩ Yes 10 MΩ Yes 10 MΩ No Yes 10 MΩ Yes

— Input resistance (Type R)	10 MΩ
• Type S	Yes
— Input resistance (Type S)	10 MΩ
• Type T	Yes
— Input resistance (Type T)	10 MΩ
• Type U	No
• Type TXK/TXK(L) to GOST	No
Input ranges (rated values), resistance thermometer	
• Cu 10	No
• Cu 10 according to GOST	No
• Cu 50	No
• Cu 50 according to GOST	No
• Cu 100	No
• Cu 100 according to GOST	No
• Ni 10	No
• Ni 10 according to GOST	No
• Ni 100	Yes; Standard/climate
— Input resistance (Ni 100)	10 MΩ
• Ni 100 according to GOST	No
• Ni 1000	Yes; Standard/climate
— Input resistance (Ni 1000)	10 MΩ
• Ni 1000 according to GOST	No
• LG-Ni 1000	Yes; Standard/climate
— Input resistance (LG-Ni 1000)	10 MΩ
• Ni 120	No
• Ni 120 according to GOST	No
• Ni 200	No
• Ni 200 according to GOST	No
• Ni 500	No
• Ni 500 according to GOST	No
• Pt 10	No
• Pt 10 according to GOST	No
• Pt 50	No
• Pt 50 according to GOST	No
• Pt 100	Yes; Standard/climate
— Input resistance (Pt 100)	10 MΩ
• Pt 100 according to GOST	No
• Pt 1000	Yes; Standard/climate
— Input resistance (Pt 1000)	10 MΩ
• Pt 1000 according to GOST	No
• Pt 200	Yes; Standard/climate
— Input resistance (Pt 200)	10 MΩ
• Pt 200 according to GOST	No
• Pt 500	Yes; Standard/climate
— Input resistance (Pt 500)	10 MΩ
• Pt 500 according to GOST	No
Input ranges (rated values), resistors	
• 0 to 150 ohms	Yes
— Input resistance (0 to 150 ohms)	10 MΩ
• 0 to 300 ohms	Yes
— Input resistance (0 to 300 ohms)	10 MΩ
• 0 to 600 ohms	Yes
— Input resistance (0 to 600 ohms)	10 MΩ
• 0 to 3000 ohms	No
• 0 to 6000 ohms	Yes
— Input resistance (0 to 6000 ohms)	10 MΩ
• PTC	Yes
— Input resistance (PTC)	10 MΩ
Thermocouple (TC)	
Temperature compensation	

— parameterizable	Yes
— internal temperature compensation	Yes
— external temperature compensation via RTD	Yes
— Compensation for 0 °C reference point temperature	Yes; fixed value can be set
— Reference channel of the module	No
Cable length	
• shielded, max.	800 m; for U/I, 200 m for R/RTD, 50 m for TC
Analog outputs	
Number of analog outputs	2
Voltage output, short-circuit protection	Yes
Voltage output, short-circuit current, max.	24 mA
Current output, no-load voltage, max.	22 V
Cycle time (all channels), min.	3.2 ms; ±0.5 ms, regardless of the number of activated channels
Output ranges, voltage	
• 0 to 10 V	Yes
• 1 V to 5 V	Yes
• -5 V to +5 V	No
• -10 V to +10 V	Yes
Output ranges, current	
• 0 to 20 mA	Yes
• -20 mA to +20 mA	Yes
• 4 mA to 20 mA	Yes
Connection of actuators	
• for voltage output two-wire connection	Yes
• for voltage output four-wire connection	Yes
• for current output two-wire connection	Yes
Load impedance (in rated range of output)	
• with voltage outputs, min.	1 kΩ; 0.5 kΩ at 1 to 5 V
• with voltage outputs, capacitive load, max.	1 μF
• with current outputs, max.	750 Ω
• with current outputs, inductive load, max.	10 mH
Cable length	
• shielded, max.	800 m; for current, 200 m for voltage
Analog value generation for the inputs	
Integration and conversion time/resolution per channel	
• Resolution with overrange (bit including sign), max.	16 bit
• Integration time, parameterizable	Yes
• Integration time (ms)	2,5 / 16,67 / 20 / 100 ms
• Basic conversion time, including integration time (ms)	9 / 23 / 27 / 107 ms
— additional conversion time for wire-break monitoring	9 ms
— additional conversion time for resistance measurement	150 ohm, 300 ohm, 600 ohm, Pt100, Pt200, Ni100: 2 ms, 6000 ohm, Pt500, Pt1000, Ni1000, LG-Ni1000, PTC: 4 ms
• Interference voltage suppression for interference frequency f1 in Hz	400 / 60 / 50 / 10
• Time for offset calibration (per module)	Basic conversion time of the slowest channel
Smoothing of measured values	
• parameterizable	Yes
• Step: None	Yes
• Step: low	Yes
• Step: Medium	Yes
• Step: High	Yes
Analog value generation for the outputs	
Integration and conversion time/resolution per channel	
• Resolution with overrange (bit including sign), max.	16 bit
• Conversion time (per channel)	0.5 ms
Settling time	
• for resistive load	1.5 ms
• for capacitive load	2.5 ms

- for inductive load

2.5 ms

Encoder

Connection of signal encoders

• for voltage measurement	Yes
• for current measurement as 2-wire transducer — Burden of 2-wire transmitter, max.	Yes 820 Ω
• for current measurement as 4-wire transducer	Yes
• for resistance measurement with two-wire connection	Yes; Only for PTC
• for resistance measurement with three-wire connection	Yes; All measuring ranges except PTC; internal compensation of the cable resistances
• for resistance measurement with four-wire connection	Yes; All measuring ranges except PTC

Errors/accuracies

Linearity error (relative to input range), (+/-)	0.02 %
Temperature error (relative to input range), (+/-)	0.005 %/K; With TC type T 0.02 ± % / K
Crosstalk between the inputs, max.	-80 dB
Repeat accuracy in steady state at 25 °C (relative to input range), (+/-)	0.02 %
Output ripple (relative to output range, bandwidth 0 to 50 kHz), (+/-)	0.02 %
Linearity error (relative to output range), (+/-)	0.15 %
Temperature error (relative to output range), (+/-)	0.002 %/K
Crosstalk between the outputs, max.	-100 dB
Repeat accuracy in steady state at 25 °C (relative to output range), (+/-)	0.05 %
Temperature error of internal compensation	±6 °C

Operational error limit in overall temperature range

• Voltage, relative to input range, (+/-)	0.3 %
• Current, relative to input range, (+/-)	0.3 %
• Resistance, relative to input range, (+/-)	0.3 %
• Resistance thermometer, relative to input range, (+/-)	0.3 %; Ptxxx standard: ±1.5 K, Ptxxx climate: ±0.5 K, Nixxx standard: ±0.5 K, Nixxx climate: ±0.3 K
• Thermocouple, relative to input range, (+/-)	0.3 %; Type B: > 600 °C ±4.6 K, type E: > -200 °C ±1.5 K, type J: > -210 °C ±1.9 K, type K: > -200 °C ±2.4 K, type N: > -200 °C ±2.9 K, type R: > 0 °C ±4.7 K, type S: > 0 °C ±4.6 K, type T: > -200 °C ±2.4 K
• Voltage, relative to output range, (+/-)	0.3 %
• Current, relative to output range, (+/-)	0.3 %

Basic error limit (operational limit at 25 °C)

• Voltage, relative to input range, (+/-)	0.1 %
• Current, relative to input range, (+/-)	0.1 %
• Resistance, relative to input range, (+/-)	0.1 %
• Resistance thermometer, relative to input range, (+/-)	0.1 %; Ptxxx standard: ±0.7 K, Ptxxx climate: ±0.2 K, Nixxx standard: ±0.3 K, Nixxx climate: ±0.15 K
• Thermocouple, relative to input range, (+/-)	0.1 %; Type B: > 600 °C ±1.7 K, type E: > -200 °C ±0.7 K, type J: > -210 °C ±0.8 K, type K: > -200 °C ±1.2 K, type N: > -200 °C ±1.2 K, type R: > 0 °C ±1.9 K, type S: > 0 °C ±1.9 K, type T: > -200 °C ±0.8 K
• Voltage, relative to output range, (+/-)	0.2 %
• Current, relative to output range, (+/-)	0.2 %

Interference voltage suppression for $f = n \times (f_1 \pm 1 \%)$, f_1 = interference frequency

• Series mode interference (peak value of interference < rated value of input range), min.	40 dB
• Common mode voltage, max.	10 V
• Common mode interference, min.	60 dB

Interrupts/diagnostics/status information

Diagnostics function	Yes
Substitute values connectable	Yes
Alarms	
• Diagnostic alarm	Yes
• Limit value alarm	Yes; two upper and two lower limit values in each case
Diagnoses	
• Monitoring the supply voltage	Yes
• Wire-break	Yes; only for input type 1 ... 5 V, 4 ... 20 mA, TC, R, RTD and output

<ul style="list-style-type: none"> • Short-circuit • Overflow/underflow 	type current Yes; Only for output type "voltage" Yes
Diagnostics indication LED	
<ul style="list-style-type: none"> • RUN LED • ERROR LED • Monitoring of the supply voltage (PWR-LED) • Channel status display • for channel diagnostics • for module diagnostics 	Yes; green LED Yes; red LED Yes; green LED Yes; green LED Yes; red LED Yes; red LED
Potential separation	
Potential separation analog inputs	
<ul style="list-style-type: none"> • between the channels • between the channels, in groups of • between the channels and backplane bus • Between the channels and load voltage L+ 	No 4 Yes Yes
Potential separation analog outputs	
<ul style="list-style-type: none"> • between the channels • between the channels, in groups of • between the channels and backplane bus • Between the channels and load voltage L+ 	No 2 Yes Yes
Permissible potential difference	
between the inputs (UCM)	20 V DC
Between the inputs and MANA (UCM)	10 V DC
between S- and MANA (UCM)	8 V DC
Isolation	
Isolation tested with	707 V DC (type test)
Ambient conditions	
Ambient temperature during operation	
<ul style="list-style-type: none"> • horizontal installation, min. • horizontal installation, max. • vertical installation, min. • vertical installation, max. 	0 °C 60 °C 0 °C 40 °C
Altitude during operation relating to sea level	
<ul style="list-style-type: none"> • Installation altitude above sea level, max. 	5 000 m; Restrictions for installation altitudes > 2 000 m, see manual
Dimensions	
Width	25 mm
Height	147 mm
Depth	129 mm
Weights	
Weight, approx.	250 g
Other	
Note:	Supplied incl. 40-pole push-in front connectors. Additional basic error and noise for integration time = 2.5 ms: Voltage: ±250 mV (±0.02%), ±80 mV (±0.05%), ±50 mV (±0.05%); resistance: 150 Ohms (±0.02%); resistance thermometer: Pt100 climate: ±0.08 K, Ni100 climate: ±0.08 K; thermoelement: Type B, R, S: ±3 K, type E, J, K, N, T: ±1 K
last modified:	4/29/2021 