

FEATURES

- Ideal for space saving installations
- CY has a tinned copper wire braid screen
- Flexible cable with copper conductors
- White numbers on the outer sheath

RS PRO 2 Core CY Control Cable 0.75 mm², 50m, Screened

RS Stock No.: 827-4133



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

The CY control cables from RS PRO are number coded and are reliable connecting cables which combine the characteristics of a flexible mains cable coupled with saving space due to the small cable diameters suitable for both fixed and flexible installations

General Specifications

Cable Shape	Multicore
Screened/Unscreened	Screened
Screen Type	Braid
Sheath Colour	Grey
Sheath Material	Polyvinyl Chloride PVC
Filler Material	Non-Wicking Filler
Fire Behaviour	Flame Retardant
Applications	Plant engineering, Conveyor and transport systems, Heating and air-conditioning systems

Electrical Specifications

Current Rating	12A
Voltage Rating	300V/500V
Conductor Resistance	26Ω/km
Test Voltage	2000VAC
Earth Cable	Yes
Conductor Material	Copper
Insulation Material	PVC

Mechanical Specifications

Length	50m
Number of Cores	2
Number of Strands	24
Size of Strands	0.20mm
Core Strands	24/0.20mm
Cross Sectional Area	0.75mm ²
Outer Diameter	5.9mm
American Wire Gauge	18
Minimum Bend Radius	Fixed - 6 x D Occasional Flexing - 20 x D
Oil Resistant	Yes
Armoured	No
Weight	49kg/km

Operation Environment Specifications

Operating Temperature Range	Flexing:	Static:
		-5°C to 70°C
Minimum Operating Temperature	-5°C	40°C
Maximum Operating Temperature	70°C	80°C

Approvals

Compliance/Certifications	RoHS Certificate Of Compliance
Standards Met	IEC 60228/VDE 0295, IEC 60 228 that is VDE 0295, class 5 ,IEC 60332.1 , ECD 73/23/EEC



Part Number	No. Cores x Cross Sectional Area (mm ²)	Outer Diameter (mm)	Weight Kg/Km
8274139	CY 2x0.5	5.8	45.0
8274149	CY 3G0.5	6.1	59.0
8274158	CY 4G0.5	6.5	71.0
8274151	CY 5G0.5	7.0	86.0
8274167	CY 7G0.5	7.5	105.0
8274177	CY 12G0.5	9.9	104.0
8274192	CY 18G0.5	11.5	141.0
8274133	CY 2x0.75	5.9	49.0
8274155	CY 5G0.75	7.4	87.0
8274161	CY 7G0.75	8.0	109.0
8274186	CY 12G0.75	10.4	177.0
8274195	CY 18G0.75	12.1	254.0
8274142	CY 2x1.0	6.2	57.0
8274164	CY 5G1	8.0	110.0
8274170	CY 7G1	8.6	134.3
8274189	CY 12G1	11.3	217.0
8274199	CY 18G1	13.2	306.0
8274145	CY 2G1.5	7.0	70.0
8274183	CY 12G1.5	13.0	365.0
8274209	CY 18G1.5	14.8	405.0
8274173	CY 7G2.5	11.2	249.0