

Product type designation

MDS D423 transponder

Transponder MDS D423 for RF200/RF300 ISO button for in and on metal, ISO 15693, Chip type FUJITSU MB89R118, 2000 byte FRAM user memory 30x 8 mm (DxH); Minimum order quantity 10 units



Wireless frequencies

Operating frequency / Rated value	13.56 MHz
Range / maximum	80 mm; range is reader dependent: observe http://support.automation.siemens.com/WW/view/en/67384964
Protocol / with radio transmission	ISO 15693
Transfer rate / with radio transmission / maximum	26.5 kbit/s
Product feature / multitag-capable	Yes

Electrical data

Product component / Backup battery	No
------------------------------------	----

Memory

Type of memory	FRAM
Storage capacity / of the user memory	2000 byte
Type of memory organization	UID (fixed code) 8 bytes, user memory 2000 bytes, configuration memory 40 bytes
Number of read cycles / at ambient temperature < 40 °C / maximum	1000000000000
Number of write cycles / at ambient temperature < 40 °C / maximum	1000000000000

Data retention time / at ambient temperature < 40 °C / not less than	10 y
Property of memory	Block-by-block write protection of the user memory
Type of transponder chip used	Fujitsu MB89R118

Mechanical data

Material	PPS
Color	black
Tightening torque / of the screw for securing the equipment / maximum	1 N·m
Mounting distance / relating to metal surfaces / recommended / minimum	0 mm

Permitted ambient conditions

Ambient temperature	
<ul style="list-style-type: none"> during read/write access 	-25 ... +85 °C
<ul style="list-style-type: none"> outside the read/write area 	-40 ... +100 °C
<ul style="list-style-type: none"> during storage 	-40 ... +100 °C
Protection class IP	IP68 / IPx9K
Shock resistance	According to DIN EN 60721-3-7 Class 7 M3
Shock acceleration	500 m/s ²
Vibrational acceleration	200 m/s ²

Design, dimensions and weight

Height	8 mm
Diameter	30 mm
Net weight	15 g
Mounting type	M4 countersunk screw

Product properties, functions, components / general

Product feature	
<ul style="list-style-type: none"> silicon-free 	Yes
<ul style="list-style-type: none"> printable 	No

Standards, specifications, approvals

MTBF	228 y
------	-------

Accessories

accessories	mounting hood
-------------	---------------

Further Information / Internet Links

Internet-Link	
<ul style="list-style-type: none"> to website: Selector SIMATIC NET SELECTION TOOL 	https://support.industry.siemens.com/cs/ww/en/view/67384964
<ul style="list-style-type: none"> to website: Industrial communication 	http://www.siemens.com/ident/rfid
<ul style="list-style-type: none"> to website: Industry Mall 	https://mall.industry.siemens.com
<ul style="list-style-type: none"> to website: Information and Download Center 	http://www.siemens.com/industry/infocenter

- to website: Image database
- to website: CAx Download Manager
- to website: Industry Online Support

<http://automation.siemens.com/bilddb>

<http://www.siemens.com/cax>

<https://support.industry.siemens.com>

last modified:

01/09/2019