

FEATURES

- Low gas emissions
99% plus recombination
- Excellent recovery from deep discharge
- Leak proof – Sealed batteries
- ABS resin case to UL94-HB conform
- Road transport to UN2800 (Batteries, Wet, Non-Spillable)
- Air Transport to Special Provision 'A67' 'IATA' & 'ICAO'. (Batteries, Wet, Non-Spillable)

RS PRO Lead Acid Battery 12V, 26Ah

RS Stock No.: 837-0978



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS Pro Lead acid batteries are suitable for use across a number of industries as well as for regular charge/discharge duty. They are sealed and have many uses, and are ideal for cyclic products. These batteries are long life rechargeable batteries.

General Specifications

Technology	AGM
Designed for Cyclic Application	Yes
Eurobat Classification	3 to 5 Years
Container Material	A.B.S. (UL94-HB) conform
Application	Cyclic products

Electrical Specifications

Capacity	26Ah
Nominal Voltage	12V
Terminal Type	T3

Mechanical Specifications

Dimensions	125mm x 166mm x 175mm
Height	125mm
Length	166mm
Width	175mm
Weight	9.4kg

Operation Environment Specifications

Operating Temperature Range	-15 → +50°C
------------------------------------	-------------

Approvals

Compliance/Certifications	UL94-HB
----------------------------------	---------



