SIEMENS

Data sheet

6GT2801-3BA10

SILVERS BAAATO BESSOR	
suitability for operation	RF300, ISO 15693 and MOBY E transponder, for connecting to communication modules and PC systems
radio frequencies	
operating frequency / rated value	13.56 MHz
range / maximum	200 mm; Range is dependent on transponder type: observe http://support.automation.siemens.com/WW/view/en/67384964
protocol / with radio transmission	RF300 specific, ISO 15693, ISO 18000-3, ISO 14443
transfer rate / with radio transmission / maximum	106 kbit/s
product feature / multitag-capable	No
electrical data	
transfer rate / at the point-to-point connection / serial / maximum	115.2 kbit/s
transmission time / for user data	
 for write access / per byte / typical 	0.13 ms
 for read access / per byte / typical 	0.13 ms
interfaces	
standard for interfaces / for communication	RS422/RS232
type of electrical connection	M12, 8-pin
mechanical data	
material	PA 12
color	Ti gray
tightening torque / of the screw for securing the equipment / maximum	1.5 N·m
mounting distance / relating to metal surfaces / recommended / minimum	0 mm
supply voltage, current consumption, power loss	
supply voltage	
 at DC / rated value 	24 V
• at DC	20.4 28.8 V
consumed current / at DC	
• at 24 V / typical	0.15 A
ambient conditions	
ambient temperature	
during operation	-25 +70 °C
during storage	-40 +85 °C
during transport	-40 +85 °C
protection class IP	
shock resistance	EN 60721-3-7 Class 7 M2 500 m/s ²
shock acceleration	

RF380R reader

SIMATIC RF300 Reader RF380R (GEN2) RS422/232 interface (3964R) IP67, -25 to +70 °C, 160x 80x 41 mm with integrated antenna.

vibrational acceleration	200 m/s ²
design, dimensions and weights	
width	80 mm
height	41 mm
depth	160 mm
net weight	0.6 kg
fastening method	4 x M5 screws
wire length	
 with RS 232 interface / maximum 	30 m
 for RS 422 interface / maximum 	1000 m
product features, product functions, product components	/ general
display version	5-color LED
product feature / silicon-free	Yes
standards, specifications, approvals	
certificate of suitability	Radio acc. to R&TTE guidelines EN 300 330, EN 301489, CE, FCC, cULus
certificate of suitability	
• IECEx	No
MTBF	173 у
further information / internet-Links	
Internet-Link	
 to web page: selection aid TIA Selection Tool 	https://support.industry.siemens.com/cs/ww/en/view/67384964
 to website: Industrial communication 	http://www.siemens.com/ident/rfid
 to website: Industry Mall 	https://mall.industry.siemens.com
 to website: Information and Download Center 	http://www.siemens.com/industry/infocenter
 to website: Image database 	http://automation.siemens.com/bilddb
 to website: CAx-Download-Manager 	http://www.siemens.com/cax
 to website: Industry Online Support 	https://support.industry.siemens.com

last modified:

12/18/2020 🖸