
B	=			N
SENDI	NG AL	L THE RIG	HT SIG	SNALS

TECHNICAL DATA SHEET	code	70046
	version	3
	date	2010-02-11
FRNC Speaker Cable 2x2.5mm2	page	1/2

APPLICATION

Speaker cable for use in indoor or outdoor applications

CONSTRUCTION



. Conductor Stranded 50 x 0.25 mm

Material Bare oxygen free copper (2.5 mm²)

2. Insulation

Material FRNC

Diameter over insulation $2.70 \pm 0.07 \text{ mm}$ Colour of insulation Black and red

3. Cable core 2 wires twisted

4. Sheath

Material FRNC with matte finish

Diameter over sheath $7.30 \pm 0.10 \text{ mm}$

Colour of sheath Grey (like RAL 7000) or Black (UV resistant)



TECHNICAL DATA SHEET	code	70046
	version	3
	date	2010-02-11
FRNC Speaker Cable 2x2.5mm2	page	2/2

REQUIREMENTS AND TEST METHODS

Electrical:

 $\begin{array}{lll} \mbox{Resistance conductor @ 20°C} & < 8 \ \Omega/km \\ \mbox{Maximum operating voltage} & 300 \ V \ RMS \\ \mbox{Test voltage conductor-conductor} & 1kV = \mbox{for 1min.} \\ \mbox{Insulation resistance at 20C} & > 200 \ Mohm*km \\ \end{array}$

Mechanical and physical:

Flame test IEC 60332-1

FRNC material

Corrosivity IEC 60754-1 & IEC 60754-2

LOI >34% Max pulling tension 350N

Temperature range operating (moving instalation)

-5 to +60 °C

Temperature range operating (fixed installation)

-30 to +70 °C



Belden CDT believes this product to be in compliance with the environmental regulations EU RoHS (Directive 2002/95/EC, 27 January 2003); this is valid for all material produced after the RoHS compliant date for this product.