Pliers Wrench XL



NEW

The unique installation tool now also in 400 mm length. For opening widths up to 85 mm / 3 3/8"

FF

Pliers and a wrench in a single tool

adjustable tightening tool, also excellent for gripping, holding, pressing and bending workpieces, replaces diverse expensive, large open-end wrenches up to AF 85 mm or 3 3/8"

smooth jaws, also for damage free installation of quality union joints made from brass, red brass, stainless steel or chrome plated material

zero backlash jaw pressure prevents damage to edges of sensitive components

adjustment at the touch of a button directly on the workpiece

parallel jaws give a more solid grip; the construction gives infinite adjustment of all widths up to the specified maximum size of AF 85 or 3 3/8"



 optimised adjustment to the workpiece with hand-friendly position of grips

KNIPE

ER EE MAN

- reliable catching of the hinge bolt: no unintentional shifting
- the action of the jaws allows quick tightening and release of bolted connections using the ratchet principle
- lever transmission greater than 10 : 1 for strong gripping power
- Chrome vanadium electric steel, forged, oil-hardened

Pliers Wrench XL

Chemicals / oil / gas industry



Hydraulic piping











District heating / public utility companies









Food industry / bottling plants







Industrial applications / cable connections













Statistics of the owner water of the





The family for all screw joints

























Article No.	EAN 4003773-	Adjustment positions	inch	mm	∢— ► mm	۲۵ و
86 03 150	069676	14	1	27	150	175
86 03 180	035466	13	1 3/8	35	180	254
86 03 250	033837	17	1 3/4	46	250	536
86 03 300	041429	22	2 3/8	60	300	729
86 03 400	077312	25	3 3/8	85	400	1460
86 05 150	069928	14	1	27	150	193
86 05 180	047162	13	1 3/8	35	180	277
86 05 250	047841	17	1 3/4	46	250	571

KNIPEX-Werk

C. Gustav Putsch KG Oberkamper Strasse 13

42349 Wuppertal Germany

Tel.: +49 (0) 202 - 47 94-0 Fax: +49 (0) 202 - 47 74 94

info@knipex.de www.knipex.de



Your distributor