

Short description:

Crucial for trimming costs, comprehensive energy measurement is necessary to optimize energy consumption. WAGO's portfolio now has new energy meters that simplify this task while offering several key advantages. They use push-in connection technology with a lever, making them connect quickly and easily. Versions for current transformers are even slimmer at only 35 mm. These slim profiles save a tremendous amount of control cabinet space. In addition to the values for active and reactive energy, the energy meters also record the mains frequency, as well as current, voltage and power for all phases. And the user can conveniently scan all of these energy characteristics at a glance on a large, illuminated display. **Features:**

- Push-in CAGE CLAMP[®] and lever save time at every stage
- Real space savings: 35 mm wide (2PUCT)
- Measurement of supply and purchase
- Energy measurement in four tariffs
- The communications pro: M-Bus/Modbus® interface and two S0 pulse outputs
- Full transparency at a glance: display energy quality characteristics on an illuminated full-format display
- Intuitive configuration: touch-sensitive controls and configuration app via Bluetooth®

Technical data

recimical data			
Configuration		Input	
Configuration options Touch-sensitive controls Configuration app via <i>Bluetooth</i> *	Input signal type	Voltage Current	
	Network configuration	Two-wire, three-wire and four-wire net- works	
	Nominal input voltage U _{i nom}	3 x AC 230 400 V	
	Input voltage range	±20 %	
	Reference current I _{ref}	1 A	
		Input current I _i	≤ 5 A

Data Sheet | Item Number: 879-3040

https://www.wago.com/879-3040



Input	
Current transformer (secondary)	1 A 5 A
Current transformer ratio	1:1 9999 : 1 / 5:5 9995 : 5
Frequency range	45 60 Hz

Communication	
Communication	Modbus [®] M-Bus <i>Bluetooth</i> ®
Interface	RS-485 (2-wire); 2x S0 interfaces (confi- gurable)
Rate control input	230 VAC
Indicators	LCD with backlight

Signal Processing

Supply

Power supply type

.

Measured variables (calculated) Measurement type (load profile) Active and reactive energy in supply and reference direction No

Measurement Error	
Accuracy class	Class B (= 1 % error); Active energy per EN 50470-3
Calibration validity period	8 years

via measurement circuit

Safety and protection	
Dielectric strength	4 kV; 1 min
Impulse withstand voltage (1.2/50 µs)	6 kV
Pollution degree	2
Protection type	IP51 / IP20; IP51 (front side); IP20 (connection)
Protection class	l

Connection data	
Connection type 1	Voltage/current
Connection technology	Push-in CAGE CLAMP®
WAGO connector	WAGO 2604 Series
Actuation type	Lever
Solid conductor	0.2 4 mm² / 24 12 AWG
Fine-stranded conductor	0.2 4 mm² / 24 12 AWG
Fine-stranded conductor; with insulated ferrule	0.25 2.5 mm²
Fine-stranded conductor; with uninsulated ferrule	0.25 2.5 mm²
Strip length	9 11 mm / 0.35 0.43 inches
Connection type 2	Communication/rate control input
Connection technology 2	Push-in CAGE CLAMP®
WAGO connector 2	WAGO 2604 Series
Actuation type 2	Lever
Solid conductor 2	0.2 4 mm² / 24 12 AWG
Fine-stranded conductor 2	0.2 4 mm² / 24 12 AWG
Fine-stranded conductor; with insulated ferrule 2	0.25 2.5 mm²
Strip length 2	9 11 mm / 0.35 0.43 inches

Data Sheet | Item Number: 879-3040 https://www.wago.com/879-3040



Physical data		
Width	36 mm / 1.417 inches	
Height	97 mm / 3.82 inches	
Depth	63 mm / 2.48 inches	
Note (dimensions)	Height with cover: 140 mm	

Mechanical Data	
Mounting type	DIN-35 rail

Material Data	
Housing material	PC 940A
Fire load	0 MJ
Weight	165 g

Environmental requirements	
Ambient temperature (operation at U_N)	-40 +70 °C
Relative humidity	\leq 75% (during storage \leq 95%)

Standards and specifications	
Conformity marking	CE
Standards/specifications	EN 50470-1/3 MID-compliant

Commercial data	
ETIM 8.0	EC002048
ETIM 7.0	EC002048
PU (SPU)	1 pcs
Packaging type	Box
Country of origin	CN
GTIN	4066966177299
Customs tariff number	90283019000

Downloads
Environmental Product Compliance
Compliance Search
Environmental Product Compliance 879-3040

Documentation

Data Sheet | Item Number: 879-3040

https://www.wago.com/879-3040

Manual			
Product Manual WAGO Energy Meters (MID)	V 1.6 26.09.2022	pdf 3668.98 KB	$\underline{\checkmark}$
Instruction Leaflet			
Energy consumption	V 1.15	pdf	1

16.02.2022



Bid Text		
879-3040	xml 6.84 KB	\downarrow
879-3040	docx 29.50 KB	\downarrow
ausschreiben.de 879-3040		\downarrow

Application Notes			
Application Note elCOCH	KPIT		
e!COCKPIT Application	2021-11-08 06.12.2021	pdf 930.71 KB	\downarrow
Measurement			<u> </u>

934.38 KB

 \downarrow


CAD/CAE-Data

meter

CAD data	
2D/3D Models 879-3040	$\underline{\downarrow}$

CAE data	
EPLAN Data Portal 879-3040	\downarrow
ZUKEN Portal 879-3040	$\underline{\downarrow}$

Libraries		
e!COCKPIT libraries		
e!COCKPIT Library De- scription WagoAppPo- werMeasurement	1.7.4.0 25.05.2021	pdf 1369.41 KB <u></u>



Data Sheet | Item Number: 879-3040

https://www.wago.com/879-3040

1.1.1.1 Plug-in current transformer

Plug-in current transformer; Primary rated

current: 100 A; Secondary rated current: 5

Plug-in current transformer; Primary rated

current: 250 A; Secondary rated current: 5

Plug-in current transformer; Primary rated

current: 500 A; Secondary rated current: 5

A; Rated power: 5 VA; Accuracy class: 0.5;

A; Rated power: 2.5 VA; Accuracy class:

A; Rated power: 2.5 VA; Accuracy class:

Item No.: 855-305/100-209

0.5; for billing purposes

Item No.: 855-405/250-209

0.5; for billing purposes

Item No.: 855-305/500-509

for billing purposes





Plug-in current transformer; Primary rated current: 150 A; Secondary rated current: 5 A; Rated power: 2.5 VA; Accuracy class: 0.5; for billing purposes



Item No.: 855-305/250-509 Plug-in current transformer; Primary rated current: 250 A; Secondary rated current: 5 A; Rated power: 5 VA; Accuracy class: 0.5; for billing purposes



Item No.: 855-405/500-509 Plug-in current transformer; Primary ra-

ted current: 500 A; Secondary rated current: 5 A; Rated power: 5 VA; Accuracy class: 0.5; for billing purposes

Item No.: 855-405/200-209

Plug-in current transformer; Primary rated current: 200 A; Secondary rated current: 5 A; Rated power: 2.5 VA; Accuracy class: 0.5; for billing purposes

-



Item No.: 855-305/400-509

Plug-in current transformer; Primary rated current: 400 A; Secondary rated current: 5 A; Rated power: 5 VA; Accuracy class: 0.5; for billing purposes



Item No.: 855-305/600-509

Plug-in current transformer; Primary rated current: 600 A; Secondary rated current: 5 A; Rated power: 5 VA; Accuracy class: 0.5; for billing purposes



Item No.: 855-305/200-509

Plug-in current transformer; Primary rated current: 200 A; Secondary rated current: 5 A; Rated power: 5 VA; Accuracy class: 0.5; for billing purposes



Item No.: 855-405/400-509

Plug-in current transformer; Primary rated current: 400 A; Secondary rated current: 5 A; Rated power: 5 VA; Accuracy class: 0.5; for billing purposes



Item No.: 855-405/600-509

Plug-in current transformer; Primary rated current: 600 A; Secondary rated current: 5 A; Rated power: 5 VA; Accuracy class: 0.5; for billing purposes

Subject to changes. Please also observe the further product documentation!