

FEATURES

- Black Neoprene Rubber
- Flexible
- Durable
- Customisable
- Resistant to ozone, sunlight and atmospheric ageing

RS PRO Black Rubber Sheet, 1m x 2m x 6mm

RS Stock No.: 733-6744



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



Product Description

Introducing a series of neoprene rubber sponge sheets from RS PRO. These black neoprene rubber sheets are suitable for use, both indoor & outdoor, offer moderate resistance to atmospheric ageing, sunlight, oils, and greases.

RS PRO Rubber Sheet Options

- 1 m x 2 m x 1.5mm RS Stock no: 733-6753
- 1 m x 2 m x 1.5mm RS Stock no: 733-6731
- 1 m x 2 m x 3mm RS Stock no: 733-6757
- 1 m x 2 m x 16mm RS Stock no: 733-6741
- 1 m x 2 m x 3mm RS Stock no: 733-6735
- 1 m x 2 m x 6mm RS Stock no: 733-6744
- 1 m x 2 m x 6mm RS Stock no: 733-6766
- 1 m x 2 m x 10mm RS Stock no: 733-6747
- 1 m x 2 m x 10mm RS Stock no: 733-6769
- 1 m x 2 m x 20mm RS Stock no: 733-6750
- 1 m x 2 m x 25mm RS Stock no: 103-4059

General Specifications

| Colour | Black |
|---------------------------------|---|
| Density | 122kg/m³ |
| Suitability | Animal Oil, Cold Water, Dilute Acid, Dilute Alkali, Ethylene Glycol, Fuel, Hot Water, Vegetable Oil |
| Elongation | >180% |
| Water Absorption | 0.8 |
| Compression Set (50% 22h 20°C) | 19.10% |
| Resistance to Air+UV | Excellent |
| Resistance to Oil | Poor |
| Resistance to Acids | Good |
| Environmental Protection | CFC and HFC FREE / CAN BE RECYCLED |
| Application | Sound-proofing, Noise and Heat insulation |



Mechanical Specifications

| Length | 1m |
|------------------|-----------|
| Thickness | 6mm |
| Width | 2m |
| Tensile Strength | >500KN/m² |

Operation Environment Specifications

| Maximum Operating Temperature | 85°C |
|-------------------------------|-------|
| Minimum Operating Temperature | -40°C |

Approvals

| Flammability Rating | FMVSS 302, UL94 HBF |
|---------------------|---------------------|