## Maxi free-standing Beacons / Revolving Signal Light 884 Rotating Beacon Fresnel 115-230VAC RD



i

Part No.: 884.130.60



MECHANICAL DATA	
Height	218 mm
Diameter	142 mm
Materials	PC PC/ABS
Dome colour	Red
Housing colour	Black
Protection category	IP65
Connection	Screw terminals
cross-sectional area maximum	1,50mm² / 16AWG
Cable entry	Rubber pinch
Cable entry minimum	d = 5 mm
Cable entry maximum	d = 7 mm
Tension relief	Pull-out protection
Type of fixing	Base mounting
Working temperature minimum	-30°C
Working temperature maximum	+50°C
Weight with packaging	809 g
Product weight	721 g
ELECTRICAL DATA	
Operating voltage	115-230V
Operating voltage type	AC
	AC 50Hz
Operating voltage type	
Operating voltage type Operating voltage frequency	50Hz
Operating voltage type Operating voltage frequency Operating voltage tolerance	50Hz +/- 10%
Operating voltage type Operating voltage frequency Operating voltage tolerance Rated operational voltage	50Hz +/- 10% 230 VAC
Operating voltage type Operating voltage frequency Operating voltage tolerance Rated operational voltage Rated operational current	50Hz +/- 10% 230 VAC 95 mA
Operating voltage type Operating voltage frequency Operating voltage tolerance Rated operational voltage Rated operational current Rated inrush current	50Hz +/- 10% 230 VAC 95 mA 1.400 mA
Operating voltage type Operating voltage frequency Operating voltage tolerance Rated operational voltage Rated operational current Rated inrush current Protection class	50Hz +/- 10% 230 VAC 95 mA 1.400 mA Protection class 2
Operating voltage type Operating voltage frequency Operating voltage tolerance Rated operational voltage Rated operational current Rated inrush current Protection class Pollution degree	50Hz +/- 10% 230 VAC 95 mA 1.400 mA Protection class 2 3
Operating voltage type Operating voltage frequency Operating voltage frequency Rated operational voltage Rated operational current Rated inrush current Protection class Pollution degree Overvoltage category	50Hz +/- 10% 230 VAC 95 mA 1.400 mA Protection class 2 3 II
Operating voltage type Operating voltage frequency Operating voltage tolerance Rated operational voltage Rated operational current Rated inrush current Protection class Pollution degree Overvoltage category Isolation voltage	50Hz +/- 10% 230 VAC 95 mA 1.400 mA Protection class 2 3 II
Operating voltage type Operating voltage frequency Operating voltage frequency Rated operational voltage Rated operational current Rated inrush current Protection class Pollution degree Overvoltage category Isolation voltage OPTICAL DATA	50Hz +/- 10% 230 VAC 95 mA 1.400 mA Protection class 2 3 II Ui = 250V; Uimp = 2.500V
Operating voltage type Operating voltage frequency Operating voltage frequency Rated operational voltage Rated operational current Rated inrush current Protection class Pollution degree Overvoltage category Isolation voltage OPTICAL DATA Light source	50Hz +/- 10% 230 VAC 95 mA 1.400 mA Protection class 2 3 II Ui = 250V; Uimp = 2.500V
Operating voltage type Operating voltage frequency Operating voltage frequency Rated operational voltage Rated operational current Rated inrush current Protection class Pollution degree Overvoltage category Isolation voltage OPTICAL DATA Light source Light colour	50Hz +/- 10% 230 VAC 95 mA 1.400 mA Protection class 2 3 II Ui = 250V; Uimp = 2.500V

For additional installation and mounting information, refer to the appropriate user guide at www.werma.com. This printed copy is for information only and is subject to alteration.

i


## Maxi free-standing Beacons / Revolving Signal Light 884 Rotating Beacon Fresnel 115-230VAC RD

APPROVAL DATA	
Conforms with CE	Yes
WEEE	Yes
Conforms with RED directive	No
Conform with ATEX-directive	No
Conforms with CCC-Ex	No
Conforms with CCC	Yes
Conforms with UL	No
Conforms with FCC	No
Conforms with IC	No
EAC certificate available	Yes
Conforms with UKCA (Importer)	No
Conforms with CMIM	No
Conforms with AS-I	No
Conforms with GL	No
Conforms with RoHS CN	No
Conforms with VdS	No

For additional installation and mounting information, refer to the appropriate user guide at www.werma.com. This printed copy is for information only and is subject to alteration.

ļ

Maxi free-standing Beacons / Revolving Signal Light 884 Rotating Beacon Fresnel 115-230VAC RD



For additional installation and mounting information, refer to the appropriate user guide at www.werma.com. This printed copy is for information only and is subject to alteration.