

VSPC RS485 2CH

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Under the protection of the data protection RS 485 come the following signals:

- Protection for wire connected serial data transmission – RS 485 or RS 422
- Pluggable arrester, with no-interrupt and impedance-neutral plug-in and pull-out
- Low residual voltage
- Can be used in accordance with the IEC 62305 and IEC61643-22 installation standards
- Can be tested with the V-TEST testing device
- Integrated PE foot, safely discharges up to 20 kA (8/20 μ s) and 2.5 kA (10/350 μ s) to PE

General ordering data

| | |
|------------|--|
| Version | Surge protection for instrumentation and control, without warning function / function indicator, $U_p(L/N-PE)$ 250 V |
| Order No. | 8924670000 |
| Type | VSPC RS485 2CH |
| GTIN (EAN) | 4032248696314 |
| Qty. | 1 pc(s). |

Creation date May 19, 2022 12:03:49 PM CEST

Catalogue status 06.05.2022 / We reserve the right to make technical changes.

VSPC RS485 2CH

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|---------|-----------------|------------|
| Depth | 69 mm | Depth (inches) | 2.717 inch |
| Height | 90 mm | Height (inches) | 3.543 inch |
| Width | 17.8 mm | Width (inches) | 0.701 inch |
| Net weight | 27.5 g | | |

Temperatures

| | | | |
|---------------------|----------------|-----------------------|----------------|
| Storage temperature | -40 °C...80 °C | Operating temperature | -40 °C...70 °C |
| Humidity | 5...96 % | | |

Probability of failure

| | | | |
|-----------------|-------------|-----------------------------------|---------|
| SIL PAPER | SIL Paper | SIL in compliance with IEC 61508 | 3 |
| MTTF | 2,003 Years | SFF | 92.54 % |
| λ_{ges} | 57 | PFH in $1 \cdot 10^{-9}$ per hour | 4.25 |

Environmental Product Compliance

| | | | |
|------------|----------------|--|--|
| REACH SVHC | Lead 7439-92-1 | | |
|------------|----------------|--|--|

Rated data UL

| | | | |
|----------------------|---------|----------------|---------------------|
| Certificate No. (UL) | E311081 | UL certificate | UL 497b Certificate |
|----------------------|---------|----------------|---------------------|

CSA protection data

| | | | |
|-------------------------------|-------|---------------------------------|-----------|
| Gas group C | IIB | Gas group D | IIA |
| Gas groups A, B | IIC | Input voltage, max. U_i | 6.4 V |
| Internal capacity, max. C_i | 11 nF | Internal inductance, max. L_i | 0 μ H |

General data

| | | | |
|---------------------------|--------|---------|--|
| Colour | orange | Design | Terminal, miscellaneous |
| Protection degree | IP20 | Segment | Measurement - Monitoring - Setting |
| UL 94 flammability rating | V-0 | Version | without warning function / function indicator |

Insulation coordination acc. to EN 50178

| | | | |
|--------------------|---|------------------------|-----|
| Pollution severity | 2 | Surge voltage category | III |
|--------------------|---|------------------------|-----|

VSPC RS485 2CH

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Rated data IEC / EN

| | | | |
|--|-----------------------|---|-----------------------|
| Discharge current I_{max} (8/20 μ s) GND-PE | 10 kA | Discharge current I_{max} (8/20 μ s) wire-PE | 2 x 10 kA |
| Discharge current I_{max} (8/20 μ s) wire-wire | 10 kA | Discharge current I_n (8/20 μ s) GND-PE | 2.5 kA |
| Discharge current I_n (8/20 μ s) wire-PE | 2.5 kA | Discharge current I_n (8/20 μ s) wire-wire | 2.5 kA |
| Insertion loss | 113.7 MHz | Lightning test current, I_{imp} (10/350 μ s) GND-PE | 0.2 kA |
| Lightning test current, I_{imp} (10/350 μ s) Wire-PE | 2 x 0.2 kA | Lightning test current, I_{imp} (10/350 μ s) wire-wire | 0.2 kA |
| Max. continuous voltage, U_c (AC) | 5 V | Max. continuous voltage, U_c (DC) | 6.4 V |
| Number of poles | 1 | Overload - failure mode | Modus 2 |
| Protection level U_p (typ.) | 250 V | Protection level on output side Wire-PE 1kV/ μ s, typically | 10 V |
| Protection level on output side Wire-wire 1 kV/ μ s, typically | 10 V | Protection level on output side Wire-wire 8/20 μ s, typically | 15 V |
| Protection level, U_p GND - PE | 500 V | Protection level, U_p wire - PE | 35 V |
| Protection level, U_p wire - wire | 15 V | Pulse-reset capacity | \leq 20 ms |
| Rated current I_N | 450 mA | Rated voltage (AC) | 5 V |
| Rated voltage (DC) | 5 V | Requirements category acc. to IEC 61643-21 | C1, C2, C3, D1 |
| Signal transmission properties (-3 dB) | 113.6 MHz | Signalling contact | No |
| Standards | IEC 61643-21 | Surge current-carrying capacity C1 | < 1 kA 8/20 μ s |
| Surge current-carrying capacity C2 | 5 kA 8/20 μ s | Surge current-carrying capacity C3 | 100 A 10/1000 μ s |
| Surge current-carrying capacity D1 | 2.5 kA 10/350 μ s | Voltage type | AC/DC |
| Volume resistance | 2.20 Ω | | |

Further details of approvals

GOST certificate GOST-Zertifikat

Connection data

Type of connection Pluggable in VSPC BASE

Ratings IECEx/ATEX/cUL

cUL certificate cUL Certificate

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000943 | ETIM 7.0 | EC000943 |
| ETIM 8.0 | EC000943 | ECLASS 9.0 | 27-13-08-07 |
| ECLASS 9.1 | 27-13-08-07 | ECLASS 10.0 | 27-13-08-07 |
| ECLASS 11.0 | 27-13-08-07 | ECLASS 12.0 | 27-17-90-90 |

VSPC RS485 2CH

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Tender specification sheets

| Long specification | Surge protection plug for use in connection with the base element VSPC BASE 2CL for two floating-ground driven signal cables and ground, e.g. for bus systems. Two-stage protection circuit consisting of coarse protection, decoupling resistors and fine protection between the signal wires and additional coarse common mode voltage protection to earth. Mechanical identification of the plug to the base element according to the switching type and rated voltage. Protected plug with coding pin and counter-profile for the base element. It is possible to mark the plug. | Short specification |
|--------------------|--|--|
| | | Surge protection plug for base element VSPC BASE 2CL, transverse voltage coarse and fine protection for two floating-ground powered IT signal cables, coarse common mode voltage protection to earth. Version: 5V DC |

Important note

| | |
|---------------------|--|
| Product information | Mode 2: State where the voltage-limiting part of the SPD was short-circuited due to a very low impedance within the SPD. The line is inoperable, but the measuring equipment is still protected by means of a short-circuit. |
|---------------------|--|

Approvals

Approvals



| | |
|-----------------------|---------|
| ROHS | Conform |
| UL File Number Search | E311081 |

Downloads

| | |
|---|--|
| Approval/Certificate/Document of Conformity | SIL Paper EU Konformitätserklärung / EU Declaration of Conformity |
| Engineering Data | CAD data - STEP |
| Engineering Data | EPLAN, WSCAD |
| User Documentation | Beipackzettel / Instruction sheet |
| Catalogues | Catalogues in PDF-format |
| Brochures | |


VSPC RS485 2CH

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Drawings



Electric symbol




Circuit diagram

| Cate- gory | Testing pulse | Surge voltage | Surge current | Pulse Type |
|------------|--------------------|-------------------------|-------------------------------|--|
| C1 | Quick- rising edge | 0.5 - 2 kV 1.2/50 µs | 0.25 - 1 kA 8/20 µs | 300 Surge voltage arrester |
| C2 | Quick- rising edge | 2 - 10 kV 1.2/50 µs | 1 - 5 kA 8/20 µs | 10 Surge voltage arrester |
| C3 | Quick- rising edge | ≥ 1 kV 1 kV/µs | 10 - 100 A 10/10000 µs | 300 Surge voltage arrester |
| D1 | High power | ≥ 1 kV | 0.5 - 2.5 kA mit 10/350 µs | 2 Arrester for lightning current and surge voltages |

Discharge capacity



Komplettmodul direkte Erdung



Komplettmodul indirekte Erdung
Komplettmodul