



## **Dimensions: [mm]**












Scale - 5:1

## **Product Marking:**

Start of Winding	•
Marking	332

## **Recommended Land Pattern: [mm]**



Scale - 5:1

## **Electrical Properties:**

Properties	Test conditions		Value	Unit	Tol.
Inductance	100 kHz/ 1 V	L	3300	μΗ	±10%
Rated Current	$\Delta T = 40 \text{ K}$	I <sub>R</sub>	0.1	А	max.
Saturation Current	IΔL/LI < 30 %	I <sub>SAT</sub>	0.15	Α	typ.
DC Resistance	@ 20 °C	R <sub>DC</sub>	21600	mΩ	±20%
Self Resonant Frequency		f <sub>res</sub>	1	MHz	typ.

# Schematic:



## **General Information:**

It is recommended that the temperature of the component does not exceed +125°C under worst case conditions

Ambient Temperature (refering to $\mathbf{I}_{\mathrm{R}}$ )	-40 °C up to +85 °C
Operating Temperature	-40 °C up to +125 °C
Storage Temperature (in original packaging)	-20°C up to +60°C, 75% RH max.

Test conditions of Electrical Properties: +20°C, 33% RH if not specified differently

Würth	Elektronik	eiSos	GmbH	&	Co.	KG
FMC 8	Inductive	Soluti	ons			

Max-Eyth-Str. 1 74638 Waldenburg Germany Tel. +49 (0) 79 42 945 - 0

www.we-online.com eiSos@we-online.com



CREATED		CHECKED	GENERAL TOLERANCE	PROJECTION METHOD		
KaS		JRS	DIN ISO 2768-1m	METHOD	<del>- 10</del> -	
					i	
DESCRIPTION	M					

**WE-LQS SMD Power Inductor** 

## **Typical Impedance Characteristics: Typical Inductance vs. Current Characteristics:** 3,500 1000000 3,000 100000 2,500 10000 Impedance [Ω] Inductance [µH] 2,000 1000 1,500 100 1,000 10 500 1000 10 100 10000 100000 1000000 Frequency [KHz] 0.00 0.05 0.10 0.15 0.20 0.25 0.30 Current [A] GENERAL TOLERANCE PROJECTION METHOD CHECKED Würth Elektronik eiSos GmbH & Co. KG CREATED **EMC & Inductive Solutions** KaS JRS DIN ISO 2768-1m Max-Eyth-Str. 1 74638 Waldenburg **WE-LQS SMD Power Inductor** Tel. +49 (0) 79 42 945 - 0

WÜRTH ELEKTRONIK

www.we-online.com

eiSos@we-online.com

ORDER CODE

DATE (YYYY-MM-DD)

2016-06-23

REVISION

5040

001.000

STATUS

Valid

74404054332


BUSINESS UNIT


eiSos

PAGE

2/6

## Packaging Specification - Tape and Reel: [mm]






W3.


W2

W1 close to center

packaging is reffered to the international standard IEC 60286-3:2013

	A0	B0	W	T	T1	T2	K0	P0	P1	P2	D0	D1	E1	E2	F	Tape type 2a	Packaging unit
tolerance	typ.	typ.	+0,3/ -0,1	ref.	max.	typ.	typ.	±0,1	±0,1	±0,05	+0,1/ -0,0	min.	±0,1	min.	±0,05		pcs.
value	5.30	5 30	12.00	0.40	0.10	4.70	4.20	4.00	8 00	2.00	1.50	1.50	1 75	10.25	5.50	Polyetyrono	1500






Pull-of force 12 mm 0,1 N - 1,3 N Tape width



Tolerance

Tape width

# **Classification Reflow Profile for SMT components:**



## **Classification Reflow Soldering Profile:**

Profile Feature		Value
Preheat Temperature Min	T <sub>s min</sub>	150 °C
Preheat Temperature Max	T <sub>s max</sub>	200 °C
Preheat Time $t_s$ from $T_{s  min}$ to $T_{s  max}$	t <sub>s</sub>	60 - 120 seconds
Ramp-up Rate (T <sub>L</sub> to T <sub>P</sub> )		3 °C/ second max.
Liquidous Temperature	T <sub>L</sub>	217 °C
Time $t_L$ maintained above $T_L$	t <sub>L</sub>	60 - 150 seconds
Peak package body temperature	T <sub>p</sub>	see table below
Time within 5°C of actual peak temperaure	t <sub>p</sub>	20 - 30 seconds
Ramp-down Rate (T <sub>L</sub> to T <sub>P</sub> )		6 °C/ second max.
Time 25°C to peak temperature		8 minutes max.

refer to IPC/ JEDEC J-STD-020E

# **Package Classification Reflow Temperature:**

Properties	Volume mm³ <350	Volume mm <sup>3</sup> 350-2000	Volume mm³ >2000
PB-Free Assembly   Package Thickness < 1.6 mm	260 °C	260 °C	260 °C
PB-Free Assembly   Package Thickness 1.6 mm - 2.5 mm	260 °C	250 °C	245 °C
PB-Free Assembly   Package Thickness ≥ 2.5 mm	250 °C	245 °C	245 °C

refer to IPC/ JEDEC J-STD-020E

Würth Elektronik eiSos GmbH & Co. KG EMC & Inductive Solutions		CREATED KaS	CHECKED JRS		GENERAL TOLERANCE DIN ISO 2768-1m		PROJECTION METHOD		
Max-Eyth-Str. 1 74638 Waldenburg Germany Tel. +49 (0) 79 42 945 - 0		WE-LQS	SMD Pov	ver Inc	ductor				
www.we-online.com eiSos@we-online.com						ORDER CODE <b>74404</b>	05433	32	
	WÜRTH ELEKTRONIK	5040	001.000	status Valid		DATE (YYYY-MM-DE 2016-06-23		BUSINESS UNIT eiSos	PAGE 4/6

# **Cautions and Warnings:**

# The following conditions apply to all goods within the product series of WE-LQS of Würth Elektronik eiSos GmbH & Co. KG:

#### General:

The usage and operation of the product within ambient conditions, which probably alloy or harm the wire isolation, has to be avoided.

If the product is potted in customer applications, the potting material might shrink during and after hardening. The product is exposed to the pressure of the potting material with the effect that the core, wire and termination is possibly damaged by this pressure and so the electrical as well as the mechanical characteristics are endangered to be affected. After the potting material is cured, the core, wire and termination of the product have to be checked if any reduced electrical or mechanical functions or destructions have occurred.

The responsibility for the applicability of customer specific products and use in a particular customer design is always within the authority of the customer. All technical specifications for standard products do also apply to customer specific products.

Cleaning agents that are used to clean the customer application might damage or change the characteristics of the component, body, pins or termination.

Direct mechanical impact to the product shall be prevented as the core material could flake or in worst case it could break.

## **Product specific:**

Follow all instructions mentioned in the data sheet, especially:

- The soldering profile has to be complied with according to the technical reflow soldering specification, otherwise this will void the
  warranty.
- All products shall be used before the end of the period of 12 months based on the product date code, if not a 100% solderability can't
  be ensured.
- Violation of the technical product specifications such as exceeding the nominal rated current will void the warranty.

The general and product specific cautions comply with the state of the scientific and technical knowledge and are believed to be accurate and reliable; however, no responsibility is assumed for inaccuracies or incompleteness.

Würth Elektronik eiSos GmbH & Co. KG EMC & Inductive Solutions		CREATED KaS	JRS		GENERAL TOLERANCE DIN ISO 2768-1m		PROJECTION METHOD		
Max-Eyth-Str. 1 74638 Waldenburg Germany Tel. +49 (0) 79 42 945 - 0	WE-LQS	SMD Pov	ver Inc	ductor					
www.we-online.com eiSos@we-online.com					ORDER CODE <b>74404</b>	05433	32		
	WÜRTH ELEKTRONIK	5040	REVISION 001.000	status Valid		DATE (YYYY-MM-DD 2016-06-23	0	BUSINESS UNIT eiSos	PAGE 5/6

## **Important Notes**

# The following conditions apply to all goods within the product range of Würth Elektronik eiSos GmbH & Co. KG:

### 1. General Customer Responsibility

Some goods within the product range of Würth Elektronik eiSos GmbH & Co. KG contain statements regarding general suitability for certain application areas. These statements about suitability are based on our knowledge and experience of typical requirements concerning the areas, serve as general guidance and cannot be estimated as binding statements about the suitability for a customer application. The responsibility for the applicability and use in a particular customer design is always solely within the authority of the customer. Due to this fact it is up to the customer to evaluate, where appropriate to investigate and decide whether the device with the specific product characteristics described in the product specification is valid and suitable for the respective customer application or not.

## 2. Customer Responsibility related to Specific, in particular Safety-Relevant Applications

It has to be clearly pointed out that the possibility of a malfunction of electronic components or failure before the end of the usual lifetime cannot be completely eliminated in the current state of the art, even if the products are operated within the range of the specifications. In certain customer applications requiring a very high level of safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health it must be ensured by most advanced technological aid of suitable design of the customer application that no injury or damage is caused to third parties in the event of malfunction or failure of an electronic component. Therefore, customer is cautioned to verify that data sheets are current before placing orders. The current data sheets can be downloaded at www.we-online.com.

#### 3. Best Care and Attention

Any product-specific notes, cautions and warnings must be strictly observed. Any disregard will result in the loss of warranty.

#### 4. Customer Support for Product Specifications

Some products within the product range may contain substances which are subject to restrictions in certain jurisdictions in order to serve specific technical requirements. Necessary information is available on request. In this case the field sales engineer or the internal sales person in charge should be contacted who will be happy to support in this matter.

#### 5. Product R&D

Due to constant product improvement product specifications may change from time to time. As a standard reporting procedure of the Product Change Notification (PCN) according to the JEDEC-Standard inform about minor and major changes. In case of further queries regarding the PCN, the field sales engineer or the internal sales person in charge should be contacted. The basic responsibility of the customer as per Section 1 and 2 remains unaffected.

## 6. Product Life Cycle

Due to technical progress and economical evaluation we also reserve the right to discontinue production and delivery of products. As a standard reporting procedure of the Product Termination Notification (PTN) according to the JEDEC-Standard we will inform at an early stage about inevitable product discontinuance. According to this we cannot guarantee that all products within our product range will always be available. Therefore it needs to be verified with the field sales engineer or the internal sales person in charge about the current product availability expectancy before or when the product for application design-in disposal is considered. The approach named above does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.

## 7. Property Rights

All the rights for contractual products produced by Würth Elektronik eiSos GmbH & Co. KG on the basis of ideas, development contracts as well as models or templates that are subject to copyright, patent or commercial protection supplied to the customer will remain with Würth Elektronik eiSos GmbH & Co. KG does not warrant or represent that any license, either expressed or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, application, or process in which Würth Elektronik eiSos GmbH & Co. KG components or services are used.

#### 8. General Terms and Conditions

Unless otherwise agreed in individual contracts, all orders are subject to the current version of the "General Terms and Conditions of Würth Elektronik eiSos Group", last version available at www.we-online.com.

