

Datasheet

RS Pro 2P + E DIN 43650 A Solenoid Connector, Female, Screw, 10A, 230 V ac

RS Stock No: **896-2063**



Product Details

RS Pro 2P+E DIN 43650 A solenoid connector features transparent polycarbonate construction with a nitrile/silicon gasket. It operates at a voltage rating of 230 V ac, current rating of 10 A and temperature rating of 0 to 90°C. This screw mount, female connector has type A sockets and comes with PG-P gland. It has maximum contact resistance of 20 mΩ.

Features and Benefits

- A selection of 2 pole and earth illuminated DIN connector sockets in a variety of voltage ratings
- Transparent polycarbonate construction, with a nitrile/silicon gasket
- 2 Pole + earth
- Type A socket type

Specifications:

Cable Gland Size	PG9
Colour	Transparent
Current Rating	10 A
DIN 43650 Type	DIN 43650 A
Gender	Female
Indicator Light	Yes
Mounting Type	Screw Mount
Pole Format	2P+E
Voltage Rating	230 V ac
Body Material	PC
Contact Material	Copper Alloy, Tin Plated
Contact Resistance	20 mΩ
Gasket Material	Nitrile/Silicone
HV Breakdown Test	2 kV ac
Insulation Resistance	100 x 10E6 Ω
Maximum Operating Temperature	+90°C
Minimum Operating Temperature	0°C
Socket Type	Type A