

#### **FEATURES**

- Dimensions of 30.3 mm (L) x 106 mm (W) x 30 mm (D)
- Maximum Voltage (AC) of 400 V
- Maximum Voltage (DC) of 250 V
- Cable connection
- Screw terminal
- DPST pole and throw configuration
- 0.1 N operating force
- Vertical orientation
- Minimum of 15,000,000 operations
- Snap minimum operating contact type
- Thermoplastic fibreglass housing type
- Roller lever actuator type
- Vertical mounting orientation

# RS PRO, Snap Limit Switch -Thermoplastic Fibreglass, NO/NC, Roller Lever, 400V, IP65

RS Stock No.: 902-6856



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



#### **Product Description**

Typically used to automatically control mechanical equipment, this type of snap limit switch often found in industrial applications. It can be used to start, stop, or slow down a device when a limit is reached. This could be when a part moves past a specific point, or when a pre-set number of objects is counted. It's also easy to install and has a simple visible operation.

#### **General Specifications**

Actuator Type	Roller
Pole and Throw Configuration	DPST
Normal State Configuration	NO/NC
Contact Type	Snap
Applications	Warehouses, Car Parks, Walkways, Construction
	areas, Parks and gardens, Home security

Materials	
Housing Material	Thermoplastic Fibreglass

#### **Electrical Specifications**

Maximum Current	10A
Maximum AC Voltage	400V
Maximum DC Voltage	250V
Frequency	50Hz
Connection Type	Cable
Terminal Type	Screw
Contact Resistance	<25mOhm max.
Rated Insulation Voltage	500V
Impulse Withstand Voltage	6KV



## **Mechanical Specifications**

Operating Force	0.1N
Mounting Orientation	Vertical
Dimensions	30.3mm x 106mm x 30mm
Length	30.3mm
Width	106mm
Depth	30mm
Mechanical Life (Minimum)	15000000 Operations

## **Operation Environment Specifications**

Maximum Operating Temperature	+70°C
Minimum Operating Temperature	-25°C
Ambient Temperature	-30°C to 80°C

## **Protection Category**

IP Rating	IP65
Class of Protection Against Electric Shock	Class II

## **Approvals**

Compliance/Certifications	UL, CSA, IMQ
Standards Met	CE, CSA, RU, UL







