

FEATURES

- Dimensions of 30.3 mm (L) x 230.5 mm (W) x 30 mm (D)
- Maximum voltage (AC) of 400 V
- Maximum voltage (DC) of 250 V
- Cable connection
- Screw terminal
- DPST pole and throw configuration
- Operating temperature range of -25 °C to +70°C
- 0.1N operating force
- Vertical orientation
- Minimum of 15,000,000 operations

RS PRO, Snap Limit Switch -Thermoplastic Fibreglass, NO/NC, Adjustable Lever, 400V, IP65

RS Stock No.: 902-6880



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



Product Description

This versatile snap limit switch is commonly used in industrial applications to automatically control mechanical equipment. It's easy to install and boasts a simple, visible operation. It can conveniently start, stop or slow down a device when a specific limit is reached. This could be when a pre-set number of objects is counted, for example, or when a part passes a pre-defined point.

General Specifications

| Actuator Type | Adjustable Lever |
|------------------------------|---|
| Pole and Throw Configuration | DPST |
| Normal State Configuration | NO/NC |
| Contact Type | Snap |
| Applications | Warehouses, Car Parks, Walkways, Construction areas, Parks and gardens, Home security |

| Materials | |
|------------------|--------------------------|
| Housing Material | Thermoplastic Fibreglass |

Electrical Specifications

| Maximum Current | 10A |
|---------------------------|--------------|
| Maximum AC Voltage | 400V |
| Maximum DC Voltage | 250V |
| Frequency | 50Hz |
| Connection Type | Cable |
| Terminal Type | Screw |
| Contact Resistance | <25mOhm max. |
| Rated Insulation Voltage | 500V |
| Impulse Withstand Voltage | 6KV |



Mechanical Specifications

| Operating Force | 0.1N |
|---------------------------|-------------------------|
| Mounting Orientation | Vertical |
| Dimensions | 30.3mm x 230.5mm x 30mm |
| Length | 30.3mm |
| Width | 230.5mm |
| Depth | 30mm |
| Mechanical Life (Minimum) | 15000000 Operations |

Operation Environment Specifications

| Maximum Operating Temperature | +70°C |
|-------------------------------|---------------|
| Minimum Operating Temperature | -25°C |
| Ambient Temperature | -30°C to 80°C |

Protection Category

| IP Rating | IP65 |
|--|----------|
| Class of Protection Against Electric Shock | Class II |

Approvals

| Compliance/Certifications | UL, CSA, IMQ |
|---------------------------|-----------------|
| Standards Met | CE, CSA, RU, UL |









