

#### **DATA SHEET** 10431000 EPIC® H-A 4 SS / H-A 4 BS Valid from: 07.07.2015

## Description

- H-A inserts with screw termination up to 2.5 mm<sup>2</sup> wire cross section.
- The small H-A 3 / H-A 4 are used whenever there is minimal space.
- Easy to service screw connection.
- Easy cable connection with strait cable entry in the contacts.



#### **General Characteristics**

Series H-A 4

Version Male/Female(Article 10432000)

**Number of Contacts** 

Screw termination: 0.5 - 2.5 mm<sup>2</sup> (2.5 mm<sup>2</sup> with **Termination Methods** conductor end sleeves depending on the crimping

Temperature Range -40°C to +100°C, short-term up to +125°C

## **Mechanical Characteristics**

Cycle of mechanical operation 100

#### **Electrical Characteristics**

400 V Rated Voltage, IEC 600 V Rated Voltage, UL Rated Voltage, CSA 600 V Rated Impulse Voltage 4 kV Rated Current, IEC 23 A Rated Current, UL 10 A Rated Current, CSA 10 A

Contact Resistance 1,5 - 4 mOhm

Degree of Soiling

#### **Materials and Surfaces**

Contacts Copper alloy, hard silver-plated

Insulating Body PΑ V0 Flammability Class according to UL 94

#### **Approvals**

UL-Approval, E-File-Number E75770 VDE-Approval, VDE-REG.-Nr. B437

#### Standard

**Product Standard** IEC 61984, UL 1977


Creator: MANU2/PDP	Document: DB10420000EN	Page <b>1</b> of <b>3</b>
Released: IVSE1/PDP	Version: 00	rage 1 of 3




DATA SHEET	10431000
EPIC <sup>®</sup> H-A 4 SS / H-A 4 BS	Valid from: 07.07.2015

# **Technical Drawings**





F



MAST1 / 11.02.2016 / freigegeben



DATA SHEET	10431000
EPIC <sup>®</sup> H-A 4 SS / H-A 4 BS	Valid from: 07.07.2015









Industrial machinery and plant engineering



Assembly time



Space requirement

#### Info

Robust power supply connector Straight cable entry into the contacts

## **Application range**

Machine and equipment manufacturings Control engineering

#### Remark

Photographs are not to scale and do not represent detailed images of the respective products.



DATA SHEET	19421900
EPIC <sup>®</sup> H-A 3 Agsv	Valid from: 20.07.2015

## Description

- Innovative metal and plastic housing design
- Housing in plastic or metal version. For power supply in the smallest possible space



## **General characteristics**

Series H-A 3

Version Surface-mount base M20

Locking mechanism single lever

Cable gland installed yes

Cable gland, clamping range 3.0 – 13.5 mm Protection rating IP 65 (locked)

Temperature range -40°C to +100°C, short-term up to +125°C

#### Materials and surfaces

Housing PA, grey

Lever zinc-plated steel

Gasket

## **Approvals**

VDE-Approval, VDE-REG.-Nr. B437

## **Standards**


Product Standard IEC 61984



DATA SHEET	19421900
EPIC <sup>®</sup> H-A 3 Agsv	Valid from: 20.07.2015

## **Drawings**











Industrial machinery and plant engineering



Mechanical resistance



Robust



Waterproof

## Info

Compact, robust metal- and plastic housings size H-A 3

## Application range

Machine and equipment manufacturing Control engineering Electronic laboratory

## Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Creator: MANA2/PDP	Document: DB19421900EN	Page 2 of 2
Released: IVSE1/PDP	Version: 00	rage Z OI Z