

### **FEATURES**

- Fits a standard XLR cutout
- Can be mounted from front or back
- Low rear profile ensures space saving
- Matt black finish frame

# RS PRO USB Connector, Panel Mount, Female to Male 3.0 B to A, Plug In, Straight-Dual Port

**RS Stock No.: 916-0224** 



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



**Product Description** 

Brought to you under the trusted RS PRO offer, this metal USB feed through connector allows you to connect and adapt different USB types through a sturdy panel mount connection that is designed to fit within a standard XLR format chassis.

Available in this Range:

<u>907-5621</u> - USB 3.0 A to A Feed through Connector with countersunk screw holes <u>907-5624</u> - USB 3.0 B to A Feed through Connector with countersunk screw holes. <u>907-5630</u> - USB 2.0 B to A Feed through Connector with countersunk screw holes <u>907-5637</u> - USB 2.0 A to B Feed through Connector with countersunk screw holes <u>907-5637</u> - USB 2.0 B to A Feed through Connector with countersunk screw holes <u>916-0215</u> - USB 3.0 A to A Feed through Connector <u>916-0224</u> - USB 3.0 B to A Feed through Connector <u>916-0227</u> - USB 2.0 B to A Feed through Connector <u>916-0221</u> - USB 2.0 B to A Feed through Connector <u>916-0221</u> - USB 2.0 A to A Feed through Connector <u>916-0220</u> - USB 2.0 A to A Feed through Connector

Gender	Female to Male	
Mounting Type	Panel Mount	
USB Type	B to A	
Termination Method	Plug In	
USB Version	3.0	
Body Orientation	Straight	
Number of Ports	2	
Contact Material	Metal	
Colour	Black	
Insert Material	ABS	
Frame Material	Nickel plated zinc diecast	
Shell Material	Nickel plated steel	
Applications	Computers, Tablets, Games consoles, Smart TVs, DVD and Blu-Ray players	

#### **General Specifications**




### Electrical Specifications

Current Rating	1.5A max.
Voltage Rating	30Vac
Contact Resistance	50mΩ max.
Insulation Resistance	20 MΩ min.
Dielectric withstanding voltage	500Vac

Operation	<b>Environment S</b>	pecifications

Minimum Operating Temperature	-20.0°C
Maximum Operating Temperature	50°C

Approvals	
Compliance/Contifications	Delle
Compliance/Certifications	RoHS







Description USB 3.0 A to USB 3.0 A, CSK hole.

Description USB 3.0 B to USB 3.0 A, CSK hole.









