




Product: GSA-U 3000 N ☑


GSA-U DIN standard receptacle with solder contacts: Form A, 4-pin (3+1PE), UL 1977, solder type; 400 V AC/DC, 16 A

# **Product Description**

GSA-U DIN standard receptacle with solder contacts: Form A, 4-pin (3+1PE), UL 1977, solder type; 400 V AC/DC, 16 A

## **Technical Drawing**





# **Technical Specifications**

## **Technical Data**

Product Family:	Valve Connectors	
Product Sub Family:	GSA-U	
Brand:	Hirschmann	
Connector Type:	Receptacle	
Connector Sub Type:	Rectangular molded receptacle with solder contacts	
Type of Contact / Gender:	Male	
Connector Design:	Straight	
Number of Pins:	3+PE	
Coding:	A	
Shielding:	Unshielded	
Attachment Type:	Central Screw	
Rated Voltage (UL):	300 V	
Rated Impulse Voltage:	4.0 kV	
Operating Voltage:	400 V AC/DC	
Rated Current*:	16 A	
Rated Current (UL)*:	15 A	
Contact Resistance:	≤ 10 mOhm	
Insulation Resistance:	> 10^9 Ohm	
Mating Cycles:	≤ 50	

Type of Connection:	Solder	
Conductor Cross Section:	0.08 - 1.5 mm <sup>2</sup>	
Ambient Temperature (Operation)*:	-40 °C - +125 °C	
Operating Temperature (UL):	max. + 90 °C	
Protection Degree / IP Rating**:	IP65 / IP67	
Design Standard:	DIN EN 175301-803-A, ISO 4400	
Pollution Degree:	3 acc. to DIN EN 60664-1 (VDE 0110-1)	
Clearance / Creepage Distance:	DIN EN 60664-1 (2008/01); VDE 0110-1	
Overvoltage Category:	III acc. to DIN EN 60664-1 (VDE 0110-1)	

#### **Materials**

Contact Base Material:	CuZn
Contact Plating:	Cu/Sn
Contact Bearer Material:	PA GF
Contact Bearer Color:	black
Flammability Class (Contact Bearer):	UL 94 HB
Housing Color:	black

## **Additional Technical Data**

Fastening torque (mounting screw):	(50-60) Ncm
Mounting:	M3 (2x)

## **Approvals**

UL-File:	E95522	
UL:	UL 1977; UR	
VDE:	yes	
SEV:	yes	

## Safety & Environmental Compliance

## Notes

Note Derating:	Notice derating	
Protection Degree / IP Rating Note:	** only if mounted and locked in combination with Hirschmann / Lumberg Automation connec	
Note:	Do not connect or disconnect under load.	

### Variants

Item #	Item Description
933379100	GSA-U 3000 N LO

### © 2021 Belden, Inc

All Rights Reserved

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.