

## FEATURES

- Black construction
- Sealed sleeve technology retains bearing lubricant
- Long life expectancy (more than 50,000 hours)

## RS PRO, 12 V dc, DC Axial Fan, 60 x 60 x 10mm, 35.7m<sup>3</sup>/h, 3W

RS Stock No.: 789-7860



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

Brought to you by RS PRO, a range of AC dual ball bearing axial fans offering a cost effective cooling solution without sacrificing on quality or reliability. Provided are a robust die-cast aluminium frame and an AC shaded pole impedance protected motor, these fans are ideal for a multitude of applications. All models are highly reliable and excellent quality

## General Specifications

<b>Air Flow</b>	18.7CFM
<b>Fan Speed</b>	4600rpm
<b>Static Pressure</b>	0.13in/H2O
<b>Noise Level</b>	37.6dB
<b>Direction of Curve</b>	Forward
<b>Frame</b>	PBT UL94V-0 Plastic
<b>Impeller</b>	PBT UL94V-0 Plastic
<b>Alarm Function</b>	No
<b>IP Rating</b>	IP44
<b>Applications</b>	Server racks, Electrical cabinets and enclosures; Production Lines, Ceiling fan/ventilation Desktop computers, Motor engines (radiator in a car), Generators, Air compressors

### Electrical Specifications

<b>Motor</b>	Brushless DC, Auto Cut off, Auto Restart, Polarity Protected
<b>AC or DC Operation</b>	DC
<b>Power Consumption</b>	3W
<b>Supply Voltage</b>	12VDC
<b>Rated Voltage</b>	12VDC
<b>Maximum Current</b>	250mA
<b>Dielectric Strength</b>	500VAC/min < 1mA
<b>Insulation Resistance</b>	10M ohm between lead wire and frame (500VDC)

### Mechanical Specifications

<b>Dimensions</b>	60mm x 60mm x10mm
<b>Height</b>	60mm
<b>Width</b>	60mm
<b>Depth</b>	10mm
<b>Bearing Type</b>	Sleeve
<b>Weight</b>	0.030Kg (0.06lbs)
<b>Life Expectancy</b>	50,000 hours (L10 at 25°C)

### Operation Environment Specifications

<b>Operating Temperature</b>	-10°C to 70°C
<b>Storage Temperature</b>	-40°C to 70°C

### Approvals

<b>Compliance/Certifications</b>	UL, cUL, TUV, UL94-V0
----------------------------------	-----------------------

## Axial Fans



LEAD WIRES : UL 1007, 26 AWG, L = 300 +/- 10 mm  
Red = Positive ; Black = Negative.

