SIEMENS

Data sheet

7KM2200-2EA30-1CA1

SENTRON, measuring device, 7KM PAC2200, LCD, L-L: 400 V, L-N: 230 V, 5 A, strd rail instr., 3-phase, M-Bus, apparent/ active/reactive energy, self-powered, screw terminals



Model	
Product brand name	SENTRON
Product designation	7KM PAC2200
Design of the product	basic
Product type designation	Measuring instrument
Type of measured value detection	complete

General technical data		
Size of Power Monitoring Device / company-specific	6MW	
Operating mode for measured value detection		
 automatic line frequency detection 	Yes	
• set at 50 Hz	No	
• set to 60 Hz	No	
Voltage curve	Sinusoidal or distorted	
Measurable line frequency / initial value	45 Hz	
Measurable line frequency / Full-scale value	65 Hz	
Measuring procedure / for voltage measurement	TRMS	

Supply voltage	
Type of voltage / of the supply voltage	self-powered

Protection class	
Protection class IP	
• Rear side	IP20
Electricity	
Measurable current / 2 / at AC / Rated value	5 A
Suitability	
Suitability for operation	Standard mounting rail device
Product function	
Product function	
• reactive power measurement	Yes
voltage measurement	Yes
Current measurement	Yes
 active power measurement 	Yes
Display and operation	
Design of the display	LCD
Number of keys	4
Communication	
Protocol	
• is supported	M-Bus
Fault limits	
Reference condition / for metering accuracy	In accordance with IEC61557-12, IEC62053-22 and IEC62053-23
Inputs Outputs	
Number of digital outputs	1
Number of digital inputs	1
Type of switching output	solid state
Type of electrical connection	
at the digital outputs	screw-type terminals
Operating conditions for digital inputs / external	Yes
voltage supply	
Measuring inputs	
Outer conductors and neutral conductors internal	1 ΜΩ
resistance / for voltage measurement	
Measurable supply voltage	
between (PE)N and L / at AC / minimum	46 V
between (PE)N and L / at AC / maximum	276 V
 between (PE)N and L / at AC / maximum rated value 	230 V
 between the outer conductors / at AC / maximum rated value 	400 V

Voltage measuring range extension / with external voltage transformers	No
Current measuring range extension / with external current transformers	Yes
Measuring category / for voltage measurement	CATIII
Supply voltage / between the outer conductors / at AC / maximum permissible	480 V
Continuous current / at AC / maximum permissible	10 A
Measuring category / for current measurement	CATIII
Zero-point suppression / for current measurement	10 mA
 for neutral conductor current 	45 mA
Relative measurable current / at AC	
• minimum	1 %
• maximum	120 %
Apparent power consumption / for current measurement	
with measuring range 5 A / per phase	0.5 V·A
Measuring procedure / for current measurement	TRMS
Measurable current / 1 / at AC / Rated value	1 A

Type of electrical connection

screw-type terminals • at the measurement inputs for voltage • at the measurement inputs for current screw-type terminals

Mechanical Design	
Height	90 mm
Width	108 mm
Depth	64 mm
Mounting position	any
Installation depth	70.8 mm
Mounting type / panel mounting	No

Declaration of Conformity



Information- and Downloadcenter (Catalogs, Brochures,...) http://www.siemens.com/lowvoltage/catalogs

Industry Mall (Online ordering system)
https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=7KM2200-2EA30-1CA1

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/ww/en/ps/7KM2200-2EA30-1CA1

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...) http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=7KM2200-2EA30-1CA1

CAx-Online-Generator

http://www.siemens.com/cax

Tender specifications

http://www.siemens.com/specifications



