



JUNCTION BOX

# Abox 040-L



## Abox 040-L

Junction box

**CUSTOMIZE**

93 x 93 x 55 mm  
Article number: 80490701

Junction box acc. to DIN EN 60670 (VDE 0606),  $U_i=690V$ , with self-sealing, soft inlet membranes, M20, seal range 2 - 16 mm

Grey, without terminal



## Technical data

### Measures

Width:	93 mm
Length:	93 mm
Height:	55 mm

### Material:

Cover:	polystyrene
material:	polystyrene
Box:	polystyrene, membrane out of TPE
Cover screw:	stainless steel V2A

### Entries

Pre-embossings, top:	2 x M20
Pre-embossings, left/right:	2 x M20
Pre-embossings, bottom:	1 x M20
Pre-embossings, rear side:	1 x M20

## Certificates



## Accessory

DMS M20/w - M20, white
Abox 025/040 KLS-2,5²/4² - Terminal block
BST M20/sw - Ventilation seal
Abox PST - Sealing kit
ADR M20 - Sealing ring
AST M20 - Attachment bushes
AST M20/or - Attachment bushes
BST M20 - Ventilation seal
DMS M20 - Double-membrane seals
DMS M20/sw - Double-membrane seals
GMU PA M20 - Lock nut
KS M20 - Combi set
KVR M20 - Cable gland



JUNCTION BOX

# Abox 040-L

## Other attributes

Entries:	8
Rated cross section:	4 mm <sup>2</sup>
Tackable:	No
Rated insulation voltage AC:	690 V
Explosion safety:	none
Functional integrity:	none
sealable:	Yes
Heavy metals-free:	Yes
PVC-free:	Yes
Silicone-free:	Yes
Ingress protection:	IP65 - acc. to EN 60529 / DIN VDE 0470-1
weatherproof:	No
Combustion behaviour acc. to UL 94:	HB acc. UL94
Combustion behaviour acc. to VDE:	650°C acc. VDE 0471/ EN 60695
Equipment:	None
Color:	Grey
Cover screw torque:	1 N m

KVR M20-GDB - Cable gland

KVR M20-GDB/MGM - Cable gland

KVR M20-GDB/MGM/sw - Cable gland

## Environmental attributes

Ambient temperature (min.):	-25 °C
Ambient temperature (max.):	40 °C
Ambient temperature (24 h):	35 °C
Max. rel. humidity at 25° C (short term):	95%
Max. rel. humidity at 40° C:	50%