

## Features

- High Speed signal transmission
- Input TTL Compatible
- Hinged shutter to prevent contamination
- PBT body

## RS PRO Optical Transmitter jack

RS Stock No.: 805-1687



RS PRO Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

This is a new design connector including traditional RCA and data link inner opto-electric components. Not only does the data link transmit electric digital signal but also a light signal.

The unit is operated at single +3V~ +5V and RCA input signal at  $\pm 0.5V$ . It has a maximum operating speed of 16Mbps. The unit has high performance at low dissipation current, steady light output and efficient light coupling.

### Applications

Audio equipment, DVD player, PC, Notebook, Sound card

## Device Selection Guide

Chip IC Material	Chip LED $\lambda$ p(nm)	Operating Voltage (Vcc)	Dissipation Current (mA)	Fibre Coupling Light Output (dBm)
Si	650	2.7~5.5	Typ. 4	Min -21 to Max -15

## Maximum Ratings ( $T_a = 25^\circ C$ )

Supply Voltage	Vcc	-0.5 to 7 V
DC Input Voltage	Vin	-0.5 to Vcc +0.5 V
Power Dissipation	P	120 mW
Storage Temperature	Tstg	-30 to +80°C
Operating Temperature	Topr	-20 to +70°C
Soldering Temperature	Tsol	260°C
Soldering Time		$\leq 5$ sec / 2 times

## Electro-Optical Specification

Operating Voltage (optic unit) (electrical unit)	Vcc	2.7 to 5.5 V 0.75 to 1.25 V
Peak Emission Wavelength	$\lambda_p$	640 to 670 nm
Transmission Speed		DC 16 Mbps (NRZ signal)
Transmission Distance		0.2 to 20 m (Using APF)
Pulse Width Distortion	$\Delta tw$	-15 to 15 ns (16Mbps NRZ Signal)
Fibre Coupling Light Output	Pf	-21 to -15 dBm. See measuring method
Dissipation Current	Icc	Typical 4 to 10 max mA. See measuring method
High Level Input Voltage	V <sub>IH</sub>	2v min

Low Level Input Voltage	V <sub>IL</sub>	0.8v max
Rise Time	t <sub>r</sub>	30ns Max.
Fall Time	t <sub>f</sub>	30ns Max.
Low to High propagation delay time	t <sub>PLH</sub>	100ns max
High to Low propagation delay time	t <sub>PLH</sub>	100ns max
Jitter	Δt <sub>j</sub>	Typical 1.5ns to max 15ns

## Reliability Tests

Sample test size: 22 pcs, no failures

Item	Test Condition	Test Hours / Cycle
Soldering Heat	260°C ± 5°C	5 sec. / 2 times
High temp & Humidity storage	Ta=40°C, 90%RH	500
High storage temp.	Ta=80°C	500
Low storage temp.	Ta=-30°C	500
Temperature cycling	-30°C ~ 80°C (30min) (5min) (30min)	20
High temp operation life	Ta=60°C, Vcc=5V ON	500
Repeated operation	500 times	Coupling force < 2kg 0.4kg < detaching force < 2kg
Terminal strength (tension)	Weight: 500g, 30 sec each terminal	
Terminal strength (bending)	Weight: 500g, 2 times each terminal	
Mechanical Shock	Acceleration: 1000m/s <sup>2</sup> Pulse width: 6ms, 3 times / X, Y, Z direction	
Vibration	Frequency range: 10~55Hz / sweep 1 min Overall amplitude: 1.5mm 2H / X, Y, Z direction	

I<sub>cc</sub> (dissipation current): CURRENT ATTENUATE DIFFERENCE < 20%

P<sub>f</sub> (fibre coupling light output): BRIGHTNESS ATTENUATION DIFFERENCE < 20%

T<sub>PLH</sub> (propagation L→H delay time): DELAY TIME DIFFERENCE < 20%

T<sub>PLH</sub> (propagation H→L delay time): DELAY TIME DIFFERENCE < 20%


T<sub>r</sub> (rise time): TIME DIFFERENCE < 20%

T<sub>f</sub> (fall time): TIME DIFFERENCE < 20%

## Approvals

Conforms to	EIAJ CP-1201 digital audio interface standard
Standards Met	RoHS


### Package Dimensions




**Notes:** 1.All dimensions are in millimeters.  
2.General Tolerance:±0.2mm

#### Pin Function

- 1. GND
- 2. Vcc
- 3. Vin
- 4. Positive
- 5. Negative



#### PCB Layout For Electrical Circuit




#### Notes:


- 1. Unit:mm
- 2. Unspecified tolerance: ±0.3mm
- 3.Substrate Thickness:1.6mm

## Measuring Method


### \*1 Measuring method of optical output coupling fiber



### \*2 Input voltage/power dissipation measuring method




### \*3 Pulse response and jitter measuring method



## Precautions for Using Method

1. Connect a by-pass capacitor (0.1 $\mu$ F) close to the optical jack within 7 mm of the unit lead frame.



2. Take proper electrostatic-discharge (ESD) precautions while handling these devices. These devices are sensitive to ESD.
3. Please follow the conditions described in the diagram below.

