Data Pack B Issued November 1996 1502297616




dc geared motor 63mm diameter

RS stock numbers 224-3647, 224-3653, 224-3596, 224-3625, 224-3603, 224-3619

Introduction

These motors have been designed and manufactured for incorporation into equipment or machines and are considered to be component parts of a larger system. The design and construction has taken in to account the provisions of the appropriate European Legislation for these items.



Technical data


| | | | ı |
|--------------------------|------------|------|------|
| Motor supply voltage | (Vdc) | 12 | 24 |
| Nominal output power | (W) | 27 | 27 |
| Nominal current | (A) | 3.6 | 1.9 |
| Starting torque | (mNm) | 600 | 600 |
| Starting current | (A) | 12 | 6.2 |
| Resistance | (Ω) | 1 | 3.9 |
| Inductive | (H) | 1.4 | 6.4 |
| Life | (h) | 5000 | 5000 |
| Maximum gearbox torque | (Nm) | 5 | 5 |
| Axial load (dynamic) | (daN) | 6 | 6 |
| Radial load (dynamic) | (daN) | 6 | 6 |
| Gearbox temperature rise | (°C) | 50 | 50 |
| Protection rating | | IP20 | IP20 |
| Weight | (g) | 1540 | 1540 |

12Vdc - Geared motor

| RS stock no. | Ratio | Final Speed (rpm) |
|--------------|---------|-------------------|
| 224-3647 | 24.5:1 | 73 |
| 224-3653 | 38.28:1 | 47 |

24Vdc - Geared motor

| RS stock no. | Ratio | Final Speed (rpm) |
|--------------|---------|-------------------|
| 224-3596 | 12.25:1 | 147 |
| 224-3625 | 24.5:1 | 73 |
| 224-3603 | 61.25:1 | 29.4 |
| 224-3619 | 122.5:1 | 14.7 |



The information provided in **RS** technical literature is believed to be accurate and reliable; however, RS Components assumes no responsibility for inaccuracies or omissions, or for the use of this information, and all use of such information shall be entirely at the user's own risk.

No responsibility is assumed by RS Components for any infringements of patents or other rights of third parties which may result from its use. Specifications shown in RS Components technical literature are subject to change without notice.

