

MCZ SC 0-20MA

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold



Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Product image



MCZ: The smallest solution

- The smallest analogue signal converter in terminal block format on the market
- Space-saving conversion of analogue signals in the control cabinet thanks to the slim, 6 mm wide module width
- Simple wiring with plug-in cross-connectors

General ordering data

Version	Limit value monitoring, Input : 0-20 mA, Output 2 x transistor
Order No.	8227350000
Type	MCZ SC 0-20MA
GTIN (EAN)	4008190193799
Qty.	10 pc(s).

MCZ SC 0-20MA

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmuller.com

www.weidmuller.com

Technical data

Dimensions and weights

Depth	63.2 mm	Depth (inches)	2.488 inch
Width	6 mm	Width (inches)	0.236 inch
Length	91 mm	Length (inches)	3.583 inch
Net weight	28 g		

Temperatures

Storage temperature	-25 °C...60 °C	Operating temperature	0 °C...50 °C
Operating temperature, min.	0 °C	Operating temperature, max.	50 °C
Humidity	40 °C / 93 % rel. humidity, no condensation		

Probability of failure

SIL in compliance with IEC 61508	None	MTTF	681 Years
----------------------------------	------	------	-----------

Input

Input current	0.5...20 mA	Input resistance, current	50 Ω
Number of inputs	1	Voltage drop	1 V

Output

Cut-off frequency (-3 dB)	100 Hz	Number of outputs	2
Switching thresholds	Via 2 potentiometers (12 turns)		

General data

Configuration	Potentiometer	Current consumption	15 mA
Galvanic isolation	Without isolation	Rail	TS 35
Step response time	< 250 μs (switching threshold at 90% of max. input signal; R _I ≤ 1 kΩ)	Temperature coefficient	max. 250 ppm/K
Type of connection	Tension-clamp connection	Voltage supply	24 V DC ± 20 %

Insulation coordination

EMC standards	EN 55011, EN 61000-6	Galvanic isolation	Without isolation
Insulation voltage input or output/rail	4 kV _{eff} / 1 min.		

Connection data

Type of connection	Tension-clamp connection	Clamping range, rated connection	1.5 mm ²
Clamping range, min.	0.5 mm ²	Clamping range, max.	1.5 mm ²

Classifications

ETIM 6.0	EC002654	ETIM 7.0	EC002654
ETIM 8.0	EC002654	ECLASS 9.0	27-21-01-22
ECLASS 9.1	27-21-01-22	ECLASS 10.0	27-21-01-22
ECLASS 11.0	27-21-01-22	ECLASS 12.0	27-21-01-22

MCZ SC 0-20MA

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technical data

Tender specification sheets

Long specification

Short specification

Trip amplifier for monitoring a 0...20 mA standard signal with two switching outputs
Trip amplifier in 6 mm width for analogue 0...20 mA standard signals with two PNP-transistor switch outputs for monitoring an upper and lower threshold (adjustable via potentiometer).

Dimensions: L/W/H
91/ 6/ 63.2 mm
Tension-clamp connection / Nominal cross-section 1.5 mm²
Protection degree: IP 20

Input
0.5...20 mA
Output
Double switching output PNP/ 50 mA per channel

Adjustable via potentiometer
Switching hysteresis of input 1 %
Step response time < 250 us (10...90 %)
Temperature coefficient < 250 ppm K
Auxiliary power 24 V DC +/- 20 %
Ambient temperature range 0°C...+50 °C
Approvals cURus, CSA

Type MCZ
SC 0-20MA

Trip amplifier for monitoring a 0...20 mA standard signal with two switching outputs
Trip amplifier in 6 mm width for analogue 0...20 mA standard signals with two PNP-transistor switch outputs for monitoring an upper and lower threshold (adjustable via potentiometer).

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	35d83707-6a3b-45b5-b9f8-6ba8184c863e

MCZ SC 0-20MA

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

Technical data

info@weidmueller.com

www.weidmueller.com

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E141197

Downloads

Approval/Certificate/Document of Conformity	Declaration of Conformity
Engineering Data	CAD data – STEP
Engineering Data	WSCAD
User Documentation	Instruction sheet
Catalogues	Catalogues in PDF-format
Brochures	

MCZ SC 0-20mA

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

Drawings

Connection diagram

