




ENGLISH

Datasheet

4-20mA remote wall mounted housing, Platinum Resistance Pt100 input with 1 metre lead

-50°C to +150°C or 0°C to +400°C ranges available



Housing moulded in general purpose ABS, the external fixing points provide a simple and rapid means of mounting sensors directly onto ducts, dispensing with the need for separate mounting plates.

Specifications

Head: High Impact ABS Plastic Construction

Transmitter: The RTD in-head mounted temperature transmitter connects to any standard

pt100 resistance sensor and converts the linearised temperature to a (4 to 20)

mA signal. (transmitter device has an ambient range of -40°C to +85°C)

Cable: 1 metre of 7/0.2mm Cable

Cable Termination: Bare tails

Туре	Cable	Cable	Cable	Transmitter	RS order
	Glands	Length (mm)	Insulation	Range	code
Pt100	M16	1000	PFA Teflon	-50°C to +150°C	872-2758
Pt100	M16	1000	F/G + SSOB	0°C to + 400°C	872-2751

RS198/0816

TRANSMITTER SPECIFICATION @ 20 °C

INPUT

Sensor Type PT100 100R @ 0°C 2 or 3 Wire Sensor Range (-200 to +850) °C (18 to 390) Ω

Sensor Connection Screw terminal

Minimum span (*1) 25°C

Linearisation BS EN 60751(IEC 751) standard /JISC 1604

Measurement Accuracy (*2) 0.2°C ± 0.05% of Reading

Thermal Drift $0.0025 \% / ^{\circ}C$ Excitation current <200 uA Lead Resistance effect $0.002 ^{\circ}C / \text{Ohm}$

Maximum lead Resistance 20 Ohms per leg

OUTPUT

Output Type 2 wire (4 to 20) mA current loop

Output range (4.0 to 20.0) mA
Output Connection Screw Terminal

Maximum output 21.5mA (in high burnout condition)
Minimum output <3.9 mA (in low burnout condition)

Accuracy (mA output /2000) or 5 uA

(Whichever is the greater)

Loop Voltage effect 0.2 uA / VThermal drift $1 \text{ uA / }^{\circ}\text{C}$

Maximum output load [(Vsupply-10)/21]K Ohms

(Example: 700 Ohms @ 24V)

GENERAL SPECIFICATION

Update time 500 ms

Response Time 1 second

Start-up time 4 seconds (I out < 4 mA during start up)

Warm-up time 1 minutes to full accuracy

Power Supply (10 to 30) Volts dc

PUSH BUTTON CONFIGURATION

A single push button and LED indicator allows the user to navigate a three menus, allowing configuration of the transmitter. The menus are as follow: -

Menu 1 Configure range.

Menu 2 Configure burnout direction.

Menu 3 Trim output current @ either 4 mA or 20 mA

ENVIRONMENTAL

Ambient operating range (-40 to +85) °C Ambient storage temperature (-50 to +90) °C

Ambient humidity range (10 to 90) % RH non condensing

Note *1 Any span may be selected; full accuracy is only guaranteed for spans greater than the minimum recommended

Note *2 Basic measurement accuracy includes the effects of calibration, linearisation and repeatability

What is the difference between a RTD and PRT sensor?


Nothing. RTD means resistance thermometer detector (the sensing element) and PRT means Platinum resistance thermometer (the whole assembly) i.e. a PRT

uses a RTD.

Need RTD Cable or Pt100/Pt1000 Detectors?

RTD Extension Cable – 4 core (10 or 25 metre reel)

Platinum Resistance Thermometer Extension Cable - Silicone Rubber Insulated



- Silicone rubber insulated cable for extending Platinum Resistance Thermometers
- Can be used to extend up to 4 wire RTD configurations
- Commonly used with Pt100 Ω thermometers but suitable with other types Pt130/500/1000 Ω etc.
- 4 core silicone rubber insulated 7/0.2mm tin plated copper conductors, twisted together with silicone rubber outer jacket
- Cores colour coded 2 x Red / 2 x White to IEC-751
- Good electrical and mechanical properties, highly flexible, resistant to oils, acids and other adverse fluids
- Good heat resistance up to 200°C
- Insulation rating -40°C to 200°C
- Supplied in 10 or 25 metre reel lengths

Туре	Conductors	mm²	Cores (4 core)	Jacket Reel Length	Allied Code	RS order Code
RTD	7/0.2mm	0.219	2x Red / 2 x White	Brown 10 metres	70657147	827-5823
RTD	7/0.2mm	0.219	2x Red / 2 x White	Brown 25 metres	70644361	455-424

Overall sheath Dimension (approx.)

4.0mmØ

RTD Extension Cable – 4 & 6 core PFA

Platinum Resistance Thermometer Extension Cable, PFA insulated & screened





4 core (cores: 2 x red / 2 white)

6 core (cores: 4 x red / 2 x white)

- PFA insulated cable for extending Platinum Resistance Thermometers
- High temperature to 260°C, extruded PFA Teflon® construction
- Commonly used for Pt100 Ω thermometers, also suitable with other types such as Pt130, Pt500 & Pt1000 Ω
- 4 & 6 core available to extend 2, 3 or 4 wire RTD configurations, the 6 core can be used to extend 2 x 3 wire duplex (dual element) configurations
- Construction PFA insulated 7/0.2mm tin plated copper conductors, twisted cores with nylon cord, tin plated copper braided screen with PFA insulated outer jacket
- Cores colour coded Red & White in accordance with IEC-751, black outer jacket
- Good mechanical strength and flexibility, resistant to oils, acids and other adverse fluids
- Insulation rating -75°C to 260°C
- See below for available reel lengths


Type order	Conductors code	mm²	Cores	Screen	Jacket	Reel Le	ength	Allied	Code	RS
RTD	7/0.2mm	0.219	x 4	Yes	Black 10 me	tres	706463	175	611-8	3078
RTD	7/0.2mm	0.219	x 4	Yes	Black 25 me	tres	70646	176	611-8	3090
RTD	7/0.2mm	0.219	x 4	Yes	Black 50 me	tres	70657	148	827-5	827
RTD	7/0.2mm	0.219	x 4	Yes	Black 100 m	etres	70657	150	827-5	836
RTD	7/0.2mm	0.219	x 6	Yes	Black 25 me	tres	70646	177	611-8	3107
RTD	7/0.2mm	0.219	x 6	Yes	Black 50 me	tres	70657	151	827-5	839

Overall sheath Dimension (approx.)

4 core: 3.2mmØ 6 core: 3.8mmØ

RTD Extension Cable – 4 core PTFE (10 & 25 reel lengths)

Platinum Resistance Thermometer Extension Cable, PTFE insulated & screened



- PTFE insulated cable for extending Platinum Resistance Thermometers
- High temperature to 260°C, wrapped PTFE tape construction
- Can be used to extend 2, 3 or 4 wire RTD configurations
- Commonly used for Pt100 Ω thermometers, also suitable with other types such as Pt130, Pt500 & Pt1000 Ω
- 4 core PTFE insulated 7/0.2mm silver plated copper conductors, twisted cores, Mylar tape, silver plated copper braided screen with PTFE insulated outer jacket
- Cores colour coded 2 x Red / 2 x White to IEC-751 + black outer jacket
- Good mechanical strength and flexibility, resistant to oils, acids and other adverse fluids, steam, gasses etc.
- Insulation rating -75°C to 260°C
- Supplied in 10, & 25 metre reel lengths


Туре	Conductors	mm²	Cores (4 core)	Screen	Jacket Reel Length	Allied Code	RS order code
RTD	7/0.2mm	0.219	2x Red/2x White	Yes	Black 10 metres	70644773	492-9775
RTD	7/0.2mm	0.219	2x Red/2x White	Yes	Black 25 metres	70642885	290-4976

Overall sheath Dimension (approx.)

3.5mmØ

RTD Extension Cable – 4 core PVC (10, 25 & 50 reel lengths)

Platinum Resistance Thermometer Extension Cable, PVC insulated & screened



- PVC insulated cable for extending Platinum Resistance Thermometers
- Can be used to extend 2, 3 or 4 wire RTD configurations
- Commonly used for Pt100 Ω thermometers but also suitable with other types such as Pt130, Pt500 & Pt1000 Ω
- 4 core PVC insulated 7/0.2mm tin plated copper conductors, twisted cores, polyester tape & nylon cord, tin plated copper braided screen with PVC insulated outer jacket
- Cores colour coded 2 x Red / 2 x White to IEC-751 with black outer jacket
- Heat resistant PVC to 105°C
- Good for general purpose cable, highly flexible & waterproof
- Insulation rating -10°C to 105°C
- Supplied in 10, 25 & 50 metre reel lengths


Type	Conductors	mm²	Cores (4 core)	Screen	Jacket Reel Length	Allied Code	RS order code
RTD	7/0.2mm	0.219	2x Red/2x White	Yes	Black 10 metres	70644772	492-9753
RTD	7/0.2mm	0.219	2x Red/2x White	Yes	Black 25 metres	70642884	290-4954
RTD	7/0.2mm	0.219	2x Red/2x White	Yes	Black 50 metres	70646179	611-8129

Overall sheath Dimension (approx.)

4.4mmØ

Platinum Resistance Pt100 & Pt1000 Thin Film Detectors Platinum

Sensing Resistors – Thin Film (Pt100 & Pt1000 Ohm)



Pt100 Elements, Thin Film (100 Ohm)

- Pt100 elements to IEC751 Class A, B and 1/3DIN
- For use from –50°C to +500°C
- Thin film construction
- Suitable for surface & immersion applications where protected
- Vibration resistant

Specifications:

Sensor type: Pt100 (100 Ohms @ 0°C) Construction: Thin film, 10mm tails Temperature range: -50° C to $+500^{\circ}$ C

Ice point resistance: 100Ω

Fundamental interval (0°C to 100°C): 38.5 Ω (nominal) Self-heating: <0.5°C/mW

Thermal response: 0.1s Stability: ±0.05%

Resistance	Dimensions (width x length)	Tolerance Class	Allied code	RS order code		
Pt100	2 x 5.0mm	Class A	70646146	611-7788		
Pt100	2 x 5.0mm	Class B	70646148	611-7801		
Pt100	2 x 5.0mm	Class B	70642888	290-5070 (Packet of 5)		
Pt100	2 x 10mm	Class A	70643577	362-9799		
Pt100	2 x 10mm	Class B	70641762	237-1607		
Pt100	2.0 x 10mm	1/3DIN	70643578	362-9812		
Pt100	2.0 x 2.3mm	Class A	70643579	362-9834		
Pt100	2.0 x 2.3mm	Class B	70643580	362-9840		
Pt100	2.0 x 2.3mm	1/3DIN	70643581	362-9856		
Pt100 Elements (continued)						
Resistance	Dimensions (width x length)	Tolerance Class	Allied code	RS order code		
Pt100	1.2 x 1.6mm	Class A	70646834	666-7362		
Pt100	1.2 x 1.6mm	Class B	70646831	666-7353		

RS198/0816

Pt100	1.0 x 3.0mm	Class A	70646833	666-7359
Pt100	1.0 x 3.0mm	Class B	70646832	666-7356
Pt100	2.0 x 5.0mm	1/3 Din	70656467	814-0162
Pt100	1.2 x 4.0mm	Class B	70656468	814-0165
Pt100	1.2 x 4.0mm	Class A	70656469	814-0169

Pt1000 Elements, Thin Film (1000 Ohm)

- Pt1000 elements to IEC 751 Class A and B
- For use from –50°C to +500°C
- Thin film construction
- Suitable for surface & immersion applications where protected
- Vibration resistant

Specifications:

Sensor type: Pt1000 (1000 Ohms @0°C)
Construction: Thin film, 10mm tails
Temperature range: -50°C to +500°C

Ice point resistance: 1000Ω


Fundamental interval (0°C to 100°C): 385 Ω (nominal) Self-heating: <0.5oC/mW

Thermal response: 0.1s Stability: ±0.05%

Resistance	Dimensions (width x length)	Tolerance Class	Allied code	RS order code
Pt1000	2.0 x 10.0mm	Class A	70643582	362-9907
Pt1000	2.0 x 10.0mm	Class B	70643583	362-9913
Pt1000	2.0 x 10.0mm	1/3 Din	70656472	814-0178
Pt1000	1.0 x 3.0mm	Class B	70656470	814-0171
Pt1000	1.25 x 1.7mm	Class B	70656471	814-0175

Resistance Pt100 Wire-Wound Detector Elements

Pt100 platinum resistance thermometer elements in a choice of sizes – single & dual element



- Pt100 elements to IEC 60751 Class A or B
- 100Ω Ohms @ 0°C
- Single or dual element
- Platinum coil wire-wound construction sealed inside a high purity alumina ceramic body
- Optimum performance & stability
- Temperature range –200°C to +650°C

Specifications:

Sensor type: Pt100 (100 Ohms @ 0°C)
Construction: Wire-Wound, 10mm tails

Temperature range: -200°C to +650°C

Ice point resistance: 100Ω

Fundamental interval (0°C to 100°C): 38.5 Ω (nominal) Self-heating: 0.02 to 0.3°C/mW

Thermal response: <0.4s (secs. to 63% of final value – in water @ 1m/s)

Measuring current: 1mA

Tolerance Class: In accordance with IEC 60751

W0.15 (Class A) -100°C to +450°C W0.3 (Class B) -196°C to +660°C

Continued:

Single element:

RS198/0816

Resistance	Tolerance Class	Diameter ('D')	Length ('L')	Allied code	RS order code		
			_				
Pt100	Class B	1.5mm	8mm	70646153	611-7851		
Pt100	Class A	1.5mm	8mm	70646155	611-7873		
Pt100	Class B	1.5mm	15mm	70646154	611-7867		
Pt100	Class A	1.5mm	15mm	70646151	611-7839		
Pt100	Class B	2.8mm	15mm	70646150	611-7823		
Pt100	Class A	2.8mm	15mm	70646152	611-7845		
Pt100	Class B	2.8mm	25mm	70646147	611-7794		
Pt100	Class A	2.8mm	25mm	70646149	611-7817		
Dual element:							
Pt100 (x2)	Class A	1.5mm	15mm	70643873	397-1595		

