Detailed Specifications & Technical Data

METRIC MEASUREMENT VERSION



8760 Multi-Conductor - Shielded Twisted Pair Cable



For more Information please call

1-800-Belden1



General Description:

18 AWG stranded (16x30) tinned copper conductors, polyethylene insulation, twisted pair, overall Beldfoil® shield (100% coverage), 20 AWG stranded tinned copper drain wire, PVC jacket.

Physical Characteristics (Overall) Conductor AWG: # Pairs AWG Stranding Conductor Material 18 |16x30 TC - Tinned Copper **Total Number of Conductors:** 2 Insulation Insulation Material: Insulation Material Wall Thickness (mm) PE - Polyethylene 0.457 **Outer Shield** Outer Shield Material: Outer Shield Trade Name Type Outer Shield Material Coverage (%) Tape | Aluminum Foil-Polyester Tape w/Shorting Fold | 100 Outer Shield Drain Wire AWG: AWG Stranding Drain Wire Conductor Material 20 7x28 TC - Tinned Copper **Outer Jacket Outer Jacket Material:** Outer Jacket Material Nom. Wall Thickness (mm) PVC - Polyvinyl Chloride 0.711 **Overall Cable Overall Nominal Diameter:** 5.639 mm Pair Pair Color Code Chart: Number Color Black & Clear **Mechanical Characteristics (Overall) Operating Temperature Range:** -20°C To +60°C **Bulk Cable Weight:** 37.205 Kg/Km 240.203 N Max. Recommended Pulling Tension: 57.150 mm Min. Bend Radius/Minor Axis: **Applicable Specifications and Agency Compliance (Overall) Applicable Standards & Environmental Programs** NEC/(UL) Specification: CM CEC/C(UL) Specification: AWM Specification: UL Style 2092 (300 V 60°C) EU Directive 2011/65/EU (ROHS II): Yes EU CE Mark: EU Directive 2000/53/EC (ELV): Yes EU Directive 2002/95/EC (RoHS): Yes EU RoHS Compliance Date (mm/dd/yyyy): 01/01/2004 EU Directive 2002/96/EC (WEEE):

Page 1 of 2 02-09-2017

Detailed Specifications & Technical Data

METRIC MEASUREMENT VERSION



8760 Multi-Conductor - Shielded Twisted Pair Cable

	EU Directive 2003/11/EC (BFR):	Yes			
	CA Prop 65 (CJ for Wire & Cable):	Yes			
	MII Order #39 (China RoHS):	Yes			
Flame Test					
	UL Flame Test:	UL1685 UL Loading			
Suitability					
	Suitability - Indoor:	Yes			
Plenum/Non-Plenum					
	Plenum (Y/N):	No			
	Plenum Number:	88760, 87760 or 82760			

Electrical Characteristics (Overall)

Nom. Inductance:

Inductance (µH/m) 0.59058

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/m) 89.243

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km) 21.3265

Max. Operating Voltage - UL:

Voltage 300 V RMS

Max. Recommended Current:

Current 7.2 Amps per conductor @ 25°C

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
8760 060U1000	1,000 FT	27.000 LB	CHROME		2 #18 LDPE SH PVC
8760 060U500	500 FT	14.000 LB	CHROME		2 #18 LDPE SH PVC
8760 0601000	1,000 FT	27.000 LB	CHROME		2 #18 LDPE SH PVC
8760 06010000	10,000 FT	270.000 LB	CHROME	CY	2 #18 LDPE SH PVC
8760 06010001	10,000 FT	270.000 LB	CHROME	CZ	2 #18 LDPE SH PVC
8760 06015000	15,000 FT	435.000 LB	CHROME	CY	2 #18 LDPE SH PVC
8760 0602000	2,000 FT	54.000 LB	CHROME	С	2 #18 LDPE SH PVC
8760 060250	250 FT	7.000 LB	CHROME		2 #18 LDPE SH PVC
8760 060500	500 FT	14.000 LB	CHROME	С	2 #18 LDPE SH PVC
8760 0605000	5,000 FT	145.000 LB	CHROME	С	2 #18 LDPE SH PVC

Notes:

C = CRATE REEL PUT-UP.

Y = FINAL PUT-UP LENGTH MAY VARY -10% TO +20% FROM LENGTH SHOWN, MAY CONTAIN 2 PIECES, MINIMUM LENGTH OF ANY ONE PIECE IS 1500'.

Z = FINAL PUT-UP LENGTH MAY VARY (+ OR -) 10% FOR SPOOLS OR REELS AND(+ OR -) 5% FOR UNREEL CARTONS FROM LENGTH SHOWN.

Revision Number: 3 Revision Date: 02-09-2017

© 2017 Belden, Inc All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product

product. ´
Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).

Page 2 of 2