



## Main

Range of product	Phaseo Universal
Product or component type	Safety and isolation transformer
Rated power in VA	1000 VA
Input voltage	230 V AC single phase, terminal(s): N-L1 400 V AC phase to phase, terminal(s): L1-L2
Output voltage	115/230 V AC
Secondary winding	Double
Protective cover	Without
Ambient air temperature for operation	-20...60 °C

## Complementary

Input voltage limits	207...253 V 360...440 V
Network frequency limits	47...63 Hz
Input voltage tolerance	+/- 15 V
Efficiency	92 %
Power dissipation in W	87 W
Voltage variation at nominal load	0,0315 at 230 V 0,034 at 400 V
Output sustained overvoltage	0,035 (no load, hot state)
Voltage drop at rated load	<= 4.08 %
No load losses	31.09 W
Short-circuit voltage	0,038
Output protection type	Against overload, protection technology: external Against overvoltage, protection technology: external Against short-circuits, protection technology: external
Connections - terminals	Screw type terminals for input connection, connection capacity: 5 x 4 mm <sup>2</sup> AWG 11 Screw type terminals for input ground connection, connection capacity: 1 x 4 mm <sup>2</sup> AWG 11 Screw type terminals for output connection, connection capacity: 6 x 10 mm <sup>2</sup> AWG 6
Marking	CE
Fixing mode	By 4 screws, screw(s) Ø = 7 mm on horizontal panel with derating to 90 % By 4 screws, screw(s) Ø = 7 mm on vertical panel, operating position: horizontal By 4 screws, screw(s) Ø = 7 mm on vertical panel, operating position: vertical

Output coupling	Grounding of secondary Parallel Series by internal jumper
Operating altitude	3000 m
Electrical insulation class	Class F
Width	150 mm
Height	146 mm
Depth	156 mm
Product weight	14 kg


## Environment

Product certifications	UR EAC
Standards	UL 506
IP degree of protection	IP20
Environmental characteristic	EMC conforming to EN 62041 Safety conforming to EN 61558-1 Safety conforming to EN 61558-2-6
Ambient air temperature for storage	-40...80 °C
Relative humidity	0...95 % during operation
Overvoltage category	Class I conforming to VDE 0106-1
Dielectric strength	Between input and ground Between output and ground Between input and output

## Contractual warranty

Warranty period	18 months
-----------------	-----------

Dimensions




Dimensions in mm

a	b	c	G	J	Ø
150	145	156	122	134	7


Dimensions in in.

a	b	c	G	J	Ø
5.90	5.71	6.14	4.80	5.28	0.27

## Internal Scheme



Primary Voltage Wiring



Secondary Voltage Wiring

