## Maxi free-standing Beacons / Rotating Mirror Light 883 Rotating Mirror Beacon LED 115-230VAC GN



i

Part No.: 883.230.60



MECHANICAL DATA	
Height	218 mm
Diameter	142 mm
Materials	PC PC/ABS
Dome colour	Green
Housing colour	Black
Protection category	IP65
Connection	Screw terminals
cross-sectional area maximum	1,50mm² / 16AWG
Cable entry	Rubber pinch
Cable entry minimum	d = 5 mm
Cable entry maximum	d = 7 mm
Tension relief	Pull-out protection
Type of fixing	Base mounting
Working temperature minimum	-30°C
Working temperature maximum	+50°C
Weight with packaging	765 g
Product weight	676 g
ELECTRICAL DATA	
Operating voltage	115-230∨
Operating voltage type	AC
Operating voltage frequency	50Hz 60Hz
Operating voltage frequency Operating voltage tolerance	
	60Hz
Operating voltage tolerance	60Hz +/- 10%
Operating voltage tolerance Rated operational voltage	60Hz +/- 10% 230 VAC
Operating voltage tolerance Rated operational voltage Rated operational current	60Hz +/- 10% 230 VAC 95 mA
Operating voltage tolerance Rated operational voltage Rated operational current Rated inrush current	60Hz   +/- 10%   230 VAC   95 mA   1.400 mA
Operating voltage tolerance Rated operational voltage Rated operational current Rated inrush current Protection class	60Hz   +/- 10%   230 VAC   95 mA   1.400 mA   Protection class 2
Operating voltage tolerance Rated operational voltage Rated operational current Rated inrush current Protection class Pollution degree	60Hz   +/- 10%   230 VAC   95 mA   1.400 mA   Protection class 2   3
Operating voltage tolerance Rated operational voltage Rated operational current Rated inrush current Protection class Pollution degree Overvoltage category	60Hz   +/- 10%   230 VAC   95 mA   1.400 mA   Protection class 2   3   II
Operating voltage tolerance Rated operational voltage Rated operational current Rated inrush current Protection class Pollution degree Overvoltage category Isolation voltage	60Hz   +/- 10%   230 VAC   95 mA   1.400 mA   Protection class 2   3   II
Operating voltage tolerance Rated operational voltage Rated operational current Rated inrush current Protection class Pollution degree Overvoltage category Isolation voltage OPTICAL DATA	60Hz +/- 10% 230 VAC 95 mA 1.400 mA Protection class 2 3 II Ui = 250V; Uimp = 2.500V
Operating voltage tolerance Rated operational voltage Rated operational current Rated inrush current Protection class Pollution degree Overvoltage category Isolation voltage OPTICAL DATA Light source	60Hz   +/- 10%   230 VAC   95 mA   1.400 mA   Protection class 2   3   II   Ui = 250V; Uimp = 2.500V
Operating voltage tolerance Rated operational voltage Rated operational current Rated inrush current Protection class Pollution degree Overvoltage category Isolation voltage OPTICAL DATA Light source Light colour	60Hz +/- 10% 230 VAC 95 mA 1.400 mA Protection class 2 3 II Ui = 250V; Uimp = 2.500V

For additional installation and mounting information, refer to the appropriate user guide at www.werma.com. This printed copy is for information only and is subject to alteration.

i


## Maxi free-standing Beacons / Rotating Mirror Light 883 Rotating Mirror Beacon LED 115-230VAC GN

APPROVAL DATA	
Conforms with CE	Yes
WEEE	Yes
Conforms with RED directive	No
Conform with ATEX-directive	No
Conforms with CCC-Ex	No
Conforms with CCC	Yes
Conforms with UL	No
Conforms with FCC	No
Conforms with IC	No
EAC certificate available	Yes
Conforms with UKCA (Importer)	No
Conforms with CMIM	No
Conforms with AS-I	No
Conforms with GL	No
Conforms with RoHS CN	No
Conforms with VdS	No

For additional installation and mounting information, refer to the appropriate user guide at www.werma.com. This printed copy is for information only and is subject to alteration.

ļ

## Maxi free-standing Beacons / Rotating Mirror Light 883 Rotating Mirror Beacon LED 115-230VAC GN



For additional installation and mounting information, refer to the appropriate user guide at www.werma.com. This printed copy is for information only and is subject to alteration.