

# Arbitrary Function Generator

## AFG1022 Datasheet



The AFG1022 Arbitrary Function Generator provides a waveform generation tool with the best price performance ratio. It includes dual channel, 25 MHz bandwidth and up-to 10 V<sub>p-p</sub> output amplitude. The four run modes, 50 built-in frequently-used waveforms and the built-in 200 MHz frequency counter cover most waveform generation needs in your experiment and test jobs. The 3.95-inch TFT LCD, short-cut buttons, USB interface and PC software provide the most intuitive ways to configure the instrument.

### Features and benefits

- Dual-channel, 25 MHz sine wave, and 12.5 MHz square/pulse wave provides a cost effective solution for basic education and other applications
- 125 MS/s sampling rate and 14-bit vertical resolution enable great signal fidelity
- 1 mV<sub>p-p</sub> to 10 V<sub>p-p</sub> output amplitude over the whole frequency range
- The intuitive user interface shortens the learning curve for students and other users
- 2 to 8,192-point length of memory for user-defined arbitrary waveforms
- 64-MByte internal non-volatile memory for arbitrary waveform storage
- Standard USB host/device for memory expansion and remote control
- Continuous, sweeping, burst, and modulation modes covers most requirements for students and other users to get the experiments/test job done
- Built-in 200 MHz counter with 6-digit resolution offers an easy and precise way of frequency/period/pulse width/duty cycle measurement
- Menu and online help are in English and Simplified Chinese

- Compact form factor for stacking on other bench instruments to save valuable bench space
- Free ArbExpress makes user defined waveforms editing extremely easy
- Compatible with TekSmartLab™ for easy teaching and learning

### Applications

- Electric and electronics experiments
- Communications experiments
- Sensor simulation
- Functional test

### Performance and features

1 μHz to 25 MHz sine waveform range, with 12-digit or 1 μHz resolution and a ±1 ppm drift high stability time base, provides great signal fidelity in the frequency domain. With 1 mV<sub>p-p</sub> to 10 V<sub>p-p</sub> output amplitude range, and 14-bit or 1 mV<sub>p-p</sub> resolution over the whole frequency range, there is no need to compromise between output amplitude and frequency any more.

Four different run modes and four modulation modes cover most use cases with a cost effective solution. 50 most-frequently used standard and arbitrary waveforms are built-in for easy access. Up to 8,192 points arbitrary waveforms memory enables users to replicate real world signals captured with a Tektronix oscilloscope or defined with ArbExpress. The built-in 200 MHz and 6 digit resolution frequency counter is an easy and precise way to measure frequencies/periods/pulse widths/duty cycles.

## Ease of use

The high-resolution 3.95-inch color TFT display shows relevant settings and parameters in both text and graphic formats, which give users full confidence in their settings, and let them focus on the task at hand. The front panel shortcut buttons and rotary knob make accesses to most frequently used functions and settings with minimum effort and time. The built-in 64-MByte non-volatile memory together with USB stick memory interface, provide unlimited space for user-defined waveform storage.

## Software and solutions

Compatible with ArbExpress, the user-defined arbitrary waveforms generated by the free software can be loaded on the AFG1022 easily with a USB memory stick.

As a building block of Tektronix educational solution, the AFG1022 can be embedded into TekSmartLab and enable a cost efficient and effective way of teaching, learning, and lab management.

## Specifications

### Channels

Number of channels	2
--------------------	---

### Built-in waveforms

Built-in waveforms	Sine, Square, Pulse, Ramp, Noise, and 45 frequently used arbitrary waveforms
--------------------	--

### Sine wave

Range	1 $\mu$ Hz to 25 MHz
-------	----------------------

Sine wave in burst mode	2 mHz to 25 MHz
-------------------------	-----------------

Effective maximum frequency out	25 MHz
---------------------------------	--------

#### Amplitude flatness (1 $V_{p-p}$ )

<10 MHz	$\pm 0.2$ dB
10 MHz to 25 MHz	$\pm 0.3$ dB

Harmonic distortion	< -50 dBc, 1 $V_{p-p}$ , 1 $\mu$ Hz to 25 MHz
---------------------	---

Total harmonic distortion	< 0.2% (10 Hz to 20 kHz, 1 $V_{p-p}$ )
---------------------------	--

Spurious	< -45 dBc, 1 $V_{p-p}$ , 1 $\mu$ Hz to 25 MHz
----------	---

Phase noise	1 MHz: < -110 dBc/Hz at 10 kHz offset, 1 $V_{p-p}$ (typical)
-------------	--

Residual clock noise	-57 dBm (typical)
----------------------	-------------------

**Square wave**

Range	1 $\mu$ Hz to 12.5 MHz
-------	------------------------

Rise/fall time	< 12 ns
----------------	---------

Jitter (rms)	< 1 ns (typical)
--------------	------------------

Overshoot	<5%
-----------	-----

**Ramp wave**

Range	1 $\mu$ Hz to 1 MHz
-------	---------------------

Linearity	$\leq$ 0.1% of peak output at 10% - 90% of amplitude range, at 1 kHz, 1 $V_{p-p}$ , 50% symmetry (typical)
-----------	--

Symmetry	0.0% to 100.0%
----------	----------------

**Pulse wave**

Range	1 MHz to 12.5 MHz
-------	-------------------

Pulse width range	40.00 ns to 999,000 s
-------------------	-----------------------

Pulse width resolution	10 ps or 5 digits
------------------------	-------------------

Pulse duty	<1 MHz, 0.001% to 99.999% (limitations of pulse duty width apply) 1 MHz to 12.5 MHz, 50% fixed
------------	---

Edge transition time	< 12 ns, fixed
----------------------	----------------

Overshoot	< 5% (typical)
-----------	----------------

Jitter (rms)	< 1 ns (typical)
--------------	------------------

**Noise**

Noise bandwidth (-3 dB)	25 MHz
-------------------------	--------

Noise type	White Gaussian
------------	----------------

**DC**

Range	-5 V to +5 V, 50 $\Omega$ load 10 V to + 10 V, open circuit or high Z load
-------	---

## Arbitrary waveform

Range	1 $\mu$ Hz to 10 MHz
Arbitrary waveform in burst mode	2 mHz to 10 MHz
Effective analog bandwidth (-3 dB)	30 MHz
Non-volatile memory	64 MByte
Memory	
Length	2 to 8,192: 125 MS/s
Sampling rate	125 MS/s
Vertical resolution	14 bits
Rise and fall time	< 10 ns
Jitter (rms)	< 6 ns (typical)

## Frequency

Resolution	1 $\mu$ Hz or 12 digits
Internal reference stability	$\pm 1$ ppm at 0 - 40 °C
Internal reference aging	$\pm 1$ ppm per year

## Amplitude

Range	1 mV <sub>p-p</sub> to 10 V <sub>p-p</sub> , 50 $\Omega$ load 2 mV <sub>p-p</sub> to 20 V <sub>p-p</sub> , open circuit or high Z load
Accuracy	$\pm(1\%$ of setting + 1 mV <sub>p-p</sub> ), (1 kHz sine waveform, 0 V offset)
Resolution	1 mV <sub>p-p</sub> , 1 mV <sub>rms</sub> or 4 digits
Units	V <sub>p-p</sub> , V <sub>rms</sub>
Output impedance	50 $\Omega$ (typical)
Local impedance setting	Selectable: 50 $\Omega$ , 1 $\Omega$ to 10.000 k $\Omega$ , High Z (adjusts displayed amplitude according to selected load impedance)
Isolation	No floating ground, signal ground connected to chassis ground
Signal output protection	Short-circuit tolerance, main output automatically disabled when over current

**DC offset**

<b>Range</b>	$\pm(5 V_{pk} - \text{Amplitude}_{pp}/2)$ , 50 $\Omega$ load $\pm(10 V_{pk} - \text{Amplitude}_{pp}/2)$ , open circuit or high Z load
<b>Accuracy</b>	$\pm(1\% \text{ of }  \text{setting}  + 1 \text{ mV} + 0.5\% \text{ of amplitude } (V_{p-p}))$
<b>Resolution</b>	1 mV or 4 digits

**Modulation <sup>1</sup>****Amplitude modulation**

<b>Carrier waveforms</b>	Sine, square, ramp, arbitrary, except DC and noise
<b>Source</b>	Internal / external
<b>Internal modulating waveforms</b>	Sine, square, ramp, noise, arbitrary
<b>Internal AM frequency</b>	2 mHz to 20 kHz
<b>Depth</b>	0.0% to 100.0%

**Frequency modulation**

<b>Carrier waveforms</b>	Sine, square, ramp, arbitrary, except DC and noise
<b>Source</b>	Internal / external
<b>Internal modulating waveforms</b>	Sine, square, ramp, noise, arbitrary
<b>Internal modulating frequency</b>	2 mHz to 20 kHz
<b>Frequency deviation</b>	2 mHz to 12.5 MHz

**Phase modulation**

<b>Carrier waveforms</b>	Sine, square, ramp, arbitrary, except DC and noise
<b>Source</b>	Internal / external
<b>Internal modulating waveforms</b>	Sine, square, ramp, noise, arbitrary
<b>Internal PM frequency</b>	2 mHz to 20 kHz
<b>Phase Deviation</b>	0° to 180°

**Frequency shift keying**

<b>Carrier waveforms</b>	Sine, square, ramp, arbitrary, except DC and noise
<b>Source</b>	Internal / external
<b>Internal modulating waveforms</b>	50% duty cycle square
<b>FSK rate</b>	2 mHz to 100 kHz

<sup>1</sup> Modulation, sweeping, and burst modes are only available in channel 1.

## Sweeping <sup>1</sup>

Carrier waveforms	Sine, square, ramp
Minimum start-stop frequency	1 $\mu$ Hz
Maximum start-stop frequency	Sine: 25 MHz Square: 12.5 MHz Ramp: 1 MHz
Type	Linear, logarithmic
Direction	Up / down
Sweep time	1 ms to 500 s $\pm$ 0.1%
Trigger sources	Internal, external, or manual

## Burst <sup>1</sup>

Waveforms	Sine, square, ramp, pulse, arbitrary except DC and noise
Types	Count (1 to 50,000 cycles), infinite, gated
Start phase	-360° to +360°
Trigger sources	Internal, external, or manual
Internal trigger interval	(40 ns or (cycles x period) to 500 s) $\pm$ 1%
Gate source	External trigger

## Frequency counter

Function	Frequency, period, positive pulse width, duty cycle
Frequency range	100 mHz to 200 MHz
Frequency resolution	6 digits
Coupling mode	AC, DC
<b>Voltage Range and Sensitivity, DC coupled (non-modulation signal)</b>	
100 mHz to 100 MHz	250 mV <sub>p-p</sub> to 5 V <sub>p-p</sub> (AC + DC)
100 MHz to 200 MHz	450 mV <sub>p-p</sub> to 3 V <sub>p-p</sub> (AC + DC)
<b>Voltage range and sensitivity, AC coupled (non-modulation signal)</b>	
1 Hz to 100 MHz	250 mV <sub>p-p</sub> to 5 V <sub>p-p</sub>
100 MHz to 200 MHz	450 mV <sub>p-p</sub> to 4 V <sub>p-p</sub>
Pulse width and duty cycle measure	1 Hz to 10 MHz

## Frequency counter

Input impedance	1 M $\Omega$ in parallel with 100 pF
High frequency noise restraint (HFR)	On / Off (HFR frequency = 500 kHz)
Sensitivity	Low, middle, or high
Trigger level range	-2.5 V to +2.5 V

## Auxiliary inputs and outputs

### External modulation input

Input frequency range	DC to 20 kHz
Input voltage range	All except FSK: $\pm 1$ V full scale, FSK: 3.3 V logic level
Input impedance	12 k $\Omega$ (typical)

### External trigger input

Level	TTL-compatible
Slope	Rising or falling (selectable)
Pulse Width	>100 ns

### External reference clock input

	(Shared with Frequency Counter Input)
Impedance	400 $\Omega$ , AC coupled
Requested Input voltage swing	100 mV <sub>p-p</sub> to 5 V <sub>p-p</sub>
Locking range	10 MHz $\pm 9$ kHz

### External reference clock output

Frequency	10 MHz
Impedance	50 $\Omega$ , DC coupled
Amplitude	1.6 V <sub>p-p</sub> into 50 $\Omega$ load

### Communication interface

USB	Host and device, USB TMC compliance
-----	-------------------------------------

## Display

Display type	3.95-inch
Display resolution	480 by 320
Display colors	65,536

## Menu and online help languages

Menu and online help languages English and Simplified Chinese

---

## Power source

Supply 220-240 VAC, 100-120 VAC, 50/60 Hz, CAT II

---

Consumption Less than 28 W

---

Fuse 110 V: 250 V, F4AL  
220 V: 250 V, F2AL

---

Warm-up time 30 minutes (typical)

---

## Physical characteristics

Dimensions (W, H, D) 235 × 110 × 295 mm (9.2 × 4.33 × 11.61 in)

---

### Weight

Net 3.4 kg (7.4 lbs)

Shipping 4.7 kg (10.3 lbs)

---

## EMC environment and safety

### Temperature

Working 0 °C to 40 °C (32 °F to 104 °F)

Storage -20 °C to 60 °C (-4 °F to 144 °F)

---

### Relative humidity

Operating: ≤ 80%, +0 °C to +40 °C (+32 °F to +104 °F)

Non-operating: 5% to 90%, < +40 °C (+104 °F), non-condensing

Non-operating: 5% to 80%, ≥ +40 °C (+104 °F) to ≤ +60 °C (+140 °F), non-condensing

---

### Altitude

Operating: up to 3,000 m (9842 ft.)

Non-operating: up to 12,000 m (39,368 ft)

---

### Cooling method

Fan cooling

---

### EMC compliance

European Union EN 61326-1

Australia/NZ CISPR 11, Class A

---

### Safety compliance

EN61010-1

IEC61010-1

---



## Ordering information

### Models

AFG1022	Arbitrary Function Generator
---------	------------------------------

### Instrument options

#### Power plug options

Opt. A0	North America power plug (115 V, 60 Hz)
Opt. A1	Universal Euro power plug (220 V, 50 Hz)
Opt. A2	United Kingdom power plug (240 V, 50 Hz)
Opt. A3	Australia power plug (240 V, 50 Hz)
Opt. A5	Switzerland power plug (220 V, 50 Hz)
Opt. A6	Japan power plug (100 V, 50/60 Hz)
Opt. A10	China power plug (50 Hz)
Opt. A11	India power plug (50 Hz)
Opt. A12	Brazil power plug (60 Hz)
Opt. A99	No power cord

#### Service options

Opt. C3	Calibration Service 3 Years
Opt. C5	Calibration Service 5 Years
Opt. R5	Repair Service 5 Years (including warranty)
Opt. R5DW	Repair Service Coverage 5 Years (includes product warranty period). 5-year period starts at time of instrument purchase

Probes and accessories are not covered by the warranty and Service Offerings. Refer to the datasheet of each probe and accessory model for its unique warranty and calibration terms.

## Accessories

### Standard Accessories

- AFG1022 Arbitrary/Function Generator Safety and Compliance Instructions; printed document
- AFG1022 Documentation CD containing the following PDF documents:
  - AFG1022 Arbitrary/Function Generators Quick Start User Manual, English
  - AFG1022 Arbitrary/Function Generators Quick Start User Manual, Simplified Chinese
  - AFG1022 Arbitrary/Function Generators Programmer Manual
  - AFG1022 Arbitrary/Function Generators Specifications and Performance Verification Manual
- Packing list
- Power cord, specified by country
- Certificate of calibration ; printed document
- USB cable x 1, Type A to Type B
- BNC cable x 2
- Tektronix Supplemental Information Sheet For the Peoples Republic of China: China RoHs; printed document
- Fuse, cartridge; 5 x 20 mm, 2 A, 250 V, time-delay
- Fuse, cartridge; 5 x 20 mm, 4 A, 250 V, time-delay

### Warranty

- Three year warranty on parts and labor

### Recommended accessories

- 174-4401-xx, USB cable, type A to type B cable – three feet
- 174-5194-xx, USB cable, type A to type B cable – six feet
- 012-1732-xx, BNC cable assembly, 0 to 1 GHz, shielded – three feet
- 159-0107-xx, Fuse, cartridge; 5 x 20 mm, 2 A, 250 V, time-delay
- 159-0397-xx, Fuse, cartridge; 5 x 20 mm, 4 A, 250 V, time-delay



Tektronix is registered to ISO 9001 and ISO 14001 by SRI Quality System Registrar.



Product Area Assessed: The planning, design/development and manufacture of electronic Test and Measurement instruments.



**ASEAN / Australasia** (65) 6356 3900  
**Belgium** 00800 2255 4835\*  
**Central East Europe and the Baltics** +41 52 675 3777  
**Finland** +41 52 675 3777  
**Hong Kong** 400 820 5835  
**Japan** 81 (3) 6714 3010  
**Middle East, Asia, and North Africa** +41 52 675 3777  
**People's Republic of China** 400 820 5835  
**Republic of Korea** 001 800 8255 2835  
**Spain** 00800 2255 4835\*  
**Taiwan** 886 (2) 2656 6688

**Austria** 00800 2255 4835\*  
**Brazil** +55 (11) 3759 7627  
**Central Europe & Greece** +41 52 675 3777  
**France** 00800 2255 4835\*  
**India** 000 800 650 1835  
**Luxembourg** +41 52 675 3777  
**The Netherlands** 00800 2255 4835\*  
**Poland** +41 52 675 3777  
**Russia & CIS** +7 (495) 6647564  
**Sweden** 00800 2255 4835\*  
**United Kingdom & Ireland** 00800 2255 4835\*

**Balkans, Israel, South Africa and other ISE Countries** +41 52 675 3777  
**Canada** 1 800 833 9200  
**Denmark** +45 80 88 1401  
**Germany** 00800 2255 4835\*  
**Italy** 00800 2255 4835\*  
**Mexico, Central/South America & Caribbean** 52 (55) 56 04 50 90  
**Norway** 800 16098  
**Portugal** 80 08 12370  
**South Africa** +41 52 675 3777  
**Switzerland** 00800 2255 4835\*  
**USA** 1 800 833 9200

\* European toll-free number. If not accessible, call: +41 52 675 3777

**For Further Information.** Tektronix maintains a comprehensive, constantly expanding collection of application notes, technical briefs and other resources to help engineers working on the cutting edge of technology. Please visit [www.tektronix.com](http://www.tektronix.com).

Copyright © Tektronix, Inc. All rights reserved. Tektronix products are covered by U.S. and foreign patents, issued and pending. Information in this publication supersedes that in all previously published material. Specification and price change privileges reserved. TEKTRONIX and TEK are registered trademarks of Tektronix, Inc. All other trade names referenced are the service marks, trademarks, or registered trademarks of their respective companies.



09 Dec 2014 75W-30936-0

[www.tektronix.com](http://www.tektronix.com)

