AM7515MT8A



The AM7515MT8A is a 5MP Dino-Lite Edge Series microscope that has a magnification range of 700-900x with built-in coaxial illumination. By using the Flexible LED Control (FLC), this model is capable of switching between or mixing, brightfield and coaxial illumination.



The coaxial illumination technique reveals details that are very difficult to see under normal light, for example when inspecting wafer plates, microchips or other microelectronics. The AM7515MT8A includes the Automatic Magnification Reading (AMR) feature which automatically detects and displays the magnification in the included Dino-Lite software. These unique features make the Dino-Lite AM7515MT8A a great inspection tool for material analysis, electronics inspection, or any similar application that requires high magnification, coaxial illumination, versatility and mobility. The Dino-Lite AM7515MT8A is bundled with the user-friendly DinoCapture 2.0 software for Windows. For this model it includes functions such as Automatic Magnification Reading (AMR), Flexible LED Control (FLC), calibration, measurement, capturing & annotating images, and recording video. When focusing at such high magnification it is recommended to use a high-precision stand. The Dino-Lite RK-10A for example is a great add-on, it is a sturdy and stable high-end stand solution constructed of resilient stainless steel and lightweight aluminum and offers a very precise fine-focus adjustment.

ADDITIONAL INFO	
7.BBITTOTAL IIII G	
DETAILS	
Dino-Lite range:	Dino-Lite High Magnification
LIGHTING	
Light/ LED type:	White
Number of LEDs:	8
LED on/off switchable:	Yes
Infrared filter:	IR cut-filter >650 nm
Diffuser available:	No
Emission filter:	No
Polarizer:	No
OPTICS	
Magnification:	700-900x
Macro zoom:	No
Working distance:	Standard
Lens type:	Glass with anti-reflection coating
SENSOR	
Sensor type:	CMOS
Resolution:	5 Megapixel (2592x1944)
Maximum frame rate:	30 fps
COMPATIBILITY	
Interface:	USB 2.0
Operating system:	Windows 7, 8 & 10, MacOS 10.9 and up
Included software:	DinoCapture 2.0 (Windows), DinoXcope (Mac OS)

Supported image formats (Windows):	BMP, GIF, PNG, JPG, TIF, RAS, PNM, TGA, PCX, MNG, WBMP, JP2, JPC, PGX
Supported video formats (Windows):	WMV, FLV, SWF
Imaging standards:	DirectShow, UVC
HOUSING	
Housing material:	Metal housing
Magnification lock:	Yes
Dimensions:	10.5cm (L) x 3.2cm (D)
Weight:	140g
Cable length:	1.8m
FEATURES	
Special feature:	Aut. Magn. reading, Flexible LED Control (FLC), Coaxial illumination
Measurement:	Yes
Calibration:	Yes
Microtouch sensor:	Yes
ESD safe:	Yes
INFORMATION	
Package contents:	Microscope, Carry pouch, Software CD, User manual, Quick guide, Calibration target, Front cover
Warranty information:	2 years European warranty
Regulatory approval:	CE, FCC, ROHS

Working distance/ field of view/ depth of

field:

MAGNIFICATION RATE	WORKING DISTANCE*	FIELD OF VIEW(X)	FIELD OF VIEW(Y)	DEPTH OF FIELD
700	6.4	0.56	0.400	0.04
750	6.3	0.52	0.375	0.035
800	6.1	0.48	0.350	0.03
850	6.0	0.46	0.330	0.0275
900	5.9	0.43	0.315	0.26
Listed values may differ slightly	*Without front cap			Unit = mm