# **Detailed Specifications & Technical Data**

#### **METRIC MEASUREMENT VERSION**



## 9502 Multi-Conductor - Computer Cable for EIA RS-232 Applications



For more Information please call

1-800-Belden1



#### **General Description:**

NEC/(UL) Specification:

CEC/C(UL) Specification:

AWM Specification:

EU CE Mark:

EU Directive 2011/65/EU (ROHS II):

EU Directive 2000/53/EC (ELV):

EU Directive 2002/95/EC (RoHS):

24 AWG stranded (7x32) TC conductors, semi-rigid PVC insulation, twisted pairs, overall Beldfoil shield (100% coverage), 24 AWG stranded TC drain Wire, PVC jacket.

#### **Physical Characteristics (Overall)** Conductor AWG: # Pairs AWG Stranding Conductor Material 24 7x32 TC - Tinned Copper **Total Number of Conductors:** Insulation Insulation Material: **Insulation Material** Wall Thickness (mm) S-R PVC - Semi-Rigid Polyvinyl Chloride | 0.279 **Outer Shield** Outer Shield Material: Outer Shield Trade Name Type Outer Shield Material Coverage (%) Tape | Aluminum Foil-Polyester Tape | 100 Outer Shield Drain Wire AWG: AWG Stranding Drain Wire Conductor Material 24 7x32 TC - Tinned Copper **Outer Jacket Outer Jacket Material:** Outer Jacket Material Nom. Wall Thickness (mm) PVC - Polyvinyl Chloride 0.813 **Overall Cable Overall Nominal Diameter:** 5.639 mm Pair Pair Color Code Chart: Number Color Black & Red Black & White **Mechanical Characteristics (Overall)** Operating Temperature Range: -30°C To +80°C **UL Temperature Rating:** 80°C (UL AWM Style 2464) 38.693 Kg/Km **Bulk Cable Weight:** Max. Recommended Pulling Tension: 97.860 N Min. Bend Radius/Minor Axis: 57.150 mm Applicable Specifications and Agency Compliance (Overall) **Applicable Standards & Environmental Programs**

CMG

Yes

Yes

Yes

Yes

UL Style 2464 (300 V 80°C)

Page 1 of 3 01-05-2017

# **Detailed Specifications & Technical Data**

#### METRIC MEASUREMENT VERSION



## 9502 Multi-Conductor - Computer Cable for EIA RS-232 Applications

EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
PMSHA Specification:	SC-7K-182037
Other Specification:	CSA AWM I/II, A
Flame Test	
UL Flame Test:	UL1685 FT4 Loading
CSA Flame Test:	FT4
Suitability	
Sunlight Resistance:	Yes
Plenum/Non-Plenum	
Plenum (Y/N):	No
Plenum Number:	82502

### **Electrical Characteristics (Overall)**

Nom. Inductance:

Inductance (µH/m) 0.623

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/m) 98.43

Nom. Capacitance Cond. to Other Conductor & Shield:

164.05

Nominal Velocity of Propagation:

VP (%)

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km) 78.744

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/km) 55.777

Max. Operating Voltage - UL:

300 V RMS (UL AWM Style 2464)

Max. Recommended Current:

Current 1.76 Amps per conductor @ 25°C

#### Notes (Overall)

Notes: Pennsylvania Department of Environmental Resources and United States Mine Safety and Health Administration certification.

#### **Put Ups and Colors:**

Item #	Putup	Ship Weight	Color	Notes	Item Desc
9502 060U1000	1,000 FT	23.000 LB	CHROME		2 PR #24 PVC FS PVC
9502 060U500	500 FT	12.000 LB	CHROME		2 PR #24 PVC FS PVC
9502 060100	100 FT	2.800 LB	CHROME		2 PR #24 PVC FS PVC
9502 0601000	1,000 FT	30.000 LB	CHROME	С	2 PR #24 PVC FS PVC
9502 06010000	10,000 FT	290.000 LB	CHROME	CY	4 #24 PVC PVC
9502 060500	500 FT	12.000 LB	CHROME	С	2 PR #24 PVC FS PVC
9502 0605000	5,000 FT	110.000 LB	CHROME	CZ	2 PR #24 PVC FS PVC

Notes:
C = CRATE REEL PUT-UP.
Y = FINAL PUT-UP LENGTH MAY VARY -10% TO +20% FROM LENGTH SHOWN.MAY CONTAIN 2 PIECES. MINIMUM LENGTH OF ANY ONE PIECE IS 1500'.
Z = FINAL PUT-UP LENGTH MAY VARY (+ OR -) 10% FOR SPOOLS OR REELS AND(+ OR -) 5% FOR UNREEL CARTONS FROM LENGTH SHOWN.

Page 2 of 3

# **Detailed Specifications & Technical Data**

#### METRIC MEASUREMENT VERSION



## 9502 Multi-Conductor - Computer Cable for EIA RS-232 Applications

Revision Number: 4 Revision Date: 06-24-2014

© 2017 Belden, Inc All Rights Reserved

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product

product. ´ Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 2014/35/EU).

Page 3 of 3